



### Model Number


**IA15-30GM-I3-5M**

Inductive analog sensor

### Features

- Inductive analog
- Output 0 mA ... 20 mA
- Non-flush mountable

### Connection



### Accessories


#### BF 30

Mounting flange, 30 mm

#### DA5-IU-C

Digital display unit

### Dimensions



### Technical Data

#### General specifications

Switching element function	Analog current output
Installation	non-flush
Output polarity	DC
Measurement range	5 ... 15 mm

#### Nominal ratings

Operating voltage	$U_B$	15 ... 30 V
Repeat accuracy		0 ... 15 $\mu$ m
No-load supply current	$I_0$	$\leq 10$ mA

#### Analog output

Output type	0 ... 20 mA
Linearity error	$\leq \pm 10$ % of full-scale value
Load resistor	$\leq 500 \Omega$
Recovery time	1 ... 10 ms, typ. 5 ms
Adjustment tolerance zero point	$\leq \pm 10$ % of full-scale value
Temperature drift	$\leq \pm 0.1$ %/K of full-scale value
Operating voltage	$\leq 0.5$ %
Residual ripple	$\pm 30 \mu$ A

#### Ambient conditions

Ambient temperature	-10 ... 70 °C (14 ... 158 °F)
---------------------	-------------------------------

#### Mechanical specifications

Connection type	cable PVC, 5 m
Core cross-section	0.5 mm <sup>2</sup>
Housing material	brass, nickel-plated
Sensing face	PBT
Protection degree	IP67

#### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007 EN 60947-5-7:2003 IEC 60947-5-7:2003

#### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	CCC approval / marking not required for products rated $\leq 36$ V

Curves

Output characteristics

