

Notes:


- The Entity Concept allows interconnection of intrinsically safe apparatus with associated apparatus not specifically examined in combination as a system when the approved values of  $V_{oc}$  (or  $V_t$ ),  $I_{sc}$  (or  $I_t$ ) and  $P_o$  (or  $P_t$ ) for the associated apparatus are less than or equal to  $V_{max}$  and  $I_{max}$  for the intrinsically safe apparatus and the approved values of  $C_a$  and  $L_a$  for the associated apparatus are greater than  $C_i + C_{cable}$  and  $L_i + L_{cable}$ , respectively, for the intrinsically safe apparatus.  
Note: For installations in which both the  $C_i$  and  $L_i$  of the intrinsically safe apparatus exceed 1% of the  $C_a$  and  $L_a$  parameters of the associated apparatus (excluding the cable), only 50% of  $C_a$  and  $L_a$  parameters are applicable and shall not be exceeded.
- Capacitance and inductance of the field wiring from the intrinsically safe equipment to the associated apparatus shall be calculated and must be included in the system calculations as shown in Note 1. Cable capacitance,  $C_{cable}$ , plus intrinsically safe equipment capacitance,  $C_i$  must be less than the marked capacitance,  $C_a$  (or  $C_o$ ), shown on any associated apparatus used. The same applies for inductance ( $L_{cable}$ ,  $L_i$  and  $L_a$  or  $L_o$ , respectively). Where the cable capacitance and inductance per foot are not known, the following values shall be used:  $C_{cable} = 60 \text{ pF/ft.}$ ,  $L_{cable} = 0.2 \text{ μH/ft.}$
- Simple Apparatus: An electrical component or combination of components of simple construction with well defined electrical parameters that does not generate more than 1.5 volts, 100 milliamps, and 25 milliwatts, or a passive component that does not dissipate more than 1.3 watts and is compatible with the intrinsic safety of the circuit in which it is used (USA). A switch non-inductive resistive device or thermocouple (Canada).
- Wiring methods must be in accordance with the electrical code of the country in use.
- Power, inputs and outputs must be in accordance with Class I, Division 2 wiring methods of National Electrical Code ANSI/NFPA 70, Canadian Electrical Code C22.1 or in accordance with the authority having jurisdiction.
- Intrinsically safe circuits must be wired and separated in accordance with Article 504.20 or other local codes, as applicable.

Dieses Dokument enthält sicherheitsrelevante Angaben. Es darf nicht ohne Absprache mit dem Normenfachmann geändert werden!					
This document contains safety-relevant information. It must not be altered without the authorization of the norm expert!					
CONFIDENTIAL according ISO 16016	Only valid as long as released in EDM or with a valid production documentation!			scale: ---	date:2010-Mar-16
<b>PF PEPPERL+FUCHS</b>	Control Drawing	change notice	respons.	GB.PAW	116-0334
	KFD2-VR2-Ex1.50M & 500M		approved	GB.TC	
			norm	GB.PT	
Oldham					

7. Barriers shall not be connected to any device which uses or generates internally any voltage in excess of 250V Rms or DC unless the device has been determined to adequately isolate the voltage from the barrier.
8. These barriers are rated “Nonincendive”. If the barriers are intended to be mounted in a Division 2 location, they must be installed in an enclosure meeting the requirements of ANSI/ISA-12.12.01-2007, C22.2 NO. 213-M1987. The enclosure may be installed in a Class I, Division 2, Group A, B, C, or D hazardous location. A temperature rating of T4 applies to all nonincendive rated barriers.
9. Connection of barriers to ground is not required.
10. **WARNING:** Substitution of components may impair intrinsic safety.  
**AVERTISSEMENT:** La substitution de composants peut compromettre la sécurité intrinsèque.

**TABLE 1 – ENTITY PARAMETERS**

MODEL NUMBER	TERMINALS	Voc (V)	Isc (mA)	Po (mW)	Vt (V)	It (mA)	Pt (mW)	Groups Ca (µF)			Groups La(mH)		
								A,B	C,E	D,F,G	A,B	C,E	D,F,G
KFD2-VR2-EX1.50M	4,5	5.5	2.4	3.3				58	1000	1000	1000	1000	1000
KFD2-VR2-EX1.500M	4,5	5.5	2.4	3.3				58	1000	1000	1000	1000	1000

Dieses Dokument enthält sicherheitsrelevante Angaben. Es darf nicht ohne Absprache mit dem Normenfachmann geändert werden!					
This document contains safety-relevant information. It must not be altered without the authorization of the norm expert!					
CONFIDENTIAL according ISO 16016	Only valid as long as released in EDM or with a valid production documentation!			scale: ---	date:2010-Mar-16
 <b>PEPPERL+FUCHS</b> Oldham	Control Drawing		change notice	respons.	GB.PAW
	KFD2-VR2-Ex1.50M & 500M			approved	GB.TC
				norm	GB.PT
				116-0334	sheet 2 of 2