

# Bestellbezeichnung / Model Number

VBA-\*E\*A-G10-Z\*

VBA-\*E-G10-Z\*

VBA-\*A-G10-E\*



## Elektrische Daten / Electrical specification

Bemessungsbetriebsspannung  $U_e$  ≤ 32 V PELV  
Rated operating voltage  $U_e$

Bemessungsbetriebsstrom $I_e$	VBA-*E1A-G10-ZAL*	≤ 60 mA
Rated operating current $I_e$	VBA-2E2A-G10-Z/*	≤ 200 mA
	VBA-2E-G10-Z*	≤ 120 mA
	VBA-*E-G10-Z*V31*	≤ 60 mA
	VBA-2A-G10-E*	≤ 60 mA
	VBA-4A-G10-E*	≤ 150 mA
	VBA-*G10-ZEJXE2J*	≤ 200 mA

## Mechanische Daten / Mechanical specification

Anzugsdrehmoment / Tightening torque

Befestigungsschraube / Fastening screw 1,65 Nm / 1.65 Nm

Kabelverschraubung / Cable gland 0,4 Nm / 0.4 Nm

## Umgebungsbedingungen / Ambient conditions

Umgebungstemperatur VBA-\* -25 ... 65 °C / -13 ... 149 °F  
Ambient temperature











Lagertemperatur VBA-\* -25 ... 85 °C / -13 ... 185 °F  
Storage temperature

## Zulassungen und Zertifikate / Approvals and certificates

UL-Zulassung / UL approval cULus Listed, Type 1 enclosure

UL File Number E223772  
„For use in NFPA 79 Applications only“

UL-anerkannte Flachkabel von P+F / UL recognized flat cable from P+F

Bestell- bezeichnung Order code	Farbe Color	Material	Aderquerschnitt Cross-section	UL cable style	Zulassungen Approvals
VAZ-FK-R-YE*	gelb/ yellow	TPE	2 x 1.5 mm <sup>2</sup>	2103	CE  
VAZ-FK-R-BK*	schwarz/ black	TPE	2 x 1.5 mm <sup>2</sup>	2103	CE  
VAZ-FK-PUR-YE*	gelb/ yellow	PUR	2 x 1.5 mm <sup>2</sup>	20549	CE   
VAZ-FK-PUR-BK*	schwarz/ black	PUR	2 x 1.5 mm <sup>2</sup>	20549	CE   
			2 x 2.5 mm <sup>2</sup>	21866	

