



Certificate of Compliance

Certificate: 1029981

Master Contract: 169790

Project: 80161710

Date Issued: 2023-03-30

Issued To: Pepperl+Fuchs SE
Lilienthalstrasse 200
Mannheim, Baden-Württemberg, 68307
Germany

Attention: Sven Kreichgauer

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.

Issued by: Junlong Pan
Junlong Pan



PRODUCTS

CLASS 2258 03 – PROCESS CONTROL EQUIPMENT – Intrinsically Safe and Non-Incendive Systems – For Hazardous Locations

CLASS 2258 04 – PROCESS CONTROL EQUIPMENT – Intrinsically Safe Entity – For Hazardous Locations

Class I, Div. 1, Groups A, B, C and D; Class II, Div. 1, Groups E, F and G; Class III, Div.1;

- Transformer Isolated Barriers, Models; KFD2-SR2-Ex2.W, KFD2-SR2-Ex2.W.SM, KFA6-SR2-Ex2.W, KFA5-SR2-Ex2.W, KFA6-SR2-Ex1.W, KFA5-SR2-Ex1.W, KFA6-SR2-Ex1.W.LB, KFA5-SR2-Ex1.W.LB, KFD2-SR2-Ex1.W.LB, KFD2-SR2-Ex1.W, KFD2-SR2-Ex2.2S, KFA5-SR2-Ex2.W.IR, KFA6-SR2-Ex2.W.IR; provides intrinsically safe circuits when connected per dwg. no. 116-0047; system parameters for terminals 1-3, 2-3, 4-6, 5-6, $V_{max} = 12.6$ V, $R_{min} = 650$ ohms; entity parameters $V_{oc} = 12.6$ V, $I_{sc} = 19.8$ mA, C_a (A,B/C,E/D,F,G) = 1.273/3.82/10.18 uF, L_a (A,B/C,E/D,F,G) = 84.88/298.7/744.4 mH; the following models with part numbers greater than 100000 are suitable for mounting in Class I, Div. 2 Group A,B,C,D



Certificate: 1029981
Project: 80161710

Master Contract: 169790
Date Issued: 2023-03-30

hazardous locations, KF**-SR2-Ex1.W, KF**-SR2-Ex1.W.LB, KF**-SR2-Ex2.W, KFD2-SR2-Ex2.W.SM, KFD2-SR2-Ex2.2S and KF**-SR2-Ex2.W.IR.

- Switch Isolator, Model KFD0-RO-Ex2; provides intrinsically safe voltage and current free contacts for connection to I.S. circuits in accordance with installation dwg. no. 116-0156; these barriers are suitable for mounting in Class I, Div. 2, Group A,B,C,D hazardous locations.
- Isolation Converters, Models KFD0-CC-Ex1 ($V_{oc} = 9.6 \text{ V}$, $I_{sc} = 0.5 \text{ mA}$, $C_a (A,B/C,E/D,F,G) = 3.5/10.5/28 \text{ uF}$, $L_a (A,B/C,E/D,F,G) = 1000/1000/1000 \text{ mH}$), KFD0-TR-Ex1 ($V_{oc} = 16.1 \text{ V}$, $I_{sc} = 33 \text{ mA}$, $C_a (A,B/C,E/D,F,G) = 0.59/1.77/4.72 \text{ uF}$, $L_a (A,B/C,E/D,F,G) = 30/113/268 \text{ mH}$) and KFD0-TT-Ex1 ($V_{oc} = 16.1 \text{ V}$, $I_{sc} = 0.8 \text{ mA}$, $C_a (A,B/C,E/D,F,G) = 0.59/1.77/4.72 \text{ uF}$, $L_a (A,B/C,E/D,F,G) = 1000/1000/1000 \text{ mH}$); provides intrinsically safe circuits when connected per dwg. no. 116-0132.
- Transformer Isolated Barriers, Models KFA5-SOT2-Ex1**, KFA5-SOT2-Ex2**, KFA6-SOT2-Ex1** and , KFA6-SOT2-Ex2**; input rated 115/230Vac, 48-62 Hz, 1.15 VA; provides intrinsically safe outputs when connected per dwg. no. 116-0047; system parameters $V_{max} = 10.5 \text{ V}$, $R_{min} = 81 \text{ ohms}$; entity parameters $V_{oc} = 10.5 \text{ V}$, $I_{sc} = 13 \text{ mA}$, $C_a (A, B/C, E/D, F, G) = 2.66 / 7.9 / 21.3 \text{ uF}$, $L_a (A,B/C,E/D,F,G) = 192 / 671 / 1000 \text{ mH}$.

Note: These barriers must be installed in suitable enclosures in a non-hazardous location (unless specified otherwise) and provide intrinsically safe circuits for switches, thermocouples, non-inductive resistive devices or CSA Certified equipment when installed per manufacturers control drawings.

Ex [ia] IIC:

- Transformer Isolated Barriers, Models KFD2-ST2-Ex1**, KFD2-ST2-Ex2**, KFD2-SOT2-Ex1**, KFD2-SOT2-Ex2**; provides intrinsically safe outputs when connected per dwg. no. 116-0047. $U_m = 60 \text{ V}$; system parameters $U_o (V_{oc}) = 10.5 \text{ V}$, $I_o (I_{sc}) = 13 \text{ mA}$; entity parameters $U_o (V_{oc}) = 10.5 \text{ V}$, $I_o (I_{sc}) = 13 \text{ mA}$, $C_o (C_a) = 2.66 / 7.9 / 21.3 \text{ uF}$ (IIC / IIB / IIA), $L_o (L_a) = 192 / 671 / 1000 \text{ mH}$ (IIC / IIB / IIA); models with part numbers greater than 100000 are suitable for mounting in Class I, Div. 2/Zone 2, Group A,B,C,D/IIC,IIB,IIA hazardous locations.

Note: These barriers must be installed in suitable enclosures in a non-hazardous location (unless specified otherwise) and provide intrinsically safe circuits for switches, thermocouples, non-inductive resistive devices or CSA Certified equipment when installed per manufacturers control drawings. Non-I.S. terminals must not be connected to any equipment that uses or generates in excess of 60 Vrms or DC unless the voltage is limited by an adequate means acceptable to the authority having jurisdiction.

CLASS 2258 04 – PROCESS CONTROL EQUIPMENT – Intrinsically Safe Entity – For Hazardous Locations
CLASS 2258 84 – PROCESS CONTROL EQUIPMENT – Intrinsically Safe Entity – For Hazardous Locations – Certified to US Standards

Class I, Div. 1, Groups A, B, C and D; Class II, Div. 1, Groups E, F and G; Class III, Div.1;
Class I, Div. 2, Group A, B, C and D;



Certificate: 1029981
Project: 80161710

Master Contract: 169790
Date Issued: 2023-03-30

- Universal Temperature Module, Models KFD2-UT2-Ex1 (1 channel) and KFD2-UT2-Ex2 (2 channel); input rated 20-30 Vdc, 48 mA (Ex1) and 70 mA (Ex2) T5 @ 60°C, provides intrinsically safe outputs when connected per dwg. No. 366-024CS-12, entity parameters Voc = 9 V, Isc = 22 mA, Po = 50 mW; Ca (A,B/C,E/D,F,G) = 4.9 / 40 / 500 uF, La (A,B/C,E/D,F,G) = 68 / 275 / 550 mH. Model numbers with a -1 suffix have a voltage output and model numbers without a -1 suffix have a current output.

These barriers must be installed in suitable enclosures in a non-hazardous or Class I, Division 2 hazardous location and provide intrinsically safe circuits for thermocouples, non-inductive resistive devices (RTDs or potentiometers) or CSA Certified entity equipment with mV outputs when installed per manufacturers control drawing.

APPLICABLE REQUIREMENTS

C22.2 No. 142-M1987	Process Control Equipment
CAN/CSA-C22.2 No.157-92	Intrinsically Safe and Non-Incendive Equipment for Use in Hazardous Locations
CSA C22.2 No. 213-M1987	Non-incendive Equipment for Use in Class I, Division 2 Hazardous Locations
UL 913: 6th Edition: 2002	Intrinsically Safe Apparatus and Associated Apparatus for Use in Class I, II, and III, Division 1, Hazardous (Classified) Locations
UL 916: 3rd Edition: 1998	Energy management Equipment
UL 1604: 3rd Edition: 1994	Electrical Equipment For Use In Class I and II, Division 2, And Class III Hazardous (Classified) Locations

MARKINGS

The manufacturer is required to apply the following markings:

- Products shall be marked with the markings specified by the particular product standard.
- Products certified for Canada shall have all Caution and Warning markings in both English and French.

Additional bilingual markings not covered by the product standard(s) may be required by the Authorities Having Jurisdiction. It is the responsibility of the manufacturer to provide and apply these additional markings, where applicable, in accordance with the requirements of those authorities.

The products listed are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US (indicating that products have been manufactured to the requirements of both Canadian and U.S. Standards) or with adjacent indicator 'US' for US only or without either indicator for Canada only.

The following markings are silk-screened onto the side panels of the isolators. Refer to Descriptive Documents List for nameplate details.

- Manufacturer's name: "Pepperl + Fuchs", or CSA Master Contract Number "169790", adjacent to the CSA Mark in lieu of manufacturers name.
- Model number: As specified in the PRODUCTS section, above.
- Electrical ratings: As specified in the PRODUCTS section, above.

Certificate: 1029981
Project: 80161710

Master Contract: 169790
Date Issued: 2023-03-30

- Maximum Ambient temperature 60°C.
- Manufacturing date in MMY format, or serial number, traceable to month of manufacture.
- The CSA Mark, as shown on the Certificate of Conformity.
- Hazardous Location designation: As specified in the PRODUCTS section, above (may be abbreviated).
- Temperature code: As specified in the PRODUCTS section, above. Marking of temperature code T5 or T6 is optional. T4 may be marked for uniformity.
- Reference to I.S. Control Drawing.
- The following words:
 - “[Exia]”.
 - "ASSOCIATED EQUIPMENT / APPAREILLAGE CONNEXE".
 - WARNING: SUBSTITUTION OF COMPONENTS MAY IMPAIR INTRINSIC SAFETY: and, AVERTISSEMENT: LA SUBSTITUTION DE COMPOSANTS PEUT COMPROMETTRE LA SECURITE INTRINSEQUE".
- In addition to the markings required above, the following optional markings may also appear; fz [Ex ia] Class I, Zone 0 or 1, Groups IIC/IIB/IIA and Ex nA Class I, Zone 2, Groups IIC/IIB/IIA.

Notes:

Products certified under Class C225803, C225804, C225884 have been certified under CSA’s ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC).
www.scc.ca





Supplement to Certificate of Compliance

Certificate: 1029981

Master Contract: 169790

The products listed, including the latest revision described below, are eligible to be marked in accordance with the referenced Certificate.

Product Certification History

Project	Date	Description
80161710	2023-03-30	Update to cCSAus Report 1029981 for non-conformance issues noted in FC# 169793, FIR dated Jan 5, 2023.
70067333	2016-05-27	Update to Report 1029981 to include change in the description of the housing material, that no specific material is called out; and only calling out specific requirements.
70041852	2015-09-10	Update of Report 1029981 to include revised drawings.
2515541	2012-04-12	Update to report 1029981 to include revised drawings.
2456233	2011-10-12	Update to report 1029981 to include alternate model KFD2-SOT2-Ex1.R1.
2419435	2011-06-03	Update to report 1029981 to revise the Resistor description.
2351532	2010-11-17	Update to report 1029981 to include revised drawings.
2246616	2010-01-22	Update Report 1029981 to delete models and add alternate components.
2246620	2009-12-03	Update Report 1029981 for revisions to Model KFD2-UT2.
2079812	2008-11-19	Update Report 1029981 to include alternate zener N26.
2023440	2008-06-13	Update Report 1029981 for revisions and model option to KFD2-UT2.
1920058	2007-07-10	Update Report 1029981 to add Model KFD2-SR2-Ex2.W.SM.
1911851	2007-05-18	Update Report 1029981 to add Model KFD2-SOT2-Ex1.N.
1877694	2007-02-02	Update Report 1029981 to add alternate circuit for KFAX-SOT2.
1787874	2006-05-11	Update Report 1029981 to add USA certification of KFD2-UT2.
1746948	2006-04-14	Update Report 1029981 to add KFD2-UT2.



1724670	2005-12-05	Update of Report 1029981 to add alternate drawings and construction.
1655185	2005-04-05	Update of Report 1029981 to add alternate opto-coupler (TOC2).
1608239	2005-01-04	Update of Report 1029981 to add alternate opto-coupler.
1234070	2021-08-21	Alternate electronics for KF**-SR2, KFD2-ST2 and KFD2-SOT2; addition of KF**-SR2-Ex2.W.IR; and Class I, Div. 2/Zone 2 coverage for KF**-SR2, KFD0-RO, KFD2-ST2 and KFD2-SOT2.
1029981	2000-01-28	Addition of Models KFA5-SOT2-Ex1/2 and KFA6-SOT2-Ex1/2 - Originally issued as 250004385. Supersedes Report LR 36087-19