



TYPE APPROVAL CERTIFICATE

Certificate No:
TAA0000160
Revision No:
2

This is to certify:

That the Position Switch

with type designation(s)

Inductive proximity switches, type N x x xx - xxx x x xx - xx - xx - xx-xx

Issued to

Pepperl+Fuchs SE
Mannheim, Germany

is found to comply with

DNV GL rules for classification – Ships, offshore units, and high speed and light craft

Application :

Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV GL.

Location classes:

Temperature	D
Humidity	B
Vibration	B
EMC	B
Enclosure	C / IP67

Issued at **Hamburg** on **2021-07-06**

for **DNV**

This Certificate is valid until **2026-07-05**.

DNV local station: **Augsburg**

Approval Engineer: **Holger Jansen**

Joannis Papanuskas
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



Product description

[1]	[2]	[3]	[4]		[5]	[6]	[7]	[8]		[9]		[10]		[11]
N	x	x	xx	-	xxx	x	x	xx	-	xx	-	xx	-	xx-xx

[1]	N = inductive	
[2]	B = base line J = initiator	
[3]	B = flush N = non-flush	
[4]	Operating range:	0,6mm ... 100mm
[5]	Cylindrical type, diameter: Surface mount type:	12, 18 or 30mm F33 L2 = Varikont L U = Varikont U1_ = plastic terminal block base, M20 and metal rotary socket U1K = plastic terminal block base, M20 and plastic rotary socket U1L= plastic terminal block base, M20 and metal rotary socket, large sensor head U2_ = plastic terminal block base, 1/2 NPT and metal rotary socket U2K = plastic terminal block base, 1/2 NPT and metal rotary socket U2L = plastic terminal block base, 1/2 NPT and metal rotary socket, large sensor head U3_ = metal terminal block base, M20 and metal rotary socket U4_ = metal terminal block base, 1/2 NPT and metal rotary socket U4K = metal terminal block base, 1/2 NPT and plastic rotary socket U4L= metal terminal block base, 1/2 NPT and metal rotary socket, large sensor head
[6]	G = threading	
[7]	M = metal K = plastic	
[8]	Cylindrical type:	usable threaded length in mm
[9]	Electrical output:	A, A0 = 4-wire, DC, NPN, NO and NC A2 = 4-wire, DC, PNP, NO and NC E, E0 = 3-wire, DC, NPN, NO E1 = 3-wire, DC, NPN, NC E2 = 3-wire, DC, PNP, NO E3 = 3-wire, DC, PNP, NC
[10]	Connection elements	V1 = M12x1 device connector for DC proximity switches _ (blank)
[11]	Special properties:	ATEX-category: 3G-3D _ (blank)

Place of manufacture

PT. Pepperl + Fuchs Bintan
 SD 56, 57 Lobam
 Bintan Industrial Estate
 Pulau Bintan, Riau
 Indonesia

Pepper+Fuchs (Vietnam) Company Limited
 Lot S12-16, Street 20 Tan Thuan EPZ
 Tan Thuan Dong Ward, District 7
 Ho Chi Minh City
 Vietnam

Application/Limitation

The Type Approval covers hardware listed under Product description. When the hardware is used in applications to be classed by DNV GL, documentation for the actual application is to be submitted for approval by the manufacturer of the application system in each case. Reference is made to DNV GL RU SHIP Pt.4 Ch.9 Sec. 1.

The operating voltage of the sensors must be well protected against surge caused by lightning, for example by operating at SELV/PELV power supplies.

Ex-certification is not covered by this certificate. Application in hazardous area to be approved in each case according to the Rules and Ex-Certification/Special Condition for Safe Use listed in valid Ex-Certificates issued by a notified/recognized Certification Body.

Type Approval documentation

Test report TÜV no. MHM-EST-7.70049396e (14.07.03)
Test report TÜV no. MHN-EST-7.70053484ea (24.11.03),
Test report Pepperl+Fuchs no. PRDE-3083 (05.08.03)
Test report Pepperl+Fuchs no. PRDE-3084 (13.10.03)
Test report Pepperl+Fuchs no. PRDE-3145 (16.10.03);
Test plan Pepperl + Fuchs no. PRDE-3083A (20.10.08)
Test report Pepperl+Fuchs no. PRDE-8967 (21.11.08)
Test report Pepperl+Fuchs no. PRDE-8966 (05.12.08)
Test report Pepperl+Fuchs no. PRDE-AOY9 (21.04.09)
Test report AUCOTEAM no. 6949/08 (01.10.08)
Test report BASF no. AVS0805669 (07.11.08)
Test report Pepperl+Fuchs no. PRDE-BL68A (14.03.17)
Test report Pepperl+Fuchs no. PRDE-BM88 (05.07.16)
Test report Pepperl+Fuchs no. PRDE-BPR1 (11.01.17)
Test report Pepperl+Fuchs no. PRDE-BPR1_2/AUCOteam no. 12510/16 (04.07.17)
Test report Pepperl+Fuchs no. PRDE-CKV4 (28.06.21)
Data sheet NBN40-U1L-A2 (15.03.17)
Data sheet NBN40-U1L-A0 (15.03.17)
Data sheet NBN40-U4L-A2 (15.03.17)
Order code N x x xx - xxx x x xx - xx - xx - xx-xx (05.04.17)
Circuit diagram no. 01-8462C (04.03.15)
Circuit diagram no. 01-8954A (04.03.15)
Material overview Product family NBN40-U*L-**
Data sheets, drawings and circuit diagrams according to CD 4794803 (21.10.03)
Data sheets, drawings and circuit diagrams according to CD 4794803 (15.01.09)
Type Approval Assessment Report Bintan (2016-12-21)
Type Approval Assessment Report Vung Tau (2018-09-20)
Type Approval Assessment Report (2021-06-30)

Tests carried out

Applicable tests according to Class Guideline DNVGL-CG-0339, Edition December 2019.
Vibration test 2 ... 100Hz with a displacement +/-2.5mm, turnover frequency 19.9Hz, and acceleration 4g.

Marking of product

The products to be marked with:

- manufacturer name or manufacturer logo
- Product name and part no.

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the type are complied with, and that no alterations are made to the product design or choice of systems, software versions, components and/or materials.

The main elements of the assessment are:

- Ensure that type approved documentation is available
- Inspection of factory samples, selected at random from the production line (where practicable)
- Review of production and inspection routines, including test records from product sample tests and control routines
- Ensuring that systems, software versions, components and/or materials used comply with type approved documents and/or referenced system, software, component and material specifications
- Review of possible changes in design of systems, software versions, components, materials and/or performance, and make sure that such changes do not affect the type approval given
- Ensuring traceability between manufacturer's product type marking and the type approval certificate

Periodical assessment is to be performed at renewal of this certificate.

END OF CERTIFICATE