

TYPE APPROVAL CERTIFICATE

This is to certify:**That the Peripheral Equipment**with type designation(s)
Fieldbus devices

Issued to

Pepperl+Fuchs AG
Mannheim, Baden-Württemberg, Germany

is found to comply with

DNV GL rules for classification – Ships, offshore units, and high speed and light craft**Application :****Location classes:****Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV GL.****Temperature D****Humidity B******Vibration A****EMC A for Power Supply devices, B for other devices****Enclosure Required protection according to DNV Rules shall be provided upon installation on board**Issued at **Hamburg** on **2019-10-25**This Certificate is valid until **2024-05-07**.for **DNV GL**DNV GL local station: **Augsburg**Approval Engineer: **Didier Girardin**.....
Joannis Papanuskas
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.



Product description

Power Supply devices

Motherboards:

Compact Fieldbus Power Hub, 8 channel Motherboard, redundant

| Device family | Device |
|---------------|--------------------|
| MBHC-FB-8R* | MBHC-FB-8R |
| | MBHC-FB-8R.YO |
| | MBHC-FB-8R.YO.R |
| | MBHC-FB-8R.RH |
| | MBHC-FB-8R.RH.R |
| | MBHC-FB-8R.HSC |
| | MBHC-FB-8R.HSC.R |
| | MBHC-FB-8R.1 |
| | MBHC-FB-8R.YO.1 |
| | MBHC-FB-8R.RH.1 |
| | MBHC-FB-8R.RH.R.1 |
| | MBHC-FB-8R.HSC.1 |
| | MBHC-FB-8R.HSC.R.1 |

Universal Fieldbus Power Hub, 1, 2, or 4 channel Motherboard

| | |
|----------|----------|
| MB-FB-4* | MB-FB-1R |
| | MB-FB-2R |
| | MB-FB-4 |
| | MB-FB-4R |

Universal PROFIBUS Power Hub, Gateway Motherboard

| | |
|-----------|-----------|
| MB-FB-GT* | MB-FB-GT |
| | MB-FB-GTR |

DART High-Density Power Hub, 4 channel Motherboard, redundant

| | |
|---------------|------------------|
| MBHD-FB-D-4R* | MBHD-FB-D-4R |
| | MBHD-FB-D-4R.GEN |
| | MBHD-FB-D-4R.YO |
| | MBCB-FB-GT-D-2 |

Compact Fieldbus Power Hub, 4 channel Motherboard

| | |
|------------|-----------------|
| MBHC-FB-4* | MBHC-FB-4R |
| | MBHC-FB-4R.1 |
| | MBHC-FB-4R.YO |
| | MBHC-FB-4R.YO.R |

Job Id: **262.1-017581-4**
 Certificate No: **TAA0000272**
 Revision No: **2**

| | |
|--|------------------|
| | MBHC-FB-4R.YO.1 |
| | MBHC-FB-4R.HSC |
| | MBHC-FB-4R.HSC.1 |
| | MBHC-FB-4 |
| | MBHC-FB-4.1 |
| | MBHC-FB-4.YO |
| | MBHC-FB-4.YO.1 |
| | MBHC-FB-4.HSC |
| | MBHC-FB-4.HSC.1 |

Power Hub Motherboard SK3 Basis

| | |
|-------------|------------|
| MBCB-FB-GT* | MBCB-FB-GT |
|-------------|------------|

Power Supplies:

Fieldbus Power Hub, Compact Power Supply Module

| | |
|------------|--------------------|
| HCD2-FBPS* | HCD2-FBPS-1.500 |
| | HCD2-FBPS-1.23.500 |

Fieldbus Power Hub, Power Supply Module

| |
|-------------------|
| HD2-FBPS-1.25.360 |
|-------------------|

DART Power Supply

| |
|-----------------------|
| HD2-FBPS-IBD-1.24.360 |
|-----------------------|

Fieldbus Power Supply

| | |
|------------|--------------------|
| KLD2-FBPS* | KLD2-FBPS-1.25.360 |
| | KLD2-FBPS-1.12.220 |

Gatewaymodules:

PROFIBUS Power Hub, Gateway Module

| | |
|----------|-------------|
| HD2-GTR* | HD2-GTR-4PA |
| | HD2-GTB-2PA |

Diagnostic Modules:

Fieldbus Power Hub, Diagnostic Module, basic or advanced or advanced with relay outputs

| | |
|---------|-------------|
| HD2-DM* | HD2-DM-B |
| | HD2-DM-A |
| | HD2-DM.A.RO |

Job Id: **262.1-017581-4**
 Certificate No: **TAA0000272**
 Revision No: **2**

Kit versions:

Compact PROFIBUS Power Hub and Segment Coupler

| | |
|---------------|----------------------------|
| Kit version | Includes following devices |
| KT-MB-GTB-2PS | |
| includes | MBCB-FB-GT |
| | HD2-FBPS-1.25.360 |
| | HD2-GTB-2PA |

DART High-Density Power Hub

| | |
|-------------------|-----------------------|
| KT-MB-FB-D-4R | |
| KT-MB-FB-D-4R.GEN | |
| KT-MB-FB-D-4R.YO | |
| includes | MBHD-FB-D-4R* |
| | HD2-FBPS-IBD-1.24.360 |

DART Compact PROFIBUS Power Hub and Segment Coupler

| | |
|-----------------|-----------------------|
| KT-MB-GTB-D-2PS | |
| includes | MBCB-FB-GT-D-2 |
| | HD2-FBPS-IBD-1.24.360 |
| | HD2-GTB-2PA |

Other devices

Field Barriers:

FieldBarrier, rated voltage 16...32V DC

| | |
|-------------|----------------|
| R4D0-FB-IA* | R4D0-FB-IA12.0 |
| | R4D0-FB-IA10.0 |
| | R4D0-FB-IA8.0 |
| | R4D0-FB-IA12.1 |
| | R4D0-FB-IA10.1 |
| | R4D0-FB-IA8.1 |

| | |
|--------------|-----------------|
| RD0-FB-Ex.4* | RD0-FB-Ex.4 |
| | RD0-FB-Ex.4.COM |

FieldBarrier in F2 housing

| |
|--------------|
| F2D0-FB-Ex4* |
|--------------|

Segment Protector:

Fieldbus Segment Protector, different number of channels

| | |
|-----------|-------------|
| F2-SP-IC* | F2-SP-IC10* |
| | F2-SP-IC8* |

Job Id: **262.1-017581-4**
 Certificate No: **TAA0000272**
 Revision No: **2**

| | |
|--|------------|
| | F2-SP-IC6* |
| | F2-SP-IC4* |

Segment Protector for Cabinet Installation, different number of channels

| | |
|-----------|--------------|
| R2-SP-IC* | R2-SP-IC12 |
| | R2-SP-IC10 |
| | R2-SP-IC08 |
| | R2-SP-IC06 |
| | R2-SP-IC04 |
| | R2-SP-IC12.1 |
| | R2-SP-IC10.1 |
| | R2-SP-IC08.1 |
| | R2-SP-IC06.1 |
| | R2-SP-IC04.1 |

DART Segment Protector for Cabinet Installation

| | |
|------------|---------------|
| R3-SP-IBD* | R3-SP-IBD8 |
| | R3-SP-IBD12 |
| | R3-SP-IBD8.1 |
| | R3-SP-IBD12.1 |

Fieldbus distribution interface, Segment Protector with trunk short circuit protection, for cabinet and enclosed installation, different number of channels

| | |
|----------|-----------|
| R2-SP-N* | R2-SP-N4 |
| | R2-SP-N6 |
| | R2-SP-N8 |
| | R2-SP-N10 |
| | R2-SP-N12 |

Modular Segment Protector for Cabinet Installation

| | |
|--------|------------|
| RM-SP* | RM-SPTM-N2 |
| | RM-SPEM-N4 |

Fieldbus Segment Protector

| |
|----------|
| R-SP-E12 |
|----------|

Temperature Multiplexer:

Temperature Multi-Input Device with Aluminum Housing

| | |
|--------------|-----------------|
| F2D0-TI-Ex8* | F2D0-TI-Ex8.PA* |
| | F2D0-TI-Ex8.FF* |

Temperature Multi-Input Device for Cabinet Installation

Job Id: **262.1-017581-4**
Certificate No: **TAA0000272**
Revision No: **2**

| | |
|--------------|------------------|
| RD0-TI-Ex8.* | RD0-TI-Ex8.PA.ST |
| | RD0-TI-Ex8.PA.SC |
| | RD0-TI-Ex8.FF.SC |
| | RD0-TI-Ex8.FF.ST |

Overvoltage protection:

Fieldbus Surge Protector, Field Installation on Trunk

| | |
|----------|---------------------|
| TCP-LBF* | TCP-LBF-IA1.36.IE.0 |
| | TCP-LBF-IA1.36.IE.1 |

Fieldbus Surge Protector, Field Installation on Spur

| | |
|----------|--------------------|
| SCP-LBF* | SCP-LBF-IA1.36.IE0 |
| | SCP-LBF-IA1.36.IE1 |

Fieldbus Surge Protector, Field Installation, Ex d or Ex ia

| | |
|---------|--------------|
| F*-LBF* | F*-LBF-D1.32 |
| | F*-LBF-I1.32 |

Leakage Sensor:

| |
|-------|
| ELS-1 |
|-------|

* Different letter and number combinations can be used instead. The letters describe different terminals or cable glands

** All devices fulfil the requirements of Humidity Class B except RD0-TI-EX8.* which fulfils the requirements of Humidity Class A

Approval conditions

The Type Approval covers hardware listed under Product description. When the hardware is used in applications to be classed by DNV, documentation for the actual application is to be submitted for approval by the manufacturer of the application system in each case. Reference is made to DNV Rules for Ships Pt.4 Ch.9 Control and Monitoring Systems.

Application/Limitation

Ex-certification is not covered by this certificate. Application in hazardous area to be approved in each case according to the Rules and Ex-Certification/ Special Condition for Safe Use listed in valid Ex-certificate issued by a notified/recognized Certification Body.

Devices listed under Product Description:

- "Power supply devices" fulfil EMC location class A
- "Other devices" fulfil EMC location class B

Job Id: **262.1-017581-4**
Certificate No: **TAA0000272**
Revision No: **2**

Type Approval documentation

Hidden

Tests carried out

Applicable tests according to class guideline DNVGL-CG-0339, November 2016

Marking of product

The products to be marked with:

- model name
- manufacturer name
- serial number.

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the type are complied with, and that no alterations are made to the product design or choice of systems, software versions, components and/or materials.

The main elements of the assessment are:

- Ensure that type approved documentation is available
- Inspection of factory samples, selected at random from the production line (where practicable)
- Review of production and inspection routines, including test records from product sample tests and control routines
- Ensuring that systems, software versions, components and/or materials used comply with type approved documents and/or referenced system, software, component and material specifications
- Review of possible changes in design of systems, software versions, components, materials and/or performance, and make sure that such changes do not affect the type approval given
- Ensuring traceability between manufacturer's product type marking and the type approval certificate

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE