




EU Type Examination Certificate CML 17ATEX3255X Issue 1

- 1 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU
- 2 Equipment **GR Terminal Box**
- 3 Manufacturer **Pepperl+Fuchs GmbH**
- 4 Address **Lilienthalstrasse 200,
68307 Mannheim,
Germany**
- 5 The equipment is specified in the description of this certificate and the documents to which it refers.
- 6 Certification Management Limited, Unit 1 Newport Business Park, New Port Road, Ellesmere Port CH65 4LZ, UK, Notified Body Number 2503, in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in the confidential reports listed in Section 12.
- 7 If an 'X' suffix appears after the certificate number, it indicates that the equipment is subject to conditions of safe use (affecting correct installation or safe use). These are specified in Section 14.
- 8 This EU Type Examination certificate relates only to the design and construction of the specified equipment or component. Further requirements of Directive 2014/34/EU Article 13 apply to the manufacture of the equipment or component and are separately certified.
- 9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the confidential report, has been demonstrated through compliance with the following documents:

EN 60079-0:2012/A11:2013	EN 60079-7:2015	EN 60079-11:2012
EN 60079-28:2015	EN 60079-31:2014	

- 10 The equipment shall be marked with the following:



II 2 G D

Ex eb IIC T* Gb	Ex eb op pr IIC T* Gb
Ex ia IIC T* Gb	Ex ia op pr IIC T* Gb
Ex op pr IIC T6 Gb	Ex eb ia op pr IIC T* Gb
Ex eb ia IIC T* Gb	Ex tb IIIC T**°C Db

Ta=-#°C to +40/55/65°C

'#' Lower ambient is dependant upon components fitted but shall be no less than -60°C

'*' Refer to description for T classes



CML 17ATEX3255X
Issue 1

11 Description

The GR Terminal Box is a range of increased safety, black, anti-static, glass-fibre reinforced polyester enclosures with a base and screw-down cover (with optional hinges in addition to the fixing screws). The range utilises the Ex Component certified Pepperl+Fuchs GR enclosures covered under certificate numbers IECEx CML 17.0039U and CML 17ATEX3084U.

The terminal boxes are populated with DIN rail mounted, increased safety Ex Component certified terminals.

For cable entry, the terminal boxes may be provided with clearance holes, as required, machined into the top, bottom, left and right faces.

An internal/external earth stud may be provided.

The enclosures are available in a range of standard sizes as shown in the table below, intermediate sizes are also permitted.

Enclosure type	MDP	Height	Width	Depth
GR.*.10.10.07*	3.2 W	100 mm	100 mm	65 mm
GR.*.13.13.09*	6.7 W	130 mm	130 mm	85 mm
GR.*.13.18.09*	11 W	130 mm	180 mm	91.5 mm
GR.*.18.18.10*	14 W	180 mm	180 mm	104 mm
GR.*.18.24.10*	17 W	180 mm	240 mm	104 mm
GR.*.18.36.10*	22 W	180 mm	360 mm	104 mm
GR.*.18.36.17*	27 W	180 mm	360 mm	166.5 mm
GR.*.36.36.10*	33 W	360 mm	360 mm	104 mm
GR.*.36.36.17*	39 W	360 mm	360 mm	166.5 mm
GR.*.36.36.24*	44 W	360 mm	360 mm	241.5 mm
GR.*.48.60.24*	72 W	480 mm	600 mm	241.5 mm
GR.*.36.72.17*	104 W	360 mm	720 mm	166.5 mm
GR.*.36.72.24*	104 W	360 mm	720 mm	241.5 mm

The maximum dissipated power (MDP) in the table above was derived with the terminals used at 60% of their rated current value.

The MDP is valid for the following ambient temperatures and temperature classes:

Ta 40°C T6 T80°C

Ta 55°C T5 T95°C

Ta 65°C T4 T130°C



CML 17ATEX3255X
Issue 1

12 Certificate history and evaluation reports

Issue	Date	Associated report	Notes
0	29/05/2018	R11362A/00	Release of prime certificate
1	19/07/2018	R11362A/01	Dust surface temperatures were changed from T85, T100, T135 to T80, T95, T130

Note: Drawings that describe the equipment or component are listed in the Annex.

13 Conditions of manufacture

The following conditions are required of the manufacturing process for compliance with the certification.

- 13.1 Where the product incorporates certified parts or safety critical components the manufacturer shall ensure that any changes to those parts or components do not affect the compliance of the certified product that is the subject of this certificate.
- 13.2 When terminals are supplied with the enclosure they shall be ATEX/IECEx approved components as specified in the scheduled drawings and having a maximum insulation temperature as below. All terminals shall be installed in accordance with their Conditions of Safe Use/Schedule of Limitations/Conditions of Certification and the relevant codes of practice/wiring regulations, specifically to the minimum creepage and clearance requirements and to any limitations to ratings that may be observed due to method of installation.

Terminals shall have minimum insulation temperature as per the table below

Ta = +40°C	Ta = +55°C	Ta = + 65°C
_80°C	_95°C	_105°C

All terminals fitted shall be suitable for the lower operating temperature marked on the certification label.

- 13.3 The lower ambient temperature shall be de-rated according to the minimum temperature limitations of the components fitted to the enclosure.

14 Special Conditions for Safe Use (Conditions of Certification)

The following conditions relate to safe installation and/or use of the equipment.

- 14.1 When fitted with the fibre optic splice tray, the fibre cables shall be sufficiently supported so as to prevent strain and their minimum bend radius shall be observed and all fibre connectors shall have dust covers fitted if not used.

Certificate Annex

Certificate Number CML 17ATEX3255X
Equipment GR Terminal Box
Manufacturer Pepperl+Fuchs GmbH



The following documents describe the equipment or component defined in this certificate:

Issue 0

Drawing No	Sheets	Rev	Approved date	Title
16-1410CM-04	1 of 7	--	29/05/2018	GR terminal box - general assembly
16-1410CM-04	2 of 7	--	29/05/2018	GR terminal box - maximum power dissipation
16-1410CM-04	3 of 7	--	29/05/2018	GR terminal box - list of terminals
16-1410CM-04	4 of 7	--	29/05/2018	GR terminal box - earth stud
16-1410CM-04	5 of 7	--	29/05/2018	GR terminal box - earth / neutral bar
16-1410CM-04	6 of 7	--	29/05/2018	GR terminal box - splice tray
16-1410CM-04	7 of 7	--	29/05/2018	Label/paint exceeding ESD limitations
16-1410CM-10	1 of 2	--	29/05/2018	GR terminal box type code
16-1410CM-10	2 of 2	--	29/05/2018	GR terminal box certification label

Issue 1

No drawings were updated