

SIL Manufacturer's Declaration

Functional safety of inductive proximity sensors acc. to IEC 61508:2000; PF20CERT1536C

1 Safety Evaluation

Pepperl+Fuchs SE, Lilienthalstrasse 200, 68307 Mannheim

declares as manufacturer that for the inductive proximity sensors, types mentioned below, the calculated PFD_{avg} values for low demand mode of operation are within the allowed range for SIL 2 according to IEC 61508-1:2000 table 2 and do fulfil the requirement to not claim more than 25% of this range, i.e. to be better than or equal to $2.5 \cdot 10^{-3}$.

For high demand mode of operation, the PFH is within the allowed range for SIL 2 according to IEC 61508-1:2000 table 3. It fulfils the requirement to not claim more than 25% of this range, i.e. to be better than or equal to $2.5 \cdot 10^{-7}$ 1/h.

The sensors are considered to be Type A components. Therefore, the SFF has to be 60 % to 90 % according to EN/IEC 61508-2 table 2 for SIL 2 (sub-) systems with a hardware fault tolerance of 0.

2 Products

Inductive proximity sensors with NAMUR interface in accordance with IEC 60947-5-6:1999 or EN 60947-5-6:2000, see product list.

The nominal sensing distance s_n and therefore the assured release distances S_{ar} depend on the dimensions and the material of the target. The distance is the air gap between the target surface and the sensing face while the reference target is in parallel with the sensing face, is centered to the reference axis and is moving along the reference axis.

Product List, Nominal Sensing Distance (s_n), Assured Release Distance (S_{ar}) and Targets

Part No.	Product Name	Function ¹⁾	s_n	S_{ar}	Reference Target
70133061	NJ5-18GK-N	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133270	NJ5-18GK-N-10M	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133271	NJ5-18GK-N-5M	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133062	NJ5-18GM-N	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133272	NJ5-18GM-N-10M	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133063	NJ5-18GM-N-5M	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133064	NJ5-18GM-N-V1	NC	5.0 mm	3.50 mm	18 x 18 x 1 mm ³ , Fe 360
70133286	NJ6-22-N	NC	6.0 mm	4.20 mm	22 x 22 x 1 mm ³ , Fe 360
70133287	NJ6-22-N-10M	NC	6.0 mm	4.20 mm	22 x 22 x 1 mm ³ , Fe 360
70133288	NJ6-22-N-5M	NC	6.0 mm	4.20 mm	22 x 22 x 1 mm ³ , Fe 360
70133289	NJ6-22-N-G	NC	6.0 mm	4.20 mm	22 x 22 x 1 mm ³ , Fe 360
70133290	NJ6-22-N-G-15M	NC	6.0 mm	4.20 mm	22 x 22 x 1 mm ³ , Fe 360
70133291	NJ6-22-N-G-5M	NC	6.0 mm	4.20 mm	22 x 22 x 1 mm ³ , Fe 360
70133065	NJ8-18GK-N	NC	8.0 mm	5.60 mm	24 x 24 x 1 mm ³ , Fe 360
70133273	NJ8-18GK-N-10M	NC	8.0 mm	5.60 mm	24 x 24 x 1 mm ³ , Fe 360
70133066	NJ8-18GM-N	NC	8.0 mm	5.60 mm	24 x 24 x 1 mm ³ , Fe 360
70133278	NJ8-18GM-N-5M	NC	8.0 mm	5.60 mm	24 x 24 x 1 mm ³ , Fe 360
70133279	NJ8-18GM-N-V1	NC	8.0 mm	5.60 mm	24 x 24 x 1 mm ³ , Fe 360
70133284	NJ10-22-N-G	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360

Part No.	Product Name	Function ¹⁾	s_n	S_{ar}	Reference Target
70133285	NJ10-22-N-G-5M	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133308	NJ10-30GKK-N	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133309	NJ10-30GK-N	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133310	NJ10-30GK-N-15M	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133311	NJ10-30GK-N-5M	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133072	NJ10-30GM-N	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133312	NJ10-30GM-N-10M	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133313	NJ10-30GM-N-5M	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133315	NJ10-30GM-N-V1	NC	10.0 mm	7.00 mm	30 x 30 x 1 mm ³ , Fe 360
70133073	NJ15-30GKK-N	NC	15.0 mm	10.50 mm	45 x 45 x 1 mm ³ , Fe 360
70133317	NJ15-30GK-N	NC	15.0 mm	10.50 mm	45 x 45 x 1 mm ³ , Fe 360
70133074	NJ15-30GK-N-10M	NC	15.0 mm	10.50 mm	45 x 45 x 1 mm ³ , Fe 360
70133321	NJ15-30GM-N	NC	15.0 mm	10.50 mm	45 x 45 x 1 mm ³ , Fe 360
70133322	NJ15-30GM-N-10M	NC	15.0 mm	10.50 mm	45 x 45 x 1 mm ³ , Fe 360

¹⁾ NC = normally closed (break)

3 Safety Function

The safe state is reached when the active face is covered with a target (actuator element, damping material) within the assured release distance S_{ar} . In this case the sensor is in the high impedance state ('off state', $I < 1.2$ mA). It is important that the gap size between the target and the active face of the sensor is smaller than S_{ar} .

The nominal sensing distance s_n and therefore the assured release distance S_{ar} depend on the dimensions and the material of the target.

If customized targets are used it must be ensured that the distance between the damping material and the active face of the sensor is closer than 0.7 times the individual measured real sensing distance.

This evaluation is only valid for using amplifiers/safety functions that rely on the 'off state' as safe state.

Sensor respective amplifier output	Sensor condition
On state (low impedance)	active face uncovered (target not present) and sensor functioning
Off state (high impedance, safe state)	active face covered (target present) or sensor defective

4 Safety Characteristic Values

Parameter	Symbol	Condition	Value	Unit
Type			A	
Hardware Fault Tolerance	<i>HFT</i>		0	
Safe Failure Rate	λ_{safe}		14.9	FIT
No Effect Failure Rate	$\lambda_{no\ effect}$		7.55	FIT
Dangerous Failure Rate	$\lambda_{dangerous}$		9.6	FIT
Total Failure Rate	λ_{total}		32.0	FIT
Total Safe Failure Rate	λ_s		22.5	FIT
Total Dangerous Failure Rate	λ_D		9.6	FIT
Safe Failure Fraction	<i>SFF</i>		70	%
Mean Time to Failure	<i>MTTF</i>		3.13E+07	h
Average Probability of Failure on Demand	$PFD_{avg}^{1)}$	$T_1 = 1\ year$	4.21E-05	
Average Probability of Failure on Demand	$PFD_{avg}^{1)}$	$T_1 = 2\ years$	8.42E-05	
Average Probability of Failure on Demand	$PFD_{avg}^{1)}$	$T_1 = 5\ years$	2.10E-04	
Probability of Dangerous Failure per Hour	$PFH^{1)}$		9.60E-09	1/h
Safety Integrity Level	<i>SIL</i>		2	
Diagnostic Coverage	<i>DC</i>		0	%

¹⁾ 1oo1 structure

5 Conditions and Assumptions

The following assumptions have been made during the Failure Mode Effect and Diagnostic Analysis:

- Failure rates are based on the Siemens standard SN 29500.
- Failure rates are constant, wear is not included.
- Propagation of failures is not relevant.
- All component failure modes are known (Type A).
- PFD and PFH values are calculated for use in a 1oo1 structure.
- The repair time after a safe failure is 8 hours.
- The average temperature over a long period of time is 40 °C.
- The stress levels are average for an industrial environment and can be compared to the Ground Fixed classification of MIL-HDBK-217F. Alternatively, the assumed environment is similar to IEC 60645-1, Class C (sheltered location) with an average temperature over a long period of time of 40 °C.
- For the high impedance state the object is within the assured release distance ($s < S_{ar}$).
- The 2-wire connection cable between the sensor and the switching amplifier must meet the qualities as follows: Line resistance $R_{series} < 50\ \Omega$ (both leads in series); Insulation resistance $R_{insulation} > 1\ M\Omega$, as stated in IEC 60947-5-6:1999 and EN 60947-5-6:2000 (NAMUR). The wires must be isolated from any other circuit.
- The sensor is operated within the limits given in its datasheet.
- The sensor is connected to a NAMUR interface in accordance with EN 60947-5-6:2000 or IEC 60947-5-6:1999 that relies on the high impedance state ("off state") of the sensor as safe state and is qualified for SIL 2 applications.
- As noted in EN/IEC 61508-2, a useful lifetime of 8-12 years can be assumed. However, this value strongly depends on the application and can even be higher if e.g. ambient conditions support a long lifetime (moderate usage temperatures and temperature cycles, low mechanical stress).

6 Definitions

The following definitions for the failure of the product were considered.

Application according to EN 60947-5-6:2000 or IEC 60947-5-6:1999 (DC interface for proximity sensors and switching amplifiers (NAMUR)):

Safe State	The safe state is defined as the output being below 1.2 mA (high impedance).
Safe Failure	Failure that causes the sensor current consumption to go to the defined safe state without a demand from the process.
Dangerous Failure	Failure leading to an output current above 1.2 mA when the target is within the assured release distance (i.e. being unable to go to the defined safe state).
“No Effect” Failure	Failure of a component that is part of the safety function but has no effect on the safety function. For the calculation of the <i>SFF</i> it is treated like a safe undetected failure.

For the calculation of the Safe Failure Fraction (*SFF*) the following has to be noted:

$$\lambda_{\text{total}} = \lambda_{\text{safe}} + \lambda_{\text{dangerous}} + \lambda_{\text{no effect}}$$

$$SFF = 1 - \lambda_{\text{dangerous}} / \lambda_{\text{total}}$$

The failure categories listed above expand on the categories listed in IEC 61508:2000 which are only safe and dangerous. It is important to realize that the „no effect“-failures are included in the safe failure category according to IEC 61508:2000.

Note that these failures on their own will not affect system reliability or safety, and should not be included in spurious trip calculations.

Although the safety characteristic values of the sensor are within the allowed range for SIL 2 according to IEC 61508:2000 it depends on the failure rates of the other devices in the safety loop whether a SIL 2 safety function can be implemented.



Reg. Nr. 000760 QM15

Signature of manufacturer:

Function of the signer:

Date:

ppa. Wolfgang Helm

Director Business Unit Sensors
Factory Automation

July 2021

i. V. Ulrich Ehrenfried

Head of Innovation Unit
Electromagnetic Sensors
Factory Automation