



1 **EC - TYPE EXAMINATION CERTIFICATE**

2 **Equipment or Protective System Intended for use in Potentially Explosive Atmospheres  
Directive 94/9/EC**

3 EC - Type Examination Certificate Number: **Baseefa10ATEX0031X**

4 Equipment or Protective System: **Transformer Isolated Voltage Repeater Type HiC2065 / HiC2068**

5 Manufacturer: **Pepperl + Fuchs GmbH**

6 Address: **Lilienthalstrasse 200, 68307 Mannheim, Germany**

7 This equipment or protective system and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.

8 Baseefa, Notified Body number 1180, in accordance with Article 9 of the Council Directive 94/9/EC of 23 March 1994, certifies that this equipment or protective system has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment and protective systems intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in confidential Report No. **GB/BAS/ExTR10.0029/00**

9 Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

**EN 60079-0:2006 EN 60079-11:2007 EN 61241-11:2006**

except in respect of those requirements listed at item 18 of the Schedule.

10 If the sign "X" is placed after the certificate number, it indicates that the equipment or protective system is subject to special conditions for safe use specified in the schedule to this certificate.

11 This EC - TYPE EXAMINATION CERTIFICATE relates only to the design and construction of the specified equipment or protective system. Further requirements of the Directive apply to the manufacturing process and supply of this equipment or protective system. These are not covered by this certificate.

12 The marking of the equipment or protective system shall include the following :

**See schedule**

This certificate may only be reproduced in its entirety, without any change, schedule included.

Baseefa Customer Reference No. **0808**

Project File No. **09/0398**

This certificate is granted subject to the general terms and conditions of Baseefa. It does not necessarily indicate that the equipment may be used in particular industries or circumstances.

**Baseefa**

Rockhead Business Park, Staden Lane,  
Buxton, Derbyshire SK17 9RZ  
Telephone +44 (0) 1298 766600 Fax +44 (0) 1298 766601  
e-mail [info@baseefa.com](mailto:info@baseefa.com) web site [www.baseefa.com](http://www.baseefa.com)  
Baseefa is a trading name of Baseefa Ltd  
Registered in England No. 4305578. Registered address as above.

**R S SINCLAIR**  
**DIRECTOR**  
On behalf of  
**Baseefa**

13

## Schedule

14

Certificate Number Baseefa10ATEX0031X

### 15 Description of Equipment or Protective System

The Transformer Isolated Voltage Repeater Type HiC2065 / HiC2068 is designed to transfer a voltage signal from a hazardous area to unspecified apparatus located in a non-hazardous area. The hazardous area circuit is galvanically isolated from the non-hazardous area circuit using transformers and the voltage and current appearing at the hazardous area connection pins is limited to intrinsically safe levels.

The Transformer Isolated Voltage Repeater Type HiC2065 / HiC2068 comprises a number of electronic components including two isolating transformers, fuses, zener diodes and resistors all mounted on a single printed circuit board and housed in a plastic enclosure with two polarised sockets in the base of the enclosure for hazardous and non-hazardous area connections via a terminal backplane. LED indication is provided for power-on, channel status and fault conditions.

The equipment may be marked:

⊕ II (1)GD [Ex ia] IIC (-20°C ≤ Ta ≤ +60°C)  
[Ex iaD]

⊕ I (M1) [Ex ia] I (-20°C ≤ Ta ≤ +60°C)

#### Input / Output Parameters

##### Non-Hazardous Area Connector(s)

Power Supply: SL1, pins 1a[-] / 1b[-] w.r.t. pins 2a[+] / 2b[+]

$$U_m = 253V \text{ r.m.s.}$$

The circuit connected to the power supply pins is designed to operate from a d.c. supply voltage of up to 30V.

Output: SL1, pins 7a[-] & 8a[+]

$$U_m = 253V \text{ r.m.s.}$$

The circuit connected to the output is designed to operate from a d.c. supply of up to 30V.

Fault Bus: SL1, pin 6b

$$U_m = 253V \text{ r.m.s.}$$

The circuit connected to the fault bus pin is designed to operate from a d.c. supply of up to 30V.

##### Hazardous Area Connector(s)

Input: SL2 pins 5a[+] w.r.t. 5b[-]

$$\begin{array}{ll} U_o = 5.5V & C_i = 0 \\ I_o = 2.4mA & L_i = 0 \\ P_o = 3.3mW \\ U_i = 20V \\ I_i = 8mA \\ P_i = 150mW \end{array}$$



The capacitance and either the inductance or inductance to resistance ratio (L/R) of the hazardous area load connected to the hazardous area connections of the apparatus must not exceed the following values:

GROUP	CAPACITANCE ( $\mu\text{F}$ )	INDUCTANCE (mH)	OR	L/R RATIO ( $\mu\text{H}/\text{ohm}$ )
IIC	58	1000		425
IIB	1000	1000		425
IIA	1000	1000		425
I	1000	1000		425

The above parameters apply when one of the two conditions below is given:

- the total  $L_i$  of the external circuit (excluding the cable) is  $< 1\%$  of the  $L_o$  value or
- the total  $C_i$  of the external circuit (excluding the cable) is  $< 1\%$  of the  $C_o$  value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- the total  $L_i$  of the external circuit (excluding the cable)  $\geq 1\%$  of the  $L_o$  value and
- the total  $C_i$  of the external circuit (excluding the cable)  $\geq 1\%$  of the  $C_o$  value.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than  $1\mu\text{F}$  for Group IIB and  $600\text{nF}$  for Group IIC.

#### 16 Report Number

GB/BAS/ExTR10.0029/00

#### 17 Special Conditions for Safe Use

1. The socket connections at the base of the enclosure must be afforded a degree of protection of at least IP20 when installed.

#### 18 Essential Health and Safety Requirements

All relevant Essential Health and Safety Requirements are covered by the standards listed at item 9.

#### 19 Drawings and Documents

Number	Sheet	Issue	Date	Description
16-0693BS	1 of 1	-	11-Aug-09	Summary HiC2065 / HiC2068
16-0693BS-00	1 – 7	-	30-Jun-09	Description HiC2065 / HiC2068
16-0693BS-01	1 – 3	-	21-Apr-09	Schematic HiC2065 / HiC2068
16-0693BS-02	1 of 1	-	21-Apr-09	Relevant Components HiC2065 / HiC2068
16-0693BS-03	1 of 1	-	21-Apr-09	Component Layout HiC2065 / HiC2068
16-534-04A	1 & 2	A	04-Feb-09	Housing HiC/HiD
16-0693BS-05	1 & 2	-	21-Apr-09	PCB Layout HiC2065 / HiC2068
16-0693BS-06	1 – 5	-	22-Apr-09	Transformers HiC2065 / HiC2068
16-0693BS-07	1 of 1	-	22-Apr-09	PCB Lacquering Details HiC2065 / HiC2068
16-0693BS-10	1 – 4	-	23-Apr-09	Type Label HiC2065 / HiC2068

These drawings are common to, and held with, IECEx BAS 10.0012X.