

1 **EU - TYPE EXAMINATION CERTIFICATE**

2 **Equipment or Protective System Intended for use in Potentially Explosive Atmospheres  
Directive 2014/34/EU**

3 EU - Type Examination Certificate Number: **Baseefa13ATEX0077X – Issue 1**

3.1 In accordance with Article 41 of Directive 2014/34/EU, EC-Type Examination Certificates referring to 94/9/EC that were in existence prior to the date of application of 2014/34/EU (20 April 2016) may be referenced as if they were issued in accordance with Directive 2014/34/EU. Supplementary Certificates to such EC-Type Examination Certificates, and new issues of such certificates, may continue to bear the original certificate number issued prior to 20 April 2016.

4 Product: **Transmitter Power Supply Type KCD2-STC-Ex1.20\***

5 Manufacturer: **Pepperl + Fuchs GmbH**

6 Address: **Lilienthalstrasse 200, 68307 Mannheim, Germany**

7 This re-issued certificate extends EU Type Examination Certificate No. Baseefa13ATEX0077X to apply to product designed and constructed in accordance with the specification set out in the Schedule of the said certificate but having any variations specified in the Schedule attached to this certificate and the documents therein referred to

8 SGS Baseefa, Notified Body number 1180, in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in confidential Report No. See Certificate History

9 Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

**EN 60079-0:2012+A11:2013 EN 60079-11:2012**

except in respect of those requirements listed at item 18 of the Schedule.

10 If the sign “X” is placed after the certificate number, it indicates that the product is subject to the Specific Conditions of Use specified in the schedule to this certificate.

11 This EU - TYPE EXAMINATION CERTIFICATE relates only to the design and construction of the specified product. Further requirements of the Directive apply to the manufacturing process and supply of this product. These are not covered by this certificate.

12 The marking of the product shall include the following :

II (1) G [Ex ia Ga] IIC (-20°C ≤ Ta ≤ +60°C / +70°C)

II (1) D [Ex ia Da] IIIC (-20°C ≤ Ta ≤ +60°C / +70°C)

I (M1) [Ex ia Ma] I (-20°C ≤ Ta ≤ +60°C / +70°C)

SGS Baseefa Customer Reference No. 0808

Project File No. 15/0577

This document is issued by the Company subject to its General Conditions for Certification Services accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and the Supplementary Terms and Conditions accessible at <http://www.sgs.com/SGSBaseefa/Terms-and-Conditions.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained herein reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. It does not necessarily indicate that the equipment may be used in particular industries or circumstances. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, schedule included, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

**SGS Baseefa Limited**

Rockhead Business Park, Staden Lane,  
Buxton, Derbyshire SK17 9RZ

Telephone +44 (0) 1298 766600 Fax +44 (0) 1298 766601

e-mail [baseefa@sgs.com](mailto:baseefa@sgs.com) web site [www.sgs.co.uk/baseefa](http://www.sgs.co.uk/baseefa)

Registered in England No. 4305578.

Registered address: Rossmore Business Park, Ellesmere Port, Cheshire, CH65 3EN

R S SINCLAIR  
TECHNICAL MANAGER

On behalf of SGS Baseefa Limited

13

## Schedule

14

Certificate Number Baseefa13ATEX0077X - Issue 1

### 15 Description of Product

The Transmitter Power Supply Type KCD2-STC-Ex1.20\* is designed to monitoring signals from equipment in a hazardous area to unspecified apparatus located in a non-hazardous area and communication signals in both directions. The hazardous area circuit is galvanically isolated from the non-hazardous area circuit using transformers and the voltage and current appearing at the hazardous area connectors are limited to intrinsically safe levels.

The Transmitter Power Supply KCD2-STC-Ex1.20\* comprises a number of electronic components including four isolating transformer, fuses, zener diodes and resistors all mounted on a single printed circuit board and housed in a plastic enclosure with plug-in terminals for hazardous and non-hazardous area connections. LED indication is provided for power-on status.

The following variants are covered by this certificate:

KCD2-STC-Ex1.20  
KCD2-STC-Ex1.20.ES  
KCD2-STC-Ex1.20.DE  
KCD2-STV-Ex1.20  
KCD2-STV-Ex1.20.ES  
KCD2-STC-Ex1.20(\*\*)-Y1...n  
KCD2-STV-Ex1.20(\*\*)-Y1...n

### Input / Output Parameters

#### Non-Hazardous Area Connector(s)

Power Supply: Terminals 9 & 10 and Power Rail 1 & 2

$$U_m = 253V \text{ r.m.s.}$$

The circuit connected to the power supply pins is designed to operate from a d.c. supply voltage of 19-30V.

Output: Terminals 5, 6, 7 & 8

$$U_m = 253V \text{ r.m.s.}$$

The circuit connected to the output is designed to operate from a d.c. supply of up to 30V.

#### Hazardous Area Connector(s)

Input: Terminals 1 & 2

$$\begin{array}{ll} U_o = 25.2V & C_i = 12nF \\ I_o = 93mA & L_i = 0 \\ P_o = 656mW & \end{array}$$

The output characteristic is trapezoidal,  $U_Q = 28.2V$  (see Annex C, EN 60079-25:2010).

The capacitance and either the inductance or inductance to resistance ratio (L/R) of the hazardous area load connected to the hazardous area connections of the apparatus must not exceed the following values:

GROUP	CAPACITANCE ( $\mu F$ )	INDUCTANCE (mH)	OR	L/R RATIO ( $\mu H/ohm$ )
IIC	0.095	3.400		54.53
IIB	0.808	16.44		218.12
IIA	2.888	32.88		436.25
I	4.788	53.95		715.73

The above parameters apply when one of the two conditions below is given:  
 - the total  $L_i$  of the external circuit (excluding the cable) is  $< 1\%$  of the  $L_o$  value or  
 - the total  $C_i$  of the external circuit (excluding the cable) is  $< 1\%$  of the  $C_o$  value.

The above parameters are reduced to 50% when both of the two conditions below are given:  
 - the total  $L_i$  of the external circuit (excluding the cable)  $\geq 1\%$  of the  $L_o$  value and  
 - the total  $C_i$  of the external circuit (excluding the cable)  $\geq 1\%$  of the  $C_o$  value.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than  $1\mu\text{F}$  for Groups I, IIA & IIB and  $600\text{nF}$  for Group IIC.

Input: Terminals 3 & 4

$$\begin{array}{ll} U_i = 30\text{V} & C_i = 12\text{nF} \\ I_i = 115\text{mA} & L_i = 0 \\ P_i = 700\text{mW} & \end{array}$$

Input: Terminal 3 (+ve) wrt 4

$$\begin{array}{ll} U_o = 5\text{V} & C_i = 12\text{nF} \\ I_o = 0\text{mA} & L_i = 0 \\ P_o = 0\text{mW} & \end{array}$$

Input: Terminal 4 (+ve) wrt 3

$$\begin{array}{ll} U_o = 0.9\text{V} & C_i = 12\text{nF} \\ I_o = 6.8\text{mA} & L_i = 0 \\ P_o = 1.6\text{mW} & \end{array}$$

The capacitance and either the inductance or inductance to resistance ratio (L/R) of the hazardous area load connected to the hazardous area connections of the apparatus must not exceed the following values:

GROUP	CAPACITANCE ( $\mu\text{F}$ )	INDUCTANCE (mH)	OR	L/R RATIO ( $\mu\text{H}/\text{ohm}$ )
IIC	100	768		23466
IIB	1000	3075		93866
IIA	1000	6151		187773
I	1000	10092		308000

The above parameters apply when one of the two conditions below is given:  
 - the total  $L_i$  of the external circuit (excluding the cable) is  $< 1\%$  of the  $L_o$  value or  
 - the total  $C_i$  of the external circuit (excluding the cable) is  $< 1\%$  of the  $C_o$  value.

The above parameters are reduced to 50% when both of the two conditions below are given:  
 - the total  $L_i$  of the external circuit (excluding the cable)  $\geq 1\%$  of the  $L_o$  value and  
 - the total  $C_i$  of the external circuit (excluding the cable)  $\geq 1\%$  of the  $C_o$  value.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than  $1\mu\text{F}$  for Groups I, IIA & IIB and  $600\text{nF}$  for Group IIC.

**16 Report Number**

GB/BAS/ExTR16.0150/00

**17 Specific Conditions of Use**

1. The KCD2-STC-Ex1.2O must be installed in a controlled environment with suitably reduced pollution.

**18 Essential Health and Safety Requirements**

In addition to the Essential Health and Safety Requirements (EHSRs) covered by the standards listed at item 9, the following are considered relevant to this product, and conformity is demonstrated in the report:

Clause	Subject	Compliance
1.2.7	LVD type requirements	Manufacturer responsibility
1.2.8	Overloading of equipment (protection relays, etc.)	User/Installer responsibility
1.4.1	External effects	User/Installer responsibility
1.4.2	Aggressive substances, etc.	User/Installer responsibility

**19 Drawings and Documents**

New drawings submitted for this issue of certificate.

Number	Sheet	Issue	Date	Description
16-0981BS-B	1 of 1	B	2016-May-03	Summary
16-0981BS-00B	1 – 11	B	2015-Jul-27	Description
16-0981BS-01A	1 – 4	A	2015-Nov-10	Schematic
16-0806BS-02A	1 & 2	A	2016-Jan-06	I.S. Relevant Components
16-0981BS-03A	1 & 2	A	2015-Nov-10	Layouts
16-0981BS-05A	1 – 4	A	2015-Jul-28	Layouts
16-0806BS-06A	1 – 7	A	2016-May-03	Transformer
16-0981BS-10A	1 – 3	A	2015-Nov-10	Type Label

Current drawings also associated with this certificate.

Number	Sheet	Issue	Date	Description
16-0533-04	1 & 2	-	2005-Dec-05	Mechanical Parts (Housing)

All drawings are common to Baseefa13ATEX0078X and IECEx BAS 13.0043X and held with IECEx BAS 13.0043X.

**20 Certificate History**

Certificate No.	Date	Comments
Baseefa13ATEX0077X	12 December 2013 Reissued 9 April 2014	The release of the prime certificate. The associated test and assessment is documented in Test Report No. GB/BAS/ExTR13.0136/01. Project File No. 13/0208.
Baseefa13ATEX0077X Issue 1	7 June 2016	To permit the use of alternative components requiring a minor PCB change, other minor drawing changes and to confirm that the current design meets the requirements of EN 60079-0: 2012+A11:2013 in respect of the differences from EN 60079-0:2012. Test Report No. GB/BAS/ExTR16.0150/00. Project File No. 15/0577.

For drawings applicable to each issue, see original of that issue.