




EU Type Examination Certificate CML 17ATEX2143X Issue 1

- 1 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU
- 2 Equipment **Smart Transmitter Power Supplies Type HiD2022 and HiD2022SK**
- 3 Manufacturer **Pepperl + Fuchs GmbH**
- 4 Address **Lilienthalstrasse 200
68307 Mannheim
Germany**
- 5 The equipment is specified in the description of this certificate and the documents to which it refers.
- 6 CML B.V. , Chamber of Commerce No 6738671, Hoogoorddreef 15, Amsterdam, 1101 BA, The Netherlands, Notified Body Number 2776, in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.
- 7 If an 'X' suffix appears after the certificate number, it indicates that the equipment is subject to conditions of safe use (affecting correct installation or safe use). These are specified in Section 14.
- 8 This EU Type Examination certificate relates only to the design and construction of the specified equipment or component. Further requirements of Directive 2014/34/EU Article 13 apply to the manufacture of the equipment or component and are separately certified.
- 9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the confidential report, has been demonstrated through compliance with the following documents:


EN 60079-0:2012+A11:2013 EN 60079-11:2012

- 10 The equipment shall be marked with the following:


 II (1) G

[Ex ia Ga] IIC

Ta = -20°C to +70°C

 II (1) D

[Ex ia Da] IIIC

 I (M1)

[Ex ia Ma] I

Note: An upper ambient temperature within the range +40°C to +70°C may be marked



CML 17ATEX2143X
Issue 1

11 Description

The Smart Transmitter Power Supplies type HiD2022 and HiD2022SK are Intrinsically Safe associated apparatus transmitter power supplies that transfer monitoring signals from a hazardous area to a safe area and communication signals in both directions. The safe area connections are the power supply and output. The hazardous area connections (input circuit) are for sink input, source input or three wire input.

The intrinsically safe input circuit is galvanically isolated from the safe area output by transformers. The voltage and current limitation for the intrinsically safe input circuit is achieved with component selection of zener diodes and current limiting resistors. The circuits are located on a single printed circuit board (PCB).

The Smart Transmitter Power Supplies are suitable for mounting on a suitably certified P+F H-System backplane which incorporates an appropriate mechanical retaining system and connections for field wiring. The enclosure provides an environmental rating of IP 20 and is required to be installed in an enclosure or area with a control of pollution access.

Nomenclature:

Smart Transmitter Power Supplies Type HiD2022 and HiD2022SK

HiD2022 Smart Transmitter Power Supplies

Input 2-wire and 3-wire SMART transmitters and 2-wire SMART current sources

Followed by one of the options:

Blank Output 0/4 mA ... 20 mA current source

SK Output 0/4 mA ... 20 mA current sink

Ratings:

SAFE Area Connections

Power Supply	HiD2022 and HiD2022SK
Connection(s):	20 pin connector SL1: 2a(+), 2b(+); 1a(-), 1b(-)
Operating Supply Voltage:	18 Vdc to 30 Vdc
Maximum Voltage (Um):	250 Vac

Output	HiD2022 and HiD2022SK
Connection(s):	20 pin connector SL1 8a(+), 7a(-); 10a(+), 9a(-)
Maximum Voltage (Um):	250 Vac



CML 17ATEX2143X
Issue 1

Hazardous Area Connections, Input Circuits

Sink input connection	HiD2022 and HiD2022SK
Connection(s):	20 pin connector SL2: 5a(+), 5b(-); 1a(+), 1b(-)
Uo	26.2 V
Uq	27.25 V
Io	93 mA
Po	634 mW
Ci	5 nF
Li	0
Trapezoidal where $R_o = U_q / I_o$	

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel shall not exceed the following values:

GROUP	CAPACITANCE (μ F)	INDUCTANCE (mH)	L/R RATIO (μ H/ Ω)
IIC	0.092	4.11	56.22
IIB	0.745	16.44	224.8
IIA	2.535	32.88	449.7
I	4.415	53.95	737.9

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value, or,
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo, and,
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1 μ F for IIB and 600nF for IIC.



CML 17ATEX2143X
Issue 1

Hazardous Area Connections, Input Circuits

Source transmitter input connection	HiD2022 and HiD2022SK
Connection(s):	20 pin connector SL2: 5b(+), 7a(-); 1b(+), 3b(-)
U _o	2.0 V
I _o	8.5 mA
P _o	4.3 mW
U _i	30 V
I _i	115 mA
P _i	1000 mW
C _i	0
L _i	0
Connection(s):	20 pin connector SL2: 5b +ve wrt 7a; 1b +ve wrt 3b
U _o	2.0 V
I _o	8.5 mA
P _o	4.3 mW
Connection(s):	20 pin connector SL2: 7a +ve wrt 5b; 3b +ve wrt 1b
U _o	1.0 V
I _o	4.3 mA
P _o	1.1 mW

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel shall not exceed the following values:

GROUP	CAPACITANCE (μ F)	INDUCTANCE (mH)	L/R RATIO (μ H/ Ω)
IIC	100	492	8366
IIB	1000	1968	33464
IIA	1000	3936	66928
I	1000	6459	109803

The entity parameters apply when one of the two conditions below is given:

- The total L_i of the external circuit (excluding the cable) is < 1% of the L_o value, or,
- The total C_i of the external circuit (excluding the cable) is < 1% of the C_o value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total L_i of the external circuit (excluding the cable) > 1% of the L_o, and,
- The total C_i of the external circuit (excluding the cable) > 1% of the C_o.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1 μ F for IIB and 600nF for IIC.



CML 17ATEX2143X
Issue 1

Hazardous Area Connections, Input Circuits:

Three wire transmitter input connection	HiD2022 and HiD2022SK
Connection(s):	20 pin connector SL2: 5a(+), 5b, 7a(-); 1a(+), 1b, 3b(-)
Uo	26.2 V
Uq	27.25 V
Io	115mA
Po	784mW
Ci	5nF
Li	0
Trapezoidal where $R_o = U_q / I_o$	

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel shall not exceed the following values:

GROUP	CAPACITANCE (μ F)	INDUCTANCE (mH)	L/R RATIO (μ H/ Ω)
IIC	0.092	2.68	45.38
IIB	0.745	10.75	181.5
IIA	2.535	21.50	363.1
I	4.415	35.27	595.6

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value, or,
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo, and,
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1 μ F for IIB and 600nF for IIC.



CML 17ATEX2143X
Issue 1

12 Certificate history and evaluation reports

Issue	Date	Associated report	Notes
0	09 Aug 2017	R2218A/00	Issue of Prime Certificate
1	07 Mar 2019	R12226A/00	Transfer of Certificate to CML BV

Note: Drawings that describe the equipment or component are listed in the Annex.

13 Conditions of Manufacture

The following conditions are required of the manufacturing process for compliance with the certification.

- i. Where the product incorporates certified parts or safety critical components, the manufacturer shall ensure that any changes to those parts or components do not affect the compliance of the certified product that is the subject of this certificate.
- ii. All transformers shall be subjected to EN 60079-11 CL 11.2 Routine Tests for Infallible Transformers with an applied voltage of 1 500 V applied between the input and output windings. The test voltage shall be applied for a period of at least 60 s. Alternatively, the test may be carried out at 1.2 times the test voltage, but with reduced duration of at least 1 s. The applied voltage shall remain constant during the test. The current flowing during the test shall not increase above that which is expected from the design of the circuit and shall not exceed 5 mA r.m.s. at any time. During these tests, there shall be no breakdown of the insulation between windings or between any winding and the core.

14 Special Conditions for Safe Use (Conditions of Certification)

The following conditions relate to safe installation and/or use of the equipment.

- i. The equipment shall be installed in an enclosure that provides a degree of protection not less than IP54 in accordance with the requirements of EN 60079-0 unless the equipment is intended to be afforded an equivalent degree of protection by location. In addition, the pollution level shall be limited to pollution degree 2 or better as defined in IEC 60664-1 (Pollution degree 2 can be achieved when the installation is in a controlled environment with suitably controlled condensation or airborne pollution).
- ii. For some types of enclosure, additional certification will be required to permit the installation of the module within the enclosure. Reference shall be made to the enclosure certificate. The installer shall ensure that the maximum ambient temperature of the module when installed is not exceeded.
- iii. The equipment shall be installed on a suitably certified P+F H-System backplane which incorporates an appropriate mechanical retaining system.



Certificate Annex

Certificate Number CML 17ATEX2143X
Equipment Smart Transmitter Power Supplies Type HiD2022 and HiD2022SK
Manufacturer Pepperl+Fuchs GmbH

The following documents describe the equipment or component defined in this certificate:

Issue 0

Drawing No	Sheets	Rev.	Approved Date	Title
16-1305CM-01	1 to 6	2017-04-06	09 Aug 2017	Schematic HiD2022 & HiD2022SK
16-1136CM-02	1 to 22	2017-02-27	09 Aug 2017	Safety Relevant Components
16-1305CM-03	1 to 2	2017-04-06	09 Aug 2017	Component Layout HiD2022 & HiD2022SK
16-0534-04A	1 to 2	2009-02-04	09 Aug 2017	Housing HiC/HiD
16-1305CM-05	1 to 5	2017-04-06	09 Aug 2017	PCB Layout HiD2022 & HiD2022SK
16-1305CM-06	1 to 6	2017-03-27	09 Aug 2017	Transformers HiD2022 & HiD2022SK
16-1305CM-09	1 to 3	2017-06-15	09 Aug 2017	Instructions HiD2022 & HiD2022SK
16-1305CM-10	1 to 3	2017-06-15	09 Aug 2017	Type Label HiD2022 & HiD2022SK

Issue 1

None.