

CERTIFICATE

(1) EU-Type Examination

(2) **Equipment or protective systems intended for use in potentially explosive atmospheres - Directive 2014/34/EU**

(3) EU-Type Examination Certificate Number: **DEKRA 17ATEX0101** Issue Number: **1**

(4) Product: **Liquid Level Transmitter Type Level Probe LGC2**

(5) Manufacturer: **Pepperl + Fuchs SE**

(6) Address: **Lilienthalstrasse 200, 68307 Mannheim Germany**

(7) This product and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.

(8) DEKRA Certification B.V., Notified Body number 0344 in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in confidential test report number NL/DEK/ExTR17.0059/01.

(9) Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

EN IEC 60079-0 : 2018

EN 60079-11 : 2012

except in respect of those requirements listed at item 18 of the Schedule.

(10) If the sign "X" is placed after the certificate number, it indicates that the product is subject to the Specific Conditions of Use specified in the schedule to this certificate.

(11) This EU-Type Examination Certificate relates only to the design and construction of the specified product. Further requirements of the Directive apply to the manufacturing process and supply of this product. These are not covered by this certificate.

(12) The marking of the product shall include the following:



II 2 G Ex ia IIC T6 ... T4 Gb

Date of certification: 31 July 2024

DEKRA Certification B.V.

R. Schuller
Certification Manager

Page 1/2



Throughout this document, a point is used as the decimal separator.

© Integral publication of this certificate and adjoining reports is allowed. This Certificate may only be reproduced in its entirety and without any change.

(13) **SCHEDULE**

(14) **to EU-Type Examination Certificate DEKRA 17ATEX0101** Issue No. 1

(15) **Description**

Level Transmitter Level Probe LGC2-..... is a pressure transmitter that is applied for measuring a liquid level using hydrostatic pressure measurement.

The transmitter consists of a sensor assembly that is suspended by means of its cable down to the bottom of the tank or reservoir and optionally a terminal enclosure for connection of the field wiring. The measured pressure is proportional to the height of the water column above the sensor. The measurement signal is converted into a 4 - 20 mA current signal with or without digital communication (HART).

Ambient temperature range -10 °C to +40 °C for T6;
-10 °C to +55 °C for T5;
-10 °C to +70 °C for T4.

Electrical data

Supply and output signal (red and black wires and/or optionally, terminals + and -):
in type of protection intrinsic safety Ex ia IIC, only for connection to a certified intrinsically safe circuit, with following maximum values:

$U_i = 30 \text{ Vdc}$; $I_i = 133 \text{ mA}$; $P_i = 1 \text{ W}$; $L_i = 1 \text{ } \mu\text{H/m}$ (integral cable);
 $C_i = 10,3 \text{ nF} + 180 \text{ pF/m}$ (integral cable).

Installation instructions

The instructions provided with the product shall be followed in detail to assure safe operation.

(16) **Report Number**

NL/DEK/ExTR17.0059/01.

(17) **Specific conditions of use**

None.

(18) **Essential Health and Safety Requirements**

Covered by the standards listed at item (9).

(19) **Test documentation**

As listed in Report No. NL/DEK/ExTR17.0059/01.