





Mining And Surface Certification (Pty) Ltd

2015/021934/07

THIS CERTIFICATE IS ISSUED AS AN I.A. CERTIFICATE IN TERMS OF THE MINE HEALTH AND SAFETY ACT, ACT NO 29 OF 1996 (AND REGULATIONS), THE OCCUPATIONAL HEALTH AND SAFETY ACT (ACT 85 OF 1993) AND REGULATION 17 OF THE ELECTRICAL MACHINERY REGULATIONS

IA CERTIFICATE	MASC MS/17-0887	Issue	3
Issue Date	30 April 2024	Expiry Date	30 April 2027
** Based on Certificate No	IECEx BAS 09.0142	Issue / Variations / Amendment	6
Requested by	Pepper+Fuchs (Pty) Ltd Zerwick Forum, 8 Glen Eagle Office Park Cnr Monument Rd and Braambos St, Glen Erasmia, Kempton Park 1619, South Africa		
Manufacturer	Pepper+Fuchs SE Lilienthalstrasse 200, 68307 Mannheim, Germany		
Description	<p>The Z Series Shunt Zener Diode Safety Barriers are designed to restrict the transfer of energy, from unspecified safe area equipment to intrinsically safe circuits, by the limitation of voltage and current. The range consists of single, double, triple and quadruple channel barriers covering polarised – positive and negative, non-polarised, non-polarised-star connected barriers and diode return barriers.</p> <p>The barriers consist of electronic components on a single printed circuit board encapsulated within a moulded plastic enclosure which incorporates two or four terminals with separate earth terminal at both the hazardous and non-hazardous area ends and an integral spring mounted foot, designed for a DIN rail.</p> <p>The barriers are asymmetrical and have light blue hazardous area terminals.</p> <p>See Base certificate** annex for series range and electrical parameters.</p>		
Equipment	Shunt Zener Diode Safety Barriers	Type	Z-Series
MARKING: Original marking as per certificate ** remains applicable. IA number must be added.	Type: Ex Marking:	Z-Series Shunt Zener Diode Safety Barriers [Ex ia Ga] IIC [Ex ia Da] III C [Ex ia Ma] I -20°C ≤ Ta ≤ +60°C	
	IA Number: Warnings:	MASC MS/17-0887 (To be additionally marked on equipment) See Base Certificate ** (original marking must be applied)	
Quality Assurance report (QAR) / Notification (QAN):	DE/PTB/QAR06.0008/20		
Compliance: The equipment as described above has been allocated the rating <u>Explosion Protected 'as above'</u> utilizing the SANS/IEC Standards: <ul style="list-style-type: none"> SANS (IEC) 60079-0: 2019 Equipment - General requirements SANS (IEC) 60079-11: 2012 Equipment protection by intrinsic safety "i" <i>Note: This certificate covers only the listed standards and does not imply compliance to any other standard, related or inferred. It is up to the manufacturer to ensure that the product complies to all relevant standards for the application.</i>			
Special conditions of safe use "X":	<ul style="list-style-type: none"> Refer to Annex A below for more details. 		
Conditions of manufacture:	<ul style="list-style-type: none"> Refer to Annex A below for more details. 		
			
C. WELTHAGEN TECHNICAL SPECIALIST	N. VILOJEN TECHNICAL OFFICER		
<p>This certificate covers all units sold as long as the QAR/QAN remains valid. According to the relevant requirements of the MHS Act and the OHS Act, production units of explosion protected equipment are required to comply with third party quality assurance (an approved mark scheme or batch testing by an accredited test laboratory).</p>			

Apparatus in hazardous locations is subject to the following provisions as applicable, which shall be adhered to:
 SANS 10086 requirements;
 Any conditions mentioned in the above certificate;
 Any relevant requirements of the MHS Act;
 Any restrictions and conditions enforced by the chief inspector of mines, principal inspector (Group I equipment) or chief inspector of factories (Group II equipment).

This certificate may only be reproduced in full
 The certificate is not transferable and remains the property of the issuing body.

IA CERTIFICATE: MASC MS/17-0887
Equipment: Z-Series Shunt Zener Diode Safety Barriers
(Expiry date: 30 April 2027)

ANNEX A

This document is based on and must be read in conjunction with certificate IECEX BAS 09.0142	
Description (According to Base Certificate) **	
"Refer to description in Base Certificate ** (and any applicable schedules/issues/variations)."	
Issue	Issue 1: Supplemented for review as per ARP 0108. Issue 2: Reviewed as per ARP 0108. Issue 3: Supplemented for review as per ARP 0108.
Standard compliance	See Base Certificate **
Special conditions of safe use ("X")	<ul style="list-style-type: none"> • None.
Conditions of manufacture	<ul style="list-style-type: none"> • None.
Conditions of Certification	<ul style="list-style-type: none"> • This IA Certificate covers all units sold from the date of this document to the expiry date of this certificate. • As per ARP 0108 a maximum three yearly review is required on this IA Certificate (expiry is determined as per the QAR/QAN/QMS expiry date). • The apparatus must be additionally marked with the MASC marking details above. • This approval only covers the equipment as certified above and does not include any scheduled additions or variations / amendments / new issues to the certificate(s), made after the above date. • The equipment does not need to be re-tested when used on the conditions and with such restrictions as prescribed by the certificate on which this IA Certificate is based and any other conditions in this IA Certificate. • The certification on which this IA Certificate is based must remain valid. • The extent of the requirements in the ARP 0108 (or regulations), SANS 10108 and any other applicable regulations on the certification of the equipment must remain unchanged. • The Ex-quality assurance notification/report for the equipment must remain valid.
Conclusion:	<ul style="list-style-type: none"> • From the above and the selective examination of the documentation, nothing contrary to the requirements of the applicable standards was found, provided that the equipment / component is used as described in the above document / certificate and according to the MASC conditions below. A MASC IA certificate is issued based on the work done as per the Base Certificate **. • The routine tests for production units according to the Base Certificate ** must be complied with (if applicable).

This document is issued based on Mining And Surface Certification's Standard Contract terms and conditions available on request.

While every endeavour is made to ensure that a test / assessment / inspection is representative and accurately performed, and that a report / certificate is accurate in the quoted results and conclusions drawn from the test / assessment / inspection, MASC or its directors/employees shall in no way be liable for any error made in carrying out the test / assessment or for any erroneous statement, whether in fact or in opinion, contained in a report / certificate issued pursuant to a test / assessment / inspection.

MASC takes no responsibility for any non-conformances, exclusions, or any results / assessments / inspections not in compliance with the standards. By marking the equipment in accordance with the documentation / standard, the manufacturer / applicant attests on his own responsibility that the equipment / installation has been designed and constructed in accordance with the applicable requirements of the relevant standards and documentation, that the routine verifications / routine tests have been correctly completed and the equipment / installation complies with the documentation and standard(s).

This document is only for use and application in South Africa. It is issued based on National interpretations and accepted practices.

This document may only be reproduced in full.
This certificate is not transferable and remains the property of the issuing body.
This document will not be supported by MASC for certification purposes outside the borders of South Africa.

Mining And Surface Certification (Pty) Ltd Reg No: 2015/021934/07
Directors: Roelof Viljoen & Francois du Toit
Unit #5, Lelyta Park, 45 Jurg Avenue, Hennospark Ext 87, Centurion, 0157
P.O. Box 14344, Clubview, 0014
Tel: 012 653 2959 ♦ Fax: 086 605 8568
e-mail: info@masc-ex.co.za