



中国国家强制性产品认证证书

证书编号: 2020322315002302

认证委托人名称及地址

Pepperl+Fuchs SE
Lilienthalstraße 200, 68307 Mannheim, Germany

生产者名称及地址

Pepperl+Fuchs SE
Lilienthalstraße 200, 68307 Mannheim, Germany

生产企业名称及地址

PT. Pepperl and Fuchs Bintan
SD56/57 Jalan Asoka BIIE, Bintan Industrial Estate Pulau Bintan, Kepulauan Riau,
Republic of Indonesia

产品名称和系列、型号、规格

电感式传感器
FJ系列, NJ系列, NB系列, NC系列

产品标准和技术要求

GB/T 3836.1-2021、GB/T 3836.4-2021

上述产品符合《强制性产品认证实施规则 防爆电气》
(CNCA-C23-01:2019)的要求, 特发此证。

发证日期:2024年03月27日 有效期至:2025年09月26日

首次发证日期:2020年09月27日

认证模式:型式试验+初始工厂检查+获证后监督

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站 (www.cnca.gov.cn) 查询。



批准:

上海仪器仪表自控系统检验测试所有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020322315002302

NAME AND ADDRESS OF THE APPLICANT

Pepperl+Fuchs SE
Lilienthalstraße 200, 68307 Mannheim, Germany

NAME AND ADDRESS OF THE MANUFACTURER

Pepperl+Fuchs SE
Lilienthalstraße 200, 68307 Mannheim, Germany

NAME AND ADDRESS OF THE FACTORY

PT. Pepperl and Fuchs Bintan
SD56/57 Jalan Asoka BIIE,
Bintan Industrial Estate Pulau Bintan, Kepulauan Riau, Republic of Indonesia

NAME, SERIES, MODEL AND SPECIFICATION

Inductive Sensor
FJ series, NJ series, NB series, NC series

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 3836.1-2021、GB/T 3836.4-2021

This is to certify that the above-mentioned product(s) complies with the requirements of implementation rules for compulsory certification (CNCA-C23-01:2019).

Issue date: : 2024-03-27 Valid until:2025-09-26

Date of initial issue:2020-09-27

Type of Certification: Type test + Initial inspection + Surveillance inspection

The certificate details and validity can be verified by scanning the QR code below or logging into the issuing authority's official website. It can also be inquired on the CNCA website (www.cnca.gov.cn).

(In case of dispute, the Chinese text shall prevail.)



APPROVAL:



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第1页共10页

产品名称：
电感式传感器

型号规格：

NCB 15 P - M1 - N0 - V - Y...	N	Inductive proximity sensor
	NJ	Inductive proximity sensor
	FJ	Inductive proximity sensor, surface shaped
NCB 15 P - M1 - N0 - V - Y...	B	Basic series with basic characteristics
	C	Comfort series with improved characteristics
	/	Blank: no specification, characters from the right will be moved left
NCB 15 P - M1 - N0 - V - Y...	B	Flush mounting
	N	Non flush mounting
	/	Blank: no specification, characters from the right will be moved left
NCB 15 P - M1 - N0 - V - Y...	0.5 - 100	Nominal sensing range in mm
NCB 15 P - M1 - N0 - V - Y...	P	Sensor to detect non ferrous metal
	/	Blank: no specification, characters from the right will be moved left
NCB 15 P - M1 - N0 - V - Y...	Enclosure details	
	-M1, M1K	Square target area
	-F	Special construction type, flat, partly with cylindrical sensor

本页为证书附页，应与证书主页同时使用。



SITIiAS
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第2页共10页

- F1 Quad shaped, flat construction
- F69 Housing form factor 'F69'
- FP Square Target area, plug in type
- L2 Housing form factor 'Varikont L' + type 'V' plug
- U10 Plastic housing form factor 'U10'
- V3 Micro switch housing
- 110 Width of sensor in mm

Base details

- +U1, -U1K Plastic base, intended for cable gland M20 x 1,5¹⁾
- +U2, -U2K Plastic base, intended for cable gland ½" NPT
- +U3, -U3K Metal base, intended for cable gland M20 x 1,5¹⁾
- +U4, -U4K Metal base, intended for cable gland ½" NPT
- U1LK Enlarged sensor head, plastic base, intended for cable gland M20, plastic rotatable base¹⁾
- U2LK Enlarged sensor head, plastic base, intended for cable gland ½" NPT, plastic rotatable base¹⁾
- U3LK Enlarged sensor head, metal base, intended for cable gland M20, plastic rotatable base¹⁾
- U4LK Enlarged sensor head, metal base, intended for cable gland ½" NPT, plastic rotatable base
- / Blank: no specification, characters from the right will be moved left

Electrical design

- | | | |
|---------------------------------|----|--------------------------------|
| N C B 15 P - M1 - N0 - V - Y... | N | NAMUR opening (normally close) |
| | N0 | NAMUR opening (normally close) |
| | N1 | NAMUR closing (normally open) |

Additional marking (multiple entries are possible)

- | | | |
|------------------------------------|------|---|
| N C B 15 P - M1 - N0 - V1 - Y... C | C | Magnetic field resistant sensors |
| V... | V... | The "V" will be followed by a string from 1 to 4 numbers between 0 and 9 which are related to |

本页为证书附页，应与证书主页同时使用。



SITIIAS
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第3页共10页

the connector details e.g. V1 or V16

P1 Plastic base, intended for cable gland M20 x 1,5

P2 Plastic base, intended for cable gland ½” NPT

P3 Metal base, intended for cable gland M20 x 1,5

P4 Metal base, intended for cable gland ½” NPT

0,05 – 100M Defines cable length

/ Blank: no specification, characters from the right will be moved left

NCB 15 P- M1 - N0 - V - Y... Y...

The “Y” will be followed by a string from 1 to 8 numbers between 0 and 9. Also a separator between the numbers, like “-” or “.” could be possible. The numbers stand for the different part numbers which are related to specific customer design without specific safety relevance e.g. color, connection detail, increased EMC

a... The "a..." will be replaced by any combination of letters or numbers which are related to specific customer design without safety relevance e.g. brand label

/ Blank: no specification

防爆标志：

Ex ia II C T6...T1 Ga

Ex ia II C T6...T1 Gb

Ex ia III C T₂₀₀ 135°C Da

电气参数：

●爆炸性气体环境

Group II (EPL Ga/Gb)	power type 1	power type 2	power type 3	power type 4
	Ui = 16 V	Ui = 16 V	Ui = 16 V	Ui = 16 V
	Ii = 25 mA	Ii = 25 mA	Ii = 52 mA	Ii = 76 mA

本页为证书附页，应与证书主页同时使用。



SITIiAS
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号: 2020322315002302

证书附页: 第4页共10页

				Pi = 34 mW			Pi = 64 mW			Pi = 169 mW			Pi = 242 mW		
maximum permissible ambient temperature in °C for application in temperature class															
Type	EPL	Ci [nF]	Li [µH]	T6	T5	T4- T1	T6	T5	T4- T1	T6	T5	T4- T1	T6	T5	T4- T1
FJ6-110-N...	GaGb	150	110	73	88	100	73	88	100	62	77	81	54	63	63
FJ7-N...	GaGb	65	220	73	88	100	73	88	100	62	77	81	54	63	63
NCB2-F1-N0...	GaGb	90	100	73	88	100	66	81	100	45	60	89	30	45	74
NCB2-V3-N0...	GaGb	100	100	73	88	100	66	81	100	45	60	89	30	45	74
NCN2-F56-N1...	GaGb	100	100	75	90	100	70	85	100	55	70	87	-	-	-
NBN3-F69-N0...	GaGb	100	100	72	87	100	65	80	100	41	56	63	24	37	37
NBN4-V3-N0...	GaGb	100	100	73	88	100	66	81	100	45	60	89	30	45	74
NBN4-V3-N0- Y189289	GaGb	120	100	72	87	100	65	80	100	41	56	63	24	37	37
NBB15-U...K-N0...	GaGb	110	200	73	88	100	66	81	100	45	60	89	30	45	74
NBB20-U...K-N0...	GaGb	110	200	73	88	100	66	81	100	45	60	89	30	45	74
NBN30-U...K-N0...	GaGb	105	300	73	88	100	66	81	100	45	60	89	30	45	74
NBN40-U...K-N0...	GaGb	105	300	73	88	100	66	81	100	45	60	89	30	45	74
NBN40-U...LK-N0...	GaGb	165	130	73	88	100	66	81	100	45	60	89	30	45	74
NCN4-V3-N0...	GaGb	100	100	73	88	100	66	81	100	45	60	89	30	45	74
NCB15+U...+N0...	GaGb	110	160	73	88	100	66	81	100	45	60	89	30	45	74
NCN15-M...-N0...	GaGb	100	100	73	88	100	66	81	100	45	60	89	30	45	74
NCB20-L2-N0...	GaGb	110	200	73	88	100	66	81	100	45	60	89	30	45	74
NCN20+U...+N0...	GaGb	110	160	73	88	100	66	81	100	45	60	89	30	45	74
NCN30+U...+N0...	GaGb	110	160	73	88	100	66	81	100	45	60	89	30	45	74
NCB40-FP-N0...	GaGb	220	360	73	88	100	66	81	100	45	60	89	30	45	74
NCN40+U...+N0...	GaGb	120	130	73	88	100	66	81	100	45	60	89	30	45	74
NCN40-L2-N0...	GaGb	105	300	73	88	100	66	81	100	45	60	89	30	45	74
NCN50-FP-N0...	GaGb	220	360	73	88	100	66	81	100	45	60	89	30	45	74

本页为证书附页，应与证书主页同时使用。



SITIAs
Worldwide Access

批准:

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第5页共10页

NJ0,8-F-N...	CaGb	30	50	73	88	100	67	82	100	45	60	78	30	45	57
NJ1,5-F-N...	CaGb	30	50	73	88	100	67	82	100	45	60	78	30	45	57
NJ2,5-F-N...	CaGb	40	50	73	88	100	66	81	100	45	60	89	30	45	74
NJ2-F1-N...	CaGb	30	50	73	88	100	66	81	100	45	60	89	30	45	74
NJ2-V3-N...	CaGb	40	50	73	88	100	66	81	100	45	60	89	30	45	74
NJ3-V3-N...	CaGb	40	50	73	88	100	66	81	100	45	60	89	30	45	74
NJ4-F-N...	CaGb	150	100	73	88	100	66	81	100	45	60	89	30	45	74
NJ6-F-N...	CaGb	70	100	73	88	100	66	81	100	45	60	89	30	45	74
NJ10-F-N...	CaGb	85	100	73	88	100	66	81	100	45	60	89	30	45	74
NJ15+U...+N...	CaGb	140	130	73	88	100	66	81	100	45	60	89	30	45	74
NJ15-M1...-N...	CaGb	140	100	73	88	100	66	81	100	45	60	89	30	45	74
NJ20+U...+N...	CaGb	150	130	73	88	100	66	81	100	45	60	89	30	45	74
NJ30+U...+N...	CaGb	160	130	73	88	100	66	81	100	45	60	89	30	45	74
NJ30P+U...+1N...	CaGb	150	170	73	88	100	66	81	100	45	60	89	30	45	74
NJ40+...+N...	CaGb	180	130	73	88	100	66	81	100	45	60	89	30	45	74
NJ50-FP-N...	CaGb	320	360	73	88	100	66	81	100	45	60	89	30	45	74

●可燃性粉尘危险场所

Group III (EPL Da)			power type 1	power type 2	power type 3	power type 4
			Ui = 16 V	Ui = 16 V	Ui = 16 V	Ui = 16 V
			Ii = 25 mA	Ii = 25 mA	Ii = 52 mA	Ii = 76 mA
			Pi = 34 mW	Pi = 64 mW	Pi = 169 mW	Pi = 242 mW
maximum permissible ambient temperature						
Type	Ci [nF]	Li [μH]	T [°C]	T [°C]	T [°C]	T [°C]
FJ6-110-N...	150	110	100	100	63	not applicable
FJ7-N...	65	220	100	100	63	
NCB2-F1-N0...	90	100	100	100	71	
NCB2-V3-N0...	100	100	100	100	71	
NCN2-F56-N1...	100	100	100	100	69	
NBN3-F69-N0...	100	100	100	98	52	

本页为证书附页，应与证书主页同时使用。



SITIIS Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第6页共10页

NBN4-V3-N0...	100	100	100	100	71
NBN4-V3-N0-Y1892 89	120	100	100	98	52
NBB15-U...K-N0...	110	200	100	100	71
NBB20-U...K-N0...	110	200	100	100	71
NBN30-U...K-N0...	105	300	100	100	71
NBN40-U...K-N0...	105	300	100	100	71
NBN40-U...LK-N0...	165	130	100	100	71
NCN4-V3-N0...	100	100	100	100	71
NCB15+U...+N0...	110	160	100	100	71
NCN15-M...-N0...	100	100	100	100	71
NCB20-L2-N0...	110	200	100	100	71
NCN20+U...+N0...	110	160	100	100	71
NCN30+U...+N0...	110	160	100	100	71
NCB40-FP-N0...	220	360	100	100	71
NCN40+U...+N0...	120	130	100	100	71
NCN40-L2-N0...	105	300	100	100	71
NCN50-FP-N0...	220	360	100	100	71
NJ0,8-F-N...	30	50	100	100	59
NJ1,5-F-N...	30	50	100	100	59
NJ2,5-F-N...	40	50	100	100	71
NJ2-F1-N...	30	50	100	100	71
NJ2-V3-N...	40	50	100	100	71
NJ3-V3-N...	40	50	100	100	71
NJ4-F-N...	150	100	100	100	71
NJ6-F-N...	70	100	100	100	71
NJ10-F-N...	85	100	100	100	71
NJ15+U...+N...	140	130	100	100	71
NJ15-M1...-N...	140	100	100	100	71
NJ20+U...+N...	150	130	100	100	71
NJ30+U...+N...	160	130	100	100	71

本页为证书附页，应与证书主页同时使用。



SITIIS
Worldwide Access

批

准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第7页共10页

NJ30P+U...+1N...	150	170	100	100	71	
NJ40+...+N...	180	130	100	100	71	
NJ50-FP-N...	320	360	100	100	71	

相关报告编号：

2023S17402-013171

使用条件：

- 1.产品最低使用环境温度为-60℃，最高使用环境温度见电气参数。
- 2.产品连接电路以及温度组别，详见电气参数。
- 3.当产品使用环境温度下限为-20℃到-60℃之间时，在实际安装使用时应采取可靠措施，防止产品受到机械冲击。
- 4.电感式传感器的连接方式应确保其在安装后至少满足IP20（GB/T 4208-2017）要求。
- 5.当产品应用于爆炸性危险环境且外壳为塑料材质时，根据应用环境的具体气体组别及EPL等级，需采用相应措施以防静电积累危险。具体详见下表。

Type	Group I	Group II (EPL Ga)	Group II (EPL Gb)	Group III
FJ6-110-N...	-	IIB/IIC	IIC	III
FJ7-N...	-	IIC	-	III
NCB2-F1-N0...	-	IIC	-	-
NCB2-V3-N0...	-	IIC	-	-
NCN2-F56-N1...	-	IIC	-	-
NBN3-F69-N0...	-	IIC	-	-
NBN4-V3-N0...	-	IIC	-	-
NBN4-V3-N0-Y189289	-	IIC	-	-
NBB15-U...K-N0...	-	IIC	IIC	III
NBB20-U...K-N0...	-	IIC	IIC	III
NBN30-U...K-N0...	-	IIC	IIC	III
NBN40-U...K-N0...	-	IIC	IIC	III

本页为证书附页，应与证书主页同时使用。



SITIAs
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第8页共10页

NBN40-U...LK-N0...	-	IIA/IIIB/IIIC	IIIC	III
NCN4-V3-N0...	-	IIIC	-	-
NCB15+U...+N0...	-	IIIC	IIIC	III
NCN15-M...-N0...	-	IIIC	-	III
NCB20-L2-N0...	-	IIIC	-	III
NCN20+U...+N0...	-	IIIC	IIIC	III
NCN30+U...+N0...	-	IIIC	IIIC	III
NCB40-FP-N0...	-	IIA/IIIB/IIIC	IIIC	III
NCN40+U...+N0...	-	IIIB/IIIC	IIIC	III
NCN40-L2-N0...	-	IIIC	-	III
NCN50-FP-N0...	-	IIA/IIIB/IIIC	IIIC	III
NJ0,8-F-N...	-	-	-	-
NJ1,5-F-N...	-	-	-	-
NJ2,5-F-N...	-	IIIC	-	-
NJ2-F1-N...	-	IIIC	-	III
NJ2-V3-N...	-	IIIC	-	-
NJ3-V3-N...	-	IIIC	-	-
NJ4-F-N...	-	IIIC	IIIC	-
NJ6-F-N...	-	IIIC	-	III
NJ10-F-N...	-	IIIC	-	III
NJ15+U...+N...	-	IIIC	IIIC	III
NJ15-M1...-N...	-	IIIC	-	III
NJ20+U...+N...	-	IIIC	IIIC	III
NJ30+U...+N...	-	IIIC	IIIC	III
NJ30P+U...+1N...	-	IIIB/IIIC	IIIC	III
NJ40+...+N...	-	IIIB/IIIC	IIIC	III
NJ50-FP-N...	-	IIA/IIIB/IIIC	IIIC	III

6.下列型号产品在爆炸性危险环境使用时，如果其浇封表面裸露在外，应注意采取措施可靠措施防止其受到机械损坏。

FJ6-110-N...

FJ7-N...

NBN3-F69-N0...

NBN4-V3-N0...

NBN4-V3-N0-Y189289

本页为证书附页，应与证书主页同时使用。



SITIAs
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第9页共10页

NCB2-V3-N0...
 NCN2-F56-N1...
 NCN4-V3-N0...
 NJ0,8-F-N...
 NJ1,5-F-N...
 NJ2-V3-N...
 NJ3-V3-N...

7.下列型号产品在爆炸性危险环境使用时，需采用相应措施（如可靠接地等）以防静电积累危险。外壳上的螺丝等体积较小的金属部件可不接地。

FJ6-110-N...	FJ7-N...	NBB15-U3K-N0...	NBB15-U4K-N0...
NBB20-U3K-N0...	NBB20-U4K-N0...	NBN30-U3K-N0...	NBN30-U4K-N0...
NBN40-U3K-N0...	NBN40-U4K-N0...	NCB15+U3+N0...	NCB15+U4+N0...
NBN40-U3LK-N0...	NBN40-U4LK-N0...	NCB40-FP-N0-P4...	NCN20+U3+N0...
NCB20-L2-N0...	NCB40-FP-N0-P3...	NCN30+U4+N0...	NCN40+U3+N0...
NCN20+U4+N0...	NCN30+U3+N0...	NCN50-FP-N0-P3...	NCN50-FP-N0-P4...
NCN40+U4+N0...	NCN40-L2-N0...	NJ15-M1-N-V...	NJ20+U3+N...
NJ15+U3+N...	NJ15+U4+N...	NJ20+U4+N...	NJ30P+U3+1N...
NJ30+U3+N...	NJ30P+U4+1N...	NJ30+U4+N...	NJ40+U4+N...
NJ40+U3+N...	NJ50-FP-N-P3...	NJ50-FP-N-P4...	

8.当用作EPL Ga设备时，以下型号的传感器金属含量超过允许值。在需要应用EPL Ga设备的危险区域，应采取适当措施确保不会发生由于撞击或摩擦效应而引起的点火危险。

NBB15-U3K-N0...	NCB15+U3+N0...	NCN50-FP-N0-P3...	NJ40+U3+N...
NBB15-U4K-N0...	NCB15+U4+N0...	NCN50-FP-N0-P4...	NJ40+U4+N...

本页为证书附页，应与证书主页同时使用。



SITIIAS
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书

证书编号：2020322315002302

证书附页：第10页共10页

NBB20-U3K-N0...	NCB40-FP-N0-P3...	NJ15+U3+N...	NJ50-FP-N-P3...
NBB20-U4K-N0...	NCB40-FP-N0-P4...	NJ15+U4+N...	NJ50-FP-N-P4...
NBN30-U3K-N0...	NCN20+U3+N0...	NJ20+U3+N...	
NBN30-U4K-N0...	NCN20+U4+N0...	NJ20+U4+N...	
NBN40-U3K-N0...	NCN30+U3+N0...	NJ30+U3+N...	
NBN40-U3LK-N0...	NCN30+U4+N0...	NJ30+U4+N...	
NBN40-U4K-N0...	NCN40+U3+N0...	NJ30P+U3+1N...	
NBN40-U4LK-N0...	NCN40+U4+N0...	NJ30P+U4+1N...	

本页为证书附页，应与证书主页同时使用。



SITIIAS
Worldwide Access

批准：

上海仪器仪表自控系统检验测试所有限公司