

CERTIFICATE OF CONFORMITY

1. HAZARDOUS LOCATION ELECTRICAL EQUIPMENT PER CANADIAN REQUIREMENTS

2. **Certificate No:** FM19CA0042X
3. **Equipment:** F2D0-MIO-Ex12*, R8D0-MIO-Ex12*
(Type Reference and Name) Fieldbus Multi-Input/Output (MIO)
4. **Name of Listing Company:** Pepperl+Fuchs SE
5. **Address of Listing Company:** Lilienthalstrasse 200, D-68307 Mannheim
Germany

6. The examination and test results are recorded in confidential report number:

PR453265 dated 24th July 2023

7. FM Approvals LLC, certifies that the equipment described has been found to comply with the following Approval standards and other documents:

CSA C22.2 No. 213:2017, CSA C22.2 No. 60079-0:2015, CSA C22.2 No. 60079-7:2016,
CSA C22.2 No. 60079-11:2014, CSA C22.2 No. 60079-31:2015, CSA C22.2 No. 61010-1:2016

8. If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to specific conditions of use specified in the schedule to this certificate.
9. This certificate relates to the design, examination and testing of the products specified herein. The FM Approvals surveillance audit program has further determined that the manufacturing processes and quality control procedures in place are satisfactory to manufacture the product as examined, tested and Approved.

10. **Equipment Ratings:**

See Annex

11. **The marking of the equipment shall include:**

See Annex

12. **Description of Equipment:**

General – The Pepperl + Fuchs Fieldbus IO (*D0-MIO-Ex*) is a field device for use in Profibus PA or Foundation Fieldbus H1 applications. It provides up to twelve channels. Four of them are configurable as in- or outputs.

Certificate issued by:



J.E. Marquedant
VP, Manager - Electrical Systems

2 November 2023

Date

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC, 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Apr 21)



SCHEDULE

Canadian Certificate Of Conformity No: FM19CA0042X



Member of the FM Global Group

They can be used for the connection of intrinsically safe valves or for the connection of binary sensors. The remaining eight inputs can be used for the connection of binary sensors. In addition, the device features an extension interface for the connection of additional accessories providing more channels or advanced functions.

Construction - The device comes either in the F2 aluminum housing for direct field use or with DIN-rail clamps for the mounting in a control cabinet or in an additional field housing. The field enclosure may be equipped with different types of separately certified cable glands.

Ratings – The Fieldbus IO operates at 9-32 VDC and 23mA. The equipment rated for use in an ambient temperature range of -50°C to +75°C or -40°C to +70°C depending on device.

Fieldbus connection (terminals + and –)

Intrinsically safe in level of protection Class I, II, III Div 1, “ia” or “ib”.

Fieldbus circuit according to the FISCO model or with the following maximum values according to the Entity model:

Ui = 24 V

Ii = 380 mA

Ci negligible

Li negligible

Intrinsically safe in level of protection “ic”.

Fieldbus circuit according to the FISCO ic model or with the following maximum values according to the Entity model:

Ui = 35 V

Ii = 380 mA

Ci negligible

Li negligible

Extension interface (terminals R, T and G)

Intrinsically safe in Class I Div 1 and level of protection “ia”.

Uo = 6.4 V

Io = 9.0 mA

Po = 14.0 mW

Ui = 6.4 V

linear characteristic

Ci negligible

Li negligible

Permissible external reactances:

Group	IIC	IIB / IIIC	IIA
Co	28 µF	650 µF	1000 µF
Lo	300 mH	1000 mH	1000 mH

These values are only applicable, if the internal inductance Li or the internal capacitance Ci of the connected equipment is ≤ 1 % of the above specified values.

If Li as well as Ci of the connected equipment are > 1 % of the above specified values, the specified values for Lo and Co shall be reduced to 50 %. The reduced capacitance of the external circuit (capacitance of the cable +

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Apr 21)



Page 2 of 6

SCHEDULE

Canadian Certificate Of Conformity No: FM19CA0042X



Member of the FM Global Group

internal capacitance of the connected equipment) shall not exceed 1 μ F for groups I, IIA, IIB, and IIIC and 600 nF for group IIC.

I/O channels (Terminals CH1 + and -, CH2 + and -, CH3 + and -, CH4 + and -, CH5 + and -, CH6 + and -, CH7 + and -, CH8 + and -, CH9 + and -, CH10 + and -, CH11 + and -, CH12 + and -)
Intrinsically safe in Class I Div 1 and level of protection "ia".

U_o = 9 V

I_o = 43 mA

P_o = 96 mW

Li negligible

Ci negligible

Group	IIC	IIB / IIIC	IIA
Co	4.9 μ F	40 μ F	500 μ F
Lo	20 mH	70 mH	150 mH

With the existence of lumped capacitances and inductances in the intrinsically safe I/O channel circuit, with both values exceeding 1 % of the values given above, the maximum permissible external capacitances and inductances for circuits in Class I Div 1 and level of protection "ia" subject to the gas group have to be taken from the following table:

Group	IIC	IIB / IIIC	IIA
Co	850 nF	790 nF	2.7 μ F
Lo	2 mH	2.5 mH	5 mH

13. Specific Conditions of Use:

See Annex

14. Test and Assessment Procedure and Conditions:

This Certificate has been issued in accordance with FM Approvals Canadian Certification Scheme.

15. Schedule Drawings

A copy of the technical documentation has been kept by FM Approvals.

16. Certificate History

Details of the supplements to this certificate are described below:

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Apr 21)



SCHEDULE

Canadian Certificate Of Conformity No: FM19CA0042X



Member of the FM Global Group

Date	Description
24 July 2023	Original Issue.
2 November 2023	<u>Supplement 1:</u> Report Reference: PR238710 dated 2 November 2023. Description of the Change(s): Correction to control document number

FM Approvals

FM Approvals

FM Approvals

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Apr 21)



SCHEDULE

Canadian Certificate Of Conformity No: FM19CA0042X



ANNEX

F2D0-MIO-Ex12.* Fieldbus IO

Equipment Ratings:

Intrinsically safe connections for Class I, II, III Division 1, Groups A, B, C, D, E, F, and G; Non Incendive for Class I Division 2, Groups A, B, C, D, F, G; Intrinsic Safety for Ex ib [ia Ga] IIC T4 Gb; Increased Safety with Intrinsically Safe connections for Ex ec [ia Ga] IIC T4 Gc; Intrinsic Safety for Ex ic [ia Ga] IIC T4 Gc; Intrinsic Safety connections to Ex [ia Da] IIIC; Dust Ignition Protection by Enclosure for Ex Tb [ia Da] IIIC T130°C hazardous locations with an ambient temperature rating of -40°C to +70°C.

Markings:

Provides Intrinsically Safe Circuits for Class I, II, III Division 1, Groups A, B, C, D, E, F, G
Class I, II, III Division 2, Groups A, B, C, D, F, G; T4

Ex ib [ia Ga] IIC T4 Gc

Ex ec [ia Ga] IIC T4 Gc

Ex ic [ia Ga] IIC T4 Gc

Ex [ia Da] IIIC

Ex tb [ia Da] IIIC T130°C

Ta = -40°C to +70°C

FISCO, Entity

Refer to Control DWG 116-0467 for FISCO and Entity parameters.

Specific Conditions of Use:

1. The enclosure has to be installed in such a way, that electrostatic charging as well as impact and friction hazards are excluded.
2. For Zones Installations, the apparatus may only be installed in areas with pollution degree 2.

R8D0-MIO-Ex12.* Fieldbus IO

Equipment Ratings:

Intrinsically safe connections for Class I, II, III Division 1, Groups A, B, C, D, E, F, and G; Non Incendive for Class I Division 2, Groups A, B, C, and D; Intrinsic Safety for Ex ib [ia Ga] IIC T4 Gb; Increased Safety with Intrinsically Safe connections for Ex ec [ia Ga] IIC T4 Gc; Intrinsic Safety for Ex ic [ia Ga] IIC T4 Gc; Intrinsic Safety connections to Ex [ia Da] IIIC; hazardous locations with an ambient temperature rating of -50°C to +75°C

Markings:

Provides intrinsically safe circuits for Class I, II, III Division 1, Groups A, B, C, D, E, F, G
Class I Division 2, Groups A, B, C, D; T4

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Apr 21)



SCHEDULE

Canadian Certificate Of Conformity No: FM19CA0042X



Member of the FM Global Group

Ex ib [ia Ga] IIC T4 Gb

Ex ec [ia Ga] IIC T4 Gc

Ex ic [ia Ga] IIC T4 Gc

Ex [ia Da] IIIC

Ta = -50°C to +75°C

FISCO, Entity

Refer to Control DWG 116-0467 for FISCO and Entity parameters.

Specific Conditions of Use:

1. The enclosure has to be installed in such a way, that electrostatic charging as well as impact and friction hazards are excluded.
2. For Division installation, the equipment shall be installed in a tool secure enclosure in compliance with the enclosure, mounting, spacing and segregation requirements of the ultimate application.
3. For Zones installations areas requiring Gc-apparatus (type of protection "ec"), the apparatus has to be installed into an enclosure providing at least degree of protection IP54 in accordance with the CAN/CSA-C22.2 No. 60079-0.
4. For Zone Installation, the apparatus may only be installed in areas with pollution degree 2.

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Apr 21)

