

Pepperl+Fuchs GmbH
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-1367A
Date / Datum: 2016-12-07

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs GmbH declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs GmbH erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

Products / Produkte

Product / Produkt	Item number	Description / Beschreibung
NBB15-30GM50-E2-3G-3D	123968	Inductive sensor
NBB15-30GM50-E2-V1-3G-3D	211275	Inductive sensor
NBB15-30GM50-E3-V1-3G-3D	225846	Inductive sensor
NBB2-12GM40-Z0-3G-3D	212671	Inductive sensor
NBB2-12GM60-A2-3G-3D	211261	Inductive sensor
NBB2-8GM40-E2-V1-3G-3D	129853	Inductive sensor
NBB4-12GM50-E2-3G-3D	212060	Inductive sensor
NBB4-12GM50-E2-V1-3G-3D	212426	Inductive sensor
NBB5-18GM40-Z0-3G-3D	183052	Inductive sensor
NBB5-18GM60-A2-V1-3G-3D	212061	Inductive sensor
NBB8-18GM50-E2-3G-3D	123969	Inductive sensor
NBB8-18GM50-E2-3G-3D-5M	180591	Inductive sensor
NBB8-18GM50-E2-V1-3G-3D	129854	Inductive sensor
NBB8-18GM60-A2-V1-3G-3D	212062	Inductive sensor
NCB10-30GM40-Z0-3G-3D	211271	Inductive sensor
NCB10-30GM40-Z0-V1-3G-3D	183050	Inductive sensor
NCB10-30GM40-Z1-3G-3D	211272	Inductive sensor
NCB2-12GM40-E2-3G-3D	211255	Inductive sensor
NCB2-12GM40-E2-3G-3D-5M	211256	Inductive sensor
NCB2-12GM40-Z0-V1-3G-3D	183042	Inductive sensor
NCB5-18GM40-Z0-3G-3D	211265	Inductive sensor
NCB5-18GM40-Z0-3G-3D-10M	211266	Inductive sensor
NCB5-18GM40-Z0-V1-3G-3D	211267	Inductive sensor
NCB5-18GM40-Z1-3G-3D	211268	Inductive sensor
NCN15-30GM40-Z0-3G-3D	211273	Inductive sensor
NCN4-12GM40-E2-3G-3D	211258	Inductive sensor
NCN4-12GM40-E2-V1-3G-3D	211259	Inductive sensor

NCN4-12GM40-Z0-3G-3D	211260	Inductive sensor
NCN8-18GM40-Z0-3G-3D	211269	Inductive sensor
NCN8-18GM50-E2-3G-3D	211262	Inductive sensor
NCN8-18GM50-E2-3G-3D-5M	211263	Inductive sensor
NJ10-30GM50-E2-3G-3D	123962	Inductive sensor
NJ10-30GM50-E2-3G-3D-5M	200108	Inductive sensor
NJ10-30GM50-E2-V1-3G-3D	212670	Inductive sensor
NJ15-30GM50-E2-3G-3D	123961	Inductive sensor
NJ15-30GM50-E2-V1-3G-3D	129851	Inductive sensor
NJ5-18GM50-E2-3G-3D	121899	Inductive sensor
NJ5-18GM50-E2-3G-3D-5M	202692	Inductive sensor
NJ5-18GM50-E2-V1-3G-3D	129845	Inductive sensor

Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
ATEX 2014/34/EU (L96/309-356)	EN 60079-0/A11:2013-11 EN 60079-0:2012-08 EN 60079-15:2010-05 EN 60079-31:2014-07
EMC 2014/30/EU (L96/79-106)	EN 60947-5-2/A1:2012-11 EN 60947-5-2:2007-12

Affixed CE Marking / Angebrachte CE-Kennzeichnung



Signatures / Unterschriften



Mannheim, 2016-12-07

ppa. Reiner Müller
President
Division Factory Automation

ppa. Wolfgang Helm
Director
Business Unit Sensors

■ ANNEX ATEX

Marking and Certificates / *Kennzeichnung und Zertifikate*

Marking <i>Kennzeichnung</i>	Certificate <i>Zertifikat</i>	Issuer ID <i>Aussteller ID</i>
 II 3 G	PF15CERT3754X	PF
 II 3 D	PF15CERT3774X	PF

Key for Issuer ID / *Schlüssel zur Aussteller ID*

ID	Issuer / <i>Aussteller</i>
PF	Pepperl+Fuchs Lilienthalstrasse 200 68307 Mannheim Germany

■ Special conditions for the installation in zone 2 and zone 22 / *Besondere Bedingungen für den Einsatz in Zone 2 und Zone 22*

The special conditions for use of the device in zone 2 and zone 22 according to the datasheet and instruction manual, available under <http://www.pepperl-fuchs.com> must be considered.

Die besonderen Bedingungen für den Einsatz des Betriebsmittels in Zone 2 und Zone 22 laut Datenblatt und Betriebsanleitung, verfügbar unter <http://www.pepperl-fuchs.com> müssen beachtet werden.