

# EU-Declaration of conformity

en/de

## EU-Konformitätserklärung

Pepperl+Fuchs GmbH  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-3066B  
Date / Datum: 2017-10-19

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



RoHS 2011/65/EU (L174/88-110)	EN 50581:2012-09
----------------------------------	------------------

### Affixed CE Marking / Angebrachte CE-Kennzeichnung



### Signatures / Unterschriften

Mannheim, 2017-10-19

ppa. Wolfgang Helm  
Director  
Business Unit Sensors

i.V. Ulrich Ehrenfried  
Head of Innovation Unit  
Electromagnetic Sensors

### Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs GmbH declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs GmbH erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

### Products / Produkte

Product / Produkt	Item number	Description / Beschreibung
NBB10-30GM50-WS-V93	801697	Inductive sensor
NBB15-30GM50-WO-V93	801698	Inductive sensor
NBB15-30GM50-WS-V93	801699	Inductive sensor
NBB10-30GM50-WS-10M	802852	Inductive sensor
NBB15-30GM50-WS-5M	802853	Inductive sensor
NBB15-30GM50-WS-10M	806441	Inductive sensor
NBB10-30GM50-WS-V11	802850	Inductive sensor
NBB15-30GM50-WS-V11	802851	Inductive sensor
NBB10-30GM50-WO-5M	308796	Inductive sensor
NBB10-30GM50-WO-10M	199640	Inductive sensor
NBB10-30GM50-WO	801647	Inductive sensor
NBB10-30GM50-WS	801648	Inductive sensor
NBB15-30GM50-WO	801649	Inductive sensor
NBB15-30GM50-WS	801650	Inductive sensor
NBB10-30GM50-WO-V12	801692	Inductive sensor
NBB10-30GM50-WS-V12	801693	Inductive sensor
NBB15-30GM50-WO-V12	801694	Inductive sensor
NBB15-30GM50-WS-V12	801695	Inductive sensor
NBB10-30GM50-WO-V93	801696	Inductive sensor

### Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
EMC 2014/30/EU (L96/79-106)	EN 60947-5-2/A1:2012-11 EN 60947-5-2:2007-12
LVD 2014/35/EU (L96/357-374)	EN 60947-5-2/A1:2012-11 EN 60947-5-2:2007-12