

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.:DOC-4984D
Date / Datum: 2025-11-03

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

 PEPPERL+FUCHS

Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

Product Family / Produktfamilie

Product Family / Produktfamilie	Item number / Artikelnr.	Description / Beschreibung
RM-320P-NX-XXXX-D-XXXXXXXX-NN0	70124565-*	Panel mount Thin Client
PC-320P-NX-XXXX-D-XXXXXXXX-NN0		Panel mount PC
DM-320P-NX-XXXX-D-XXXXXXXX-NN0		Panel mount Direct Monitor

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2014/30/EU (EMC) (L96/79-106)	EN 61000-6-4:2007+A1:2011 EN 55035:2017/A11:2020 EN 55011:2016+A1:2017
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12
(EU) 2023/1542 (L191/1-84)	EN IEC 63000:2018-12



Signatures / Unterschriften

Mannheim, 2025-11-03


i.V. Rolf Wessels
Executive Vice President
Business Unit Enterprise Mobility


i.V. Fabian Reukauf
Product Portfolio Manager HMI
Business Unit HMI

■ ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

XX-XXXX-XX-XXXX-X-XXXXXXXX-NN0			
Variable	Feature	Option	Description
XX-XXXX-	Technology	RM-320P-	Remote Monitor Panel
		PC-320P-	Panel PC
		DM-320P-	Direct Monitor Panel
X	Certification	N	Industrial, non-ex general purpose
X-	Operating Temperature	A-	0 ... 45 °C
		B-	-20 ... 55 °C
XXXX-	Display	22GT-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch
		22KT-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch
		22FC-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
		19SC-	19" (5:4), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
		15FC-	15,6" (16:9), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
X-	Power Supply	D-	24 V DC (+/- 20%)
XX	Computing Platform	1N	Intel Celeron 3965U
		2N	Intel Core i5-7300U
		VN	Direct Monitor unit
X	RAM	N	none (<i>only Technology "Direct Monitor"</i>)
		A	4 GB
		B	8 GB
		C	16 GB
		D	32 GB
		K	4 GB (<i>only Operating Temperature "B"</i>)
		L	8 GB (<i>only Operating Temperature "B"</i>)
		M	16 GB (<i>only Operating Temperature "B"</i>)
		P	32 GB (<i>only Operating Temperature "B"</i>)
X	Storage	N	none (<i>only Technology "Direct Monitor"</i>)
		A	32 GB
		B	64 GB
		D	256 GB
		E	512 GB
		K	32 GB (<i>only Operating Temperature "B"</i>)
		L	64 GB (<i>only Operating Temperature "B"</i>)
		P	256 GB (<i>only Operating Temperature "B"</i>)
		Q	512 GB (<i>only Operating Temperature "B"</i>)
X	Software	N	none (<i>only Technology "Direct Monitor"</i>)
		I	IGEL OS 11 (unlicensed)
		J	IGEL OS 12 (unlicensed)
		3	Windows 10 IoT Enterprise 2021 LTSC
		4	P+F RM Shell 6
		X	<i>Other software options</i>
XX-	Mounting	S1-	Panel mounting w/ stainless steel bezel (SS304)
		S2-	Panel mounting w/ stainless steel bezel (SS316L)
NN0	Options	NN0	Standard