EU-Declaration of conformity

EU-Konformitätserklärung

en/de

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / *Nr.*:DOC-5008D
Date / *Datum*: 2025-11-03

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

PEPPERL+FUCHS

Declaration of conformity / *Konformitätserklärung*

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

Product Family / *Produktfamilie*

Product Family / *Produktfamilie*	**Item number /** *Artikelnr.*	**Description /** *Beschreibung*
BPC3200-NX-XXXX-D-XXXXXXX-NN0	70124565-*	Industrial Box PC

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / *Richtlinien und Normen*

EU-Directive *EU-Richtlinie*	**Standards** *Normen*
2014/30/EU (EMC) (L96/79-106)	EN 61000-6-4:2007+A1:2011 EN 55035:2017/A11:2020 EN 55011:2016+A1:2017
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12
(EU) 2023/1542 (L191/1-84)	EN IEC 63000:2018-12

Affixed CE Marking / *Angebrachte CE-Kennzeichnung*

CE

Signatures / *Unterschriften*

Mannheim, 2025-11-03

i.V. Roolf Wessels
Executive Vice President
Business Unit Enterprise Mobility

i.V. Fabian Reukauf
Product Portfolio Manager HMI
Business Unit HMI

ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:
Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

XX-XXXX-XX-XXXX-X-XXXXXXX-NN0			
Variable	**Feature**	**Option**	**Description**
XX-XXXX-	Technology	BPC3200-	Industrial Box PC
N	Certification	N	Industrial, non-ex general purpose
X-	Operating Temperature	A-NNNN-	0 … 45 °C
		B-NNNN-	-20 … 55 °C
X-	Power Supply	D-	24 V DC (+/- 20%)
XX	Computing Platform	1N	Intel Celeron 3965U
		2N	Intel Core i5-7300U
		VN	Direct Monitor unit
X	RAM	A	4 GB
		B	8 GB
		C	16 GB
		D	32 GB
		K	4 GB *(only Operating Temperature “B-NNNN-”)*
		L	8 GB *(only Operating Temperature “B-NNNN-”)*
		M	16 GB *(only Operating Temperature “B-NNNN-”)*
		P	32 GB *(only Operating Temperature “B-NNNN-”)*
X	Storage	A	32 GB
		B	64 GB
		D	256 GB
		E	512 GB
		L	64 GB *(only Operating Temperature “B-NNNN-”)*
		K	32 GB *(only Operating Temperature “B-NNNN-”)*
		P	256 GB *(only Operating Temperature “B-NNNN-”)*
		Q	512 GB *(only Operating Temperature “B-NNNN-”)*
X	Software	INN-	IGEL OS 11 (unlicensed)
		JNN-	IGEL OS 12 (unlicensed)
		1NN-	Windows 10 IoT Enterprise 2019 LTSC
		2NN-	P+F RM Shell 5
		3NN-	Windows 10 IoT Enterprise 2021 LTSC
		4NN-	P+F RM Shell 6
		XNN-	*Other software options*
NN0	Options	NN0	Standard