




EU Type Examination Certificate CML 20ATEX3156X Issue 0

- 1 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU
- 2 Equipment SR Terminal Box
- 3 Manufacturer Pepperl+Fuchs SE
- 4 Address Lilienthalstrasse 200
68307 Mannheim
Germany
- 5 The equipment is specified in the description of this certificate and the documents to which it refers.
- 6 CML B.V., Chamber of Commerce No 6738671, Hoogoorddreef 15, Amsterdam, 1101 BA, The Netherlands, Notified Body Number 2776, in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in the confidential reports listed in Section 12.
- 7 If an 'X' suffix appears after the certificate number, it indicates that the equipment is subject to conditions of safe use (affecting correct installation or safe use). These are specified in Section 14.
- 8 This EU Type Examination certificate relates only to the design and construction of the specified equipment or component. Further requirements of Directive 2014/34/EU Article 13 apply to the manufacture of the equipment or component and are separately certified.
- 9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the confidential report, has been demonstrated through compliance with the following documents:

EN IEC 60079-0:2018 EN IEC 60079-7:2015/A1:2018 EN 60079-11:2012
EN 60079-28:2015 EN 60079-31:2014

- 10 The equipment shall be marked with the following:



Ex eb IIC T* Gb


Ex ia IIC T* Gb

Ex op pr IIC T* Gb

*T6/T80°C Ta = -60°C to +40°C

*T5/T95°C Ta = -60°C to +55°C

*T4/T130°C Ta = -60°C to +90°C



Ex tb IIIC T* Db

Other values possible according to the limitations within the schedule drawings.



CML 20ATEX3156X
Issue 0

11 Description

The SR Terminal Box is a range of increased safety fabricated steel enclosures with a base and mechanically fixed cover with optional hinges. The range utilises the Ex Component certified Pepperl+Fuchs SR enclosures covered under certificate numbers IECEx CML 20.0076U and CML 20ATEX3118U.

The SR Terminal Box is populated with DIN rail mounted, increased safety Ex component certified terminals, their number and orientation being subject to pre-determined limitations. The SR Terminal Box may also be used for connecting intrinsically safe circuits.

In addition, the SR Terminal Box may be fitted with an Ex component certified fibre optic splice tray(s).

For cable entry, the terminal boxes may be provided with clearance holes, as required, in the top, bottom, left, right or back faces, or alternatively via glandplates. An internal/external earth stud may be provided.

The enclosures are available in a range of standard sizes as shown in Table 1 below, intermediate sizes are also permitted.

Design Options

Enclosure type	H (mm)	W (mm)	D (mm)
LRS / SRS.10.11.09	96	110	85.5
LRS / SRS.14.11.09	136	110	85.5
LRS / SRS.18.11.09	176	110	85.5
LRS / SRS.22.11.09	216	110	85.5
SRS.15.15.09	150	150	90
SRS.15.19.09	150	190	90
SRS.19.19.10	190	190	100
SRM.26.26.09	260	260	87
SRM.26.26.16	260	260	160
SRM.26.26.22	260	260	220
SRM.23.30.16	230	300	160
SRM.19.38.16	190	380	160
SRM.31.31.09	310	310	87
SRM.31.31.16	310	310	160
SRM.31.31.22	310	310	220
SRM.38.38.16	380	380	160
SRM.38.38.22	380	380	220
SRM.38.48.09	380	480	87
SRM.38.48.16	380	480	160
SRM.38.48.22	380	480	220
SRL.48.48.16	480	480	160
SRL.48.48.22	480	480	220
SRL.40.60.22	400	600	220



**CML 20ATEX3156X
Issue 0**

Enclosure type	H (mm)	W (mm)	D (mm)
SRL.38.76.16	380	760	160
SRL.48.76.16	480	760	160
SRL.48.76.22	480	760	220
SRL.60.60.26	600	600	260
SRX.90.60.30	900	600	300
SRX.80.80.30	800	800	300
SRX.100.80.30	1000	800	300
SRX.130.80.30	1300	800	300
SRX.120.120.30	1200	1200	300

Table 1

Maximum Dissipated Power for T6/T5/T4 Ta = 40°C/55°C/90°C

Enclosure type	Ta(°C)	Power (W)		
		T6/T80°C	T5/T95°C	T4/T130°C
LRS / SRS.10.11.09	40	5.5	8.7	11.8
LRS / SRS.10.11.09	55	-	5.5	11.8
LRS / SRS.10.11.09	90	-	-	5.5
LRS / SRS.14.11.09	40	6.4	10.1	13.7
LRS / SRS.14.11.09	55	-	6.4	13.7
LRS / SRS.14.11.09	90	-	-	6.4
LRS / SRS.18.11.09	40	7.3	11.5	15.6
LRS / SRS.18.11.09	55	-	7.3	15.6
LRS / SRS.18.11.09	90	-	-	7.3
LRS / SRS.22.11.09	40	8.2	12.9	17.5
LRS / SRS.22.11.09	55	-	8.2	17.5
LRS / SRS.22.11.09	90	-	-	8.2
SRS.15.15.09	40	7.7	12.1	16.5
SRS.15.15.09	55	-	7.7	16.5
SRS.15.15.09	90	-	-	7.7
SRS.15.19.09	40	8.6	13.6	18.4
SRS.15.19.09	55	-	8.6	18.4
SRS.15.19.09	90	-	-	8.6
SRS.19.19.10	40	10.2	16.1	21.8
SRS.19.19.10	55	-	10.2	21.8
SRS.19.19.10	90	-	-	10.2
SRM.26.26.09	40	14.4	22.7	30.7
SRM.26.26.09	55	-	14.4	30.7
SRM.26.26.09	90	-	-	14.4
SRM.26.26.16	40	17.7	27.8	37.8
SRM.26.26.16	55	-	17.7	37.8
SRM.26.26.16	90	-	-	17.7
SRM.26.26.22	40	20.4	32.1	43.5



CML 20ATEX3156X
Issue 0

Enclosure type	Power (W)			
	Ta(°C)	T6/T80°C	T5/T95°C	T4/T130°C
SRM.26.26.22	55	-	20.4	43.5
SRM.26.26.22	90	-	-	20.4
SRM.23.30.16	40	17.7	27.8	37.8
SRM.23.30.16	55	-	17.7	37.8
SRM.23.30.16	90	-	-	17.7
SRM.19.38.16	40	18	28.3	38.4
SRM.19.38.16	55	-	18	38.4
SRM.19.38.16	90	-	-	18
SRM.31.31.09	40	12.1	23.9	35.5
SRM.31.31.09	55	-	12.1	35.5
SRM.31.31.09	90	-	-	12.1
SRM.31.31.16	40	15.6	30.8	45.8
SRM.31.31.16	55	-	15.6	45.8
SRM.31.31.16	90	-	-	15.6
SRM.31.31.22	40	18.5	36.5	54.3
SRM.31.31.22	55	-	18.5	54.3
SRM.31.31.22	90	-	-	18.5
SRM.38.38.16	40	22.3	44	65.4
SRM.38.38.16	55	-	22.3	65.4
SRM.38.38.16	90	-	-	22.3
SRM.38.38.22	40	25.8	50.9	75.6
SRM.38.38.22	55	-	25.8	75.6
SRM.38.38.22	90	-	-	25.8
SRM.38.48.09	40	22.4	44.2	65.7
SRM.38.48.09	55	-	22.4	65.7
SRM.38.48.09	90	-	-	22.4
SRM.38.48.16	40	27.1	53.4	79.5
SRM.38.48.16	55	-	27.1	79.5
SRM.38.48.16	90	-	-	27.1
SRM.38.48.22	40	30.9	60.9	90.6
SRM.38.48.22	55	-	30.9	90.6
SRM.38.48.22	90	-	-	30.9
SRL.48.48.16	40	33.6	66.2	98.5
SRL.48.48.16	55	-	33.6	98.5
SRL.48.48.16	90	-	-	33.6
SRL.48.48.22	40	38.1	75.1	111.7
SRL.48.48.22	55	-	38.1	111.7
SRL.48.48.22	90	-	-	38.1
SRL.40.60.22	40	38.6	76.1	113.1
SRL.40.60.22	55	-	38.6	113.1
SRL.40.60.22	90	-	-	38.6



CML 20ATEX3156X
Issue 0

Enclosure type	Power (W)			
	Ta(°C)	T6/T80°C	T5/T95°C	T4/T130°C
SRL.38.76.16	40	40.3	79.4	118.1
SRL.38.76.16	55	-	40.3	118.1
SRL.38.76.16	90	-	-	40.3
SRL.48.76.16	40	49.8	98.2	146
SRL.48.76.16	55	-	49.8	146
SRL.48.76.16	90	-	-	49.8
SRL.48.76.22	40	55.1	108.6	161.5
SRL.48.76.22	55	-	55.1	161.5
SRL.48.76.22	90	-	-	55.1
SRL.60.60.26	40	59.2	116.7	173.5
SRL.60.60.26	55	-	59.2	173.5
SRL.60.60.26	90	-	-	59.2
SRX.90.60.30	40	90.6	178.5	265.5
SRX.90.60.30	55	-	90.6	265.5
SRX.90.60.30	90	-	-	90.6
SRX.80.80.30	40	100.9	198.8	295.7
SRX.80.80.30	55	-	100.9	295.7
SRX.80.80.30	90	-	-	100.9
SRX.100.80.30	40	123.5	243.3	361.9
SRX.100.80.30	55	-	123.5	361.9
SRX.100.80.30	90	-	-	123.5
SRX.130.80.30	40	157.5	310.3	461.5
SRX.130.80.30	55	-	157.5	461.5
SRX.130.80.30	90	-	-	157.5
SRX.120.120.30	40	201.7	397.4	591
SRX.120.120.30	55	-	201.7	591
SRX.120.120.30	90	-	-	201.7

Table 2

12 Certificate history and evaluation reports

Issue	Date	Associated report	Notes
0	06 Jul 2021	R13369A/00	Issue of prime certificate

Note: Drawings that describe the equipment or component are listed in the Annex.

13 Conditions of Manufacture

The following conditions are required of the manufacturing process for compliance with the certification.



CML 20ATEX3156X
Issue 0

- i. Where the product incorporates certified parts or safety critical components the manufacturer shall ensure that any changes to those parts or components do not affect the compliance of the certified product that is the subject of this certificate.
- ii. The manufacture shall ensure that all restrictions or Schedules of Limitations of component certified parts are adhered to.
- iii. The SR Range of Terminal Boxes are to be designed in accordance with general electrical safety standards e.g., IEC 61439.



**CML 20ATEX3156X
Issue 0**

14 Specific Conditions of Use (Special Conditions)

The following conditions relate to safe installation and/or use of the equipment.

- i. The torque applied to the cover securing fasteners shall be at least 3 Nm.
- ii. When fitted with the fibre optic splice tray, the fibre cables shall be sufficiently supported to prevent strain and their minimum bend radius shall be observed with all unused fibre connectors having dust covers fitted.

Certificate Annex

Certificate Number CML 210ATEX3156X
Equipment SR Terminal Box
Manufacturer Pepperl+Fuchs SE



The following documents describe the equipment or component defined in this certificate:

Issue 0

Drawing No.	Sheets	Rev.	Approved date	Title
161533CM-04	1 to 7	-	02 Jul 2021	SR Terminal Box General Assembly
161533CM-10	1 to 2	-	02 Jul 2021	SR Terminal Box Type Code