

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-5345
Date: 2021-08-30

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

■ Productfamily

| Productfamily | Description |
|---------------|------------------------|
| O...-R3-... | Thru beam sensor |
| O...-R3-... | Retroreflective sensor |
| O...-R3-... | Background suppression |

The „...“ marked parts of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

■ Regulations and Standards

| UK Regulation | Standards |
|----------------------------|--------------------------|
| UK SI 2016 No. 1091 (EMC) | EN IEC 60947-5-2:2020-03 |
| UK SI 2012 No. 3032 (RoHS) | EN IEC 63000:2018-12 |

■ Affixed UKCA Marking



■ Signatures

Mannheim, 2021-08-30

ppa. Hinrik Weber
Factory Automation –
Director Business Unit Opto

i.V. Dr. Lutz Lohmann
Factory Automation –
Manager Development Opto KOS

■ ANNEX TYPE CODE

The "...“ marked parts of the type code are placeholders and can be replaced by the following code:

Die mit „...“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

| Nomenclature | | | | | | | | | | |
|------------------|---------------------------------------|-----------------------------------------------------|---|-----------------------|---|------------------------------|---|----------------------------------------|---|---------------------------|
| Sensor principle | Sensor category and optical principle | Sensing range | | Mechanical properties | | Electrical process interface | | Mechanical process interface, optional | | Special options, optional |
| I | II | III | - | IV | - | V | - | VI | - | VII |
| O | BE BR BT | Sensing range (mm) plus optional letter designating | - | R3 | - | any | - | V3 V31 0,2MV3 0,2MV31 | - | 1T |