

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6619  
Date: 2022-07-15

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### Product Family

Product Family	Description
Vuvwww-F400-Bxx-Ayyyy-zzzz	Vision 3-D sensor

The „u,v,w,x,y,z“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN 55011:2016-04 EN 61000-6-2/AC:2005-09 EN 61000-6-2:2005-08 EN 61000-6-4/A1:2011-02 EN 61000-6-4:2007-01

### Affixed UKCA Marking



### Signatures

Mannheim, 2022-07-15

i.V. Hilmar Hofmann

RnD Manager Business Unit Industrial  
Vision Components

i.V. Armin Hornberger

Head of Global Product Management  
Business Unit Industrial Vision  
Components

## ■ ANNEX TYPE CODE

The „u,v,w,x,y,z“ marked letters of the type code are placeholders and can be replaced by the following code:

<b>Vuvwww-F400-Bxx-Ayyy-zzzz</b>						
<b>u = Technology</b>	<b>v = Type</b>	<b>w = Working Distance</b>	<b>F400</b>	<b>x = Interface</b>	<b>y = Option</b>	<b>z = Customer specific</b>
S – Stereo Vision T – Time of Flight	E - Explorer	1000 mm 7500 mm	Metal Housing	B12 – Ethernet TCP/IP	A1000 – CMOS Chip, 850nm A1500 – CMOS Chip, 950nm	