

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-6633
Date: 2022-07-15

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

■ Product Family

Product Family	Description
OPCwww-xxxx-yyy-zzzz	2D Code Reader

The „w,x,y,z“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

■ Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN 55011:2016-04 EN 61000-6-4/A1:2011-02 EN 61000-6-4:2007-01 EN 61326-1:2013-01

■ Affixed UKCA Marking



■ Signatures

Mannheim, 2022-07-15

i.V. Hilmar Hofmann
RnD Manager Business Unit Industrial
Vision Components

i.V. Dr. Tim Weis
Product Manager Business Unit Industrial
Vision Components

■ ANNEX TYPE CODE

The „w,x,y,z“ marked letters of the type code are placeholders and can be replaced by the following code:

OPCwww-xxx-yy-zzzz			
w = Working Distance	x = Housing	x = Interface	z = Customer specific
70 mm 120 mm	F200 – Plastic housing with 50 mm depth F201 – Plastic housing with 54 mm depth	R2 – RS232, Ethernet TCP/IP B17 – Profinet, Ethernet TCP/IP	