

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.:	<b>ANZEx 21.2003X</b>	Current Issue:	0	Date of Issue:	2022-03-02
------------------	-----------------------	----------------	---	----------------	------------

**Applicant:** **Pepperl+Fuchs SE**  
Lilienthalstrasse 200  
68307 Mannheim  
GERMANY

**Equipment:** Smart Transmitter Isolator Type KFD2-STC(V)5-Ex1...


**Type of Explosion Protection:** Intrinsic Safety "i"

**Explosion Protection Marking:** [Ex ia Ma] I  
Tamb: -20 °C to +70 °C

*This certificate is granted subject to the requirements as set out in  
Joint Accreditation System of Australia and New Zealand Publications  
ANZEx System Rules 2020 & ANZEx Certified Equipment Scheme Rules 2021*

Signed for and on behalf of issuing body

Name & Position

  
.....  
Geoff Barnier  
Principal Engineer - Certification  
.....

*This certificate is not transferable and remains the property of the issuing body.*

*The status of this certificate can be confirmed through the database located at [www.anzex.com.au](http://www.anzex.com.au)*

Certificate issued by:

Safety in Mines, Testing and Research Station  
2 Robert Smith Street, REDBANK QLD 4301

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.:	<b>ANZEx 21.2003X</b>	Current Issue:	0	Date of Issue:	2022-03-02
------------------	-----------------------	----------------	---	----------------	------------

**Manufacturer :** **Pepperl+Fuchs SE**  
Lilienthalstrasse 200  
68307 Mannheim  
GERMANY

**Additional Manufacturing Location(s):** **Pepperl+Fuchs Asia Pte. Ltd.**  
18 Ayer Rajah Crescent  
Singapore 139942  
SINGAPORE

### STANDARDS:

*The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards:*

**IEC 60079-0:2017 Ed 7.0** Explosive atmospheres - Part 0: Equipment—General requirements

**IEC 60079-11:2011 Ed 6.0** Explosive atmospheres - Part 11: Equipment protection by intrinsic safety "i"

*This Certificate does not indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.*

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: **ANZEx 21.2003X**

Current Issue: 0

Date of Issue: 2022-03-02

### Schedule

#### Equipment Description:

The Smart Transmitter Isolator Type KFD2-STC(V)5-Ex1... are Intrinsically Safe Associated Apparatus Transmitter Power Supplies that transfer monitoring signals from a hazardous area to a safe area and communication signals in both directions. The Safe Area connections are the Power Supply and Output. The Hazardous Area Connections (Input Circuit) are for Sink Input, Source Input or Three Wire Input.

#### Electrical Ratings/Parameters

SAFE Area Connections: KFD2-STC(V)5-Ex1:

Power Supply	
Connection(s):	Terminals 14, 15 and Power Rail 1,2
Operating Supply Voltage:	18 Vdc to 30 Vdc
Maximum Voltage (Um):	250 Vac
Maximum Power::	
- KFD2-STC5-Ex1	≤ 1.6 W

Output	
Connection(s):	Terminals 7, 8, 9
Maximum Voltage (Um):	250 Vac

#### Sink transmitter input connection - KFD2-STC(V)5-Ex1:

Hazardous Area Connections, Input Circuits:

Sink transmitter input connection	
Connection(s):	Terminals 1, 3
Uo	26.2 V
Uq	27.25 V
Io	93 mA
Po	634 mW
Ci	5 nF
Li	0

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel must not exceed the following values:

Group	Co ( $\mu$ F)	Lo (mH)	Lo/Ro ( $\mu$ H/ $\Omega$ )
I	4.415	53.95	737.9

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: **ANZEx 21.2003X**      Current Issue: 0      Date of Issue: 2022-03-02

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value, or
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo, and
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1 uF.

**Source transmitter input connection - KFD2-STC(V)5-Ex1:**

Hazardous Area Connections, Input Circuits:

Source transmitter input connection	
Connection(s):	Terminals 3, 2
Uo	2.0 V
Io	8.5 mA
Po	4.3 mW
Ui	30 V
Ii	115 mA
Pi	1000 mW
Ci	0
Li	0
Connection(s):	3 +ve wrt 2
Uo	2.0 V
Io	8.5 mA
Po	4.3 mW
Connection(s):	2 +ve wrt 3
Uo	1.0 V
Io	4.3 mA
Po	1.1 mW
Li	0

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel must not exceed the following values:

Group	Co (µF)	Lo (mH)	Lo/Ro (µH/Ω)
I	1000	6459	109803

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value or
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: <b>ANZEx 21.2003X</b>	Current Issue: 0	Date of Issue: 2022-03-02
--	------------------	---------------------------

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo and
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F.

**Three wire transmitter input connection - KFD2-STC(V)5-Ex1:**

Hazardous Area Connections, Input Circuits:

Three wire transmitter input connection	
Connection(s):	Terminals 1, 2, 3
Uo	26.2 V
Uq	27.25 V
Io	115 mA
Po	784 mW
Ci	5 nF
Li	0

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel must not exceed the following values:

Group	Co ( $\mu$ F)	Lo (mH)	Lo/Ro ( $\mu$ H/ $\Omega$ )
I	4.415	35.27	595.6

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value, or
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo, and
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F.

**Sink transmitter input connection - KFD2-STC(V)5-Ex1.H:**

Hazardous Area Connections, Input Circuits:

Sink transmitter input connection	
Connection(s):	Terminals 1, 3
Uo	27.2 V
Io	93 mA
Po	633 mW
Ci	5 nF
Li	0

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: <b>ANZEx 21.2003X</b>	Current Issue: 0	Date of Issue: 2022-03-02
--	------------------	---------------------------

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel must not exceed the following values:

Group	Co ( $\mu$ F)	Lo (mH)	Lo/Ro ( $\mu$ H/ $\Omega$ )
I	4.045	53.95	737.9

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value, or
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo, and
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F.

**Source transmitter input connection - KFD2-STC(V)5-Ex1.H:**

Hazardous Area Connections, Input Circuits:

Source transmitter input connection	
Connection(s):	Terminals 3, 2
Uo	2.0 V
Io	8.5mA
Po	4.3mW
Ui	30V
Ii	115mA
Pi	1000mW
Ci	0
Li	0
Connection:	3 +ve wrt 2
Uo	2.0 V
Io	8.5mA
Po	4.3mW
Connection:	2 +ve wrt 3
Uo	1.0V
Io	4.3mA
Po	1.1mW

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel must not exceed the following values:

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: <b>ANZEx 21.2003X</b>	Current Issue: 0	Date of Issue: 2022-03-02
--	------------------	---------------------------

Group	Co ( $\mu$ F)	Lo (mH)	Lo/Ro ( $\mu$ H/ $\Omega$ )
I	1000	6459	109803

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value or
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo and
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F.

**Three wire transmitter input connection - KFD2-STC(V)5-Ex1.H:**

Hazardous Area Connections, Input Circuits:

Three wire transmitter input connection	
Connection(s):	Terminals 1, 2, 3
Uo	27.2 V
Io	115mA
Po	782mW
Ci	5nF
Li	0

The capacitance and either the inductance or the inductance to resistance ratio (L/R) of the load connected to the output terminals of either channel must not exceed the following values:

Group	Co ( $\mu$ F)	Lo (mH)	Lo/Ro ( $\mu$ H/ $\Omega$ )
I	4.045	35.27	596.7

The entity parameters apply when one of the two conditions below is given:

- The total Li of the external circuit (excluding the cable) is < 1% of the Lo value, or
- The total Ci of the external circuit (excluding the cable) is < 1% of the Co value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total Li of the external circuit (excluding the cable) > 1% of the Lo, and
- The total Ci of the external circuit (excluding the cable) > 1% of the Co.

Note: the reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F.

# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: **ANZEx 21.2003X**

Current Issue: 0

Date of Issue: 2022-03-02

**Specific Conditions of Use:**

1. The entity parameters shall be observed.
2. The equipment shall be installed in an enclosure that provides a degree of protection not less than IP54 in accordance requirements of IEC 60079-0 unless the equipment is intended to be afforded an equivalent degree of protection by location. In addition, the pollution level shall be limited to pollution degree 2 or better as defined in IEC 60664-1 (Pollution degree 2 can be achieved when the installation is in a controlled environment with suitably controlled condensation or airborne pollution).

For some types of enclosure, additional certification will be required to permit the installation of the module within the enclosure. Reference should be made to the enclosure certificate. The installer shall ensure that the maximum ambient temperature of the module when installed is not exceeded.

**Conditions of Certification:**

1. All transformers shall be subjected to IEC 60079-11 Clause 11.2 Routine Tests for Infallible Transformers with an applied voltage of 1 500 V applied between the input and output windings.

**Additional Information:**

None



# Certificate of Conformity

## Ex EQUIPMENT

Certificate No.: **ANZEx 21.2003X**      Current Issue: 0      Date of Issue: 2022-03-02

### Register of Issues and Variations

includes the current issue

#### Issue 0 dated 2022-03-02

#### Model Description

Model: Smart Transmitter Isolator Type KFD2-STC(V)5-Ex1...

Where: KFD2-ST = Smart Transmitter Isolator

C = Current source/sink

(V) = Voltage

5-Ex1 = Single hazardous area input/Single non-hazardous area output.

-1 = 5 Volt – used with “V”

-2 = 10 Volt – used with “V”

.H = Higher field voltage

.NCL = No current limit

-Y1...n = Customised version - does not affect intrinsic safety

-... = Customised version - combination of numbers/letters does not affect intrinsic safety

#### Test & Assessment Reports relevant for this issue:

TR No. & Issuing CBs: GB/CML/ExTR17.0036/00, GB/CML/ExTR18.0077/00, GB/CML/ExTR20.0237/00, GB/CML/ExTR21.0098/00; CML

QAR No. & Issuing CB: DE/PTB/QAR06.0008/16; PTB

File Reference: 210002 Cert

#### Manufacturer's Documents/Drawings associated with this issue:

Document Number	Pages / Sheets	Document Title	Revision	Date
<b>GB/CML/ExTR17.0036/00</b>				
16-1135CM-01	1 to 4	Schematics KFD2-STC(V)5-Ex1...	-	2017-Jan-09
16-1135CM-02	1 to 22	Safety Relevant Components KFD2-STC(V)5- Ex1...	-	2017-Feb-27
16-1135UL-02	1 to 57	Relevant Component List for Div.2/ Zone 2 KFD2-STC(V)5-Ex1...	-	2016-Dec-13
16-1135CM-03	1 of 1	Component Layout KFD2-STC(V)5-Ex1...	-	2017-Jan-20
16-1135CM-04	1 to 10	Mechanical Parts KF-Extended-Housing 15 term. Asymm	-	2016-Sep-06
16-1135CM-05	1 to 4	PCB Layout KFD2-STC(V)5-Ex1...	-	2017-Jan-24
16-1135CM-06	1 to 6	Transformers KFD2-STC(V)5-Ex1...	-	2016-Oct-19
16-1135CM-09	1 to 3	Instructions KFD2-STC(V)5-Ex1...	-	2017-Mar-10
<b>GB/CML/ExTR18.0077/00</b>				
16-1135CM-05A	1 to 8	PCB Layout – Top KFD2-STC(V)5-Ex1...	-	2017-Dec-06

# Certificate of Conformity

## Ex EQUIPMENT

<i>Certificate No.:</i> <b>ANZEx 21.2003X</b>		<i>Current Issue:</i> 0	<i>Date of Issue:</i> 2022-03-02	
Document Number	Pages / Sheets	Document Title	Revision	Date
<b>Labels</b>				
16-1135SI-10	1	Type Label (ANZEx) KFD2-STC(V)5-Ex1..	-	2022-Feb-15

*Note: There are no Manufacturer's Documents/Drawings associated with GB/CML/ExTR20.0237/00.*