

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6825  
Date: 2022-11-18

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### Product family

Product	Description
V1S-a-b-c	M12 male A-coded 4-pin field attachable connector

The "a", "b" and "c" marked letters of the type code are placeholders and can be replaced by the code described in AN-NEX TYPE CODE.

### Regulations and Standards

UK Regulation	Standards
UK SI 2016 No. 1011 (LV)	EN 60204-1:2018 EN 60529:1991 EN 60529:1991/A1:2000 EN 60529:1991/A2:2013
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018

Supplemental Standards	Remarks
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking

### Affixed UKCA Marking



### Signatures

Mannheim, 2022-11-18

i.V. Sebastian Stöber  
Vice President Business Unit Systems

i.V. Simon Wagner  
Product Manager

### ANNEX TYPE CODE

The "a", "b" and "c" marked letters of the type code are placeholders and can be replaced by the following code:

V1S-a-b-c	
V1S	Connector type
a	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut
b	ABG = Shielded; BK = Black; DUO = Two cable; Q2 = Cross section 0,34-0,75mm <sup>2</sup> ; Q3 = Cross section 0,14-0,34mm <sup>2</sup> ; PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter; SC = Spring clamp
c	PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter