



Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-7598
Date: 2024-03-27

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Signatures

Mannheim, 2024-03-27

i.v. R. Wessels

i.v. J. Hartleb

i.V. Rolf Wessels
Executive Vice President Business
Unit MCC+HMI

i.V. Jörg Hartleb
COO ECOM Instruments GmbH

ANNEX UK SI 2016 No. 1107 (EX)

Approved Body QM System:

Eurofins E&E CML Limited (2503)
Newport Business Park - New Port Road
CH65 4LZ Ellesmere Port
United Kingdom

Marking and Certificates

Marking	Certificate	ID
II 2 D II 2 G	EPS 23 UKEX 1 095 X	8507

Key for ID

ID	Responsible Body
8507	Bureau Veritas Consumer Products Services UK Ltd 31 Kingsland Grange WA1 4RW Woolston Warrington United Kingdom

ANNEX RED

Certificates

Products	ELWMS
Certificate	ID
EMA23RE0144	0891

Key for ID

ID	Responsible Body
0891	Element Materials Technology Unit 1, Pendle Place, Skelmersdale, West Lancashire WN8 9PN, UK

ANNEX TYPE LETTER CODE

The [X] marked letters of the type code are placeholders and can be replaced by the following code:

SMART-EX03-DZ1-[x1][x2][x3][x4][x5]			
Variable	Feature	Option	Description
x1	Region / Country	[AI-] [AIC] [xxx-]	Europe Europe / North America Country specific variant acc. to Alpha-3 code (ISO alpha-3)
x2	Camera	[C] [N]	With Camera Without Camera
x3	Storage	[128]	128 GB
X4	Customization	[000-]	Ecom Standard
X5	Version	[..] [NC] [HM]	Standard No charger HART-Modem (Viator)-KIT

Declaration of Conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the products listed below are in conformity with the below listed UK Regulations (as amended) and standards.

Productfamily

Productfamily	Description
Smart-Ex 03 ROW DZ1 [x1][x2][x3][x4][x5]	Smartphone

The [X] marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	BS EN IEC 63000:2018-12
UK SI 2016 No. 1107 (EX)	EN 60079-11:2012-01 EN IEC 60079-0:2018-07
UK SI 2017 No. 1206 (RE)	BS EN 50360:2017-10 BS EN 50566:2017-10 BS EN 50663:2017-11 BS EN 55032:2015+A11:2020-00 BS EN 55032:2015-07 BS EN 55035:2017+A11:2020-00 BS EN 55035:2017-11 BS EN 61000-3-3:2013+A2:2021-00 BS EN 62479:2010-12 BS EN IEC 61000-3-2:2019+A1:2021-00 BS EN IEC 62311:2020-02 BS EN IEC 62368-1:2020+A11:2020-00 BS EN IEC/IEEE 62209-1528:2021-00 EN 300328 V 2.2.2:2019-07 EN 300330 V 2.1.1:2017-02 EN 300687 V 1.2.1:2001-07 FINAL Draft ETSI EN 3010908-25 V15.1.1 EN 301440 V 1.2.2:1999-01 EN 301489-1 V 2.2.3:2019-11 EN 301489-17 V 3.2.4:2020-09 EN 301489-19 V 2.2.1:2022-09 EN 301489-3 V 2.3.2:2023-01 EN 301489-52 V 1.2.1:2021-11 EN 301511 V 12.5.1:2017-03 EN 301893 V 2.1.1:2017-05 EN 301908-1 V 15.2.1:2023-01 EN 301908-13 V 13.2.1:2022-02 EN 303413 V 1.2.1:2021-04