



■ Signatures / Unterschriften

Mannheim, 2018-07-18

i.V. Roolf Wessels
Business Unit Director

i.V. Nils Bleshoy
Norm Expert of the Product Group

■ ANNEX ATEX

Marking and Certificates / Kennzeichnung und Zertifikate

| Products / Produkte | VisuNet IND-8200 Series | |
|--------------------------|---------------------------|----------------------------|
| Marking Kennzeichnung | Certificate Zertifikat | Issuer ID Aussteller ID |
| II 3 G | DEMKO12ATEX1107369X | DEMKO |

Key for Issuer ID / Schlüssel zur Aussteller ID

| ID | Issuer / Aussteller |
|-------|--|
| DEMKO | UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark |

Pepperl+Fuchs GmbH
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-B021E
Date / Datum: 2018-07-18

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs GmbH declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs GmbH erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

■ Productfamily / Produktfamilie

| Productfamily / Produktfamilie | Description / Beschreibung |
|--------------------------------|---|
| VisuNet IND-8200 Series | Direct -, Remote-, KVM Monitor and Panel PC |

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

■ Directives and Standards / Richtlinien und Normen

| EU-Directive EU-Richtlinie | Standards Normen |
|------------------------------------|--|
| 2014/30/EU (EMC) (L96/79-106) | EN 61326-1:2013 |
| 2014/34/EU (ATEX) (L96/309-356) | EN 60079-0:2012/A11:2013 EN 60079-15:2010 |
| 2011/65/EU (RoHS) (L174/88-110) | EN 50581:2012 |

ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

| XXXXXX-X-XX-XX-XX-XXX-X-XX-XX-XX-XX-X | | | | |
|---------------------------------------|---------------------|---|---|---------|
| Variable | Description | Option | Description / Designation | |
| XXXX | Family | DM82 RM82 KM82 PC82 | Direct Monitor Family Remote Monitor Family KVM Monitor Family Panel PC Family | |
| XX | Screen Size | 15 19 21 22 | 15.0", XGA (1024 x 768 pixel) 19.0", SXGA (1280 x 1024 pixel) 21.5", Full HD (1920 x 1080 pixel) 22.0", WSXGA (1680 x 1050 pixel) | |
| X | Screen Type | A R T U F K | Antiglare glass front, non-touch Touch Screen, Resistive, 5-wire, hardened Glass (15", 19", 21.5" only) Touch Screen, Resistive, 5-wire High Bright Display with Touch Screen, Resistive, 5-wire (15", 19", 21.5" only) High Bright Display with antiglare front, non-touch (15", 19", 21.5" only) High Bright Display with Touch Screen, Resistive, 5-wire, hardened glass (15", 19", 21.5" only) | |
| XX | Protection | V3 | ATEX Zone 2 | |
| XX | Board Specification | V2 | Video VGA | Only DM |
| | | T3 | Thin Client, ATOM 1.6 GHz, 1 GB RAM, 2GB Flash, RM shell (W7 based) | Only RM |
| | | T4 | Thin Client, ATOM 1.6 GHz, 2 GB RAM, 8GB Flash, W7 Embedded | Only RM |
| | | TC | Thin Client, ATOM 1.6 GHz, 2GB RAM, Thin Manager Compliant | Only RM |
| | | T51 | Thin Client, ATOM Dual Core E3826, 4 GB RAM, 16GB CFAST, RM shell (W7 based) | Only RM |
| | | T52 | Thin Client, ATOM Dual Core E3826, 4 GB RAM, 16GB CFAST, W7 Embedded | Only RM |
| | | T61 | Thin Client, ATOM Dual Core E3826, 4 GB RAM, 32GB CFAST, RM Shell 5 (W10 IOT based) | Only RM |
| | | K3 | KVM for VGA Video included, 2x PS/2, 1x RS232, analogue CATx cable transmission, ROSE | Only KM |
| | | K4 | KVM for DVI-D Video included, 2 x USB, 1 x RS232, CATx cable transmission, ROSE | Only KM |
| | | K5 | KVM for DVI-D Video included, 2 x USB, 1 x RS232, F.O. transmission , 2x LC connectors, ROSE | Only KM |
| | | PDX | i7 Dual Core processor, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC |
| | | PEX | i7 Dual Core processor, 8 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC |
| | | PFX | ATOM Dual Core E3826, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC |
| | | PGX | ATOM Dual Core E3826, 8 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC |
| | | PHX | ATOM Dual Core E3826, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC |
| | | PIX | ATOM Dual Core E3826, 8 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC |
| | PJX | i7-7600U, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC | |
| | PKx | i7-7600U, / GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package) | Only PC | |
| XX | Power Supply | DC | 24V DC | |
| XXX | Housing Version | CL5 | Panel mount, stainless steel | |
| | | CP5 | Panel mount, black painted steel | |
| | | CP6 | 19" Rack mount, black painted steel, Only 19" display | |
| X | Keyboard Housing | N | No Keyboard & Mouse housing | |
| XX | Keyboard / Mouse | K0 | No Keyboard, no Mouse | |
| XX | Keyboard Layout | L0 | No Keyboard, no Layout | |
| XX | Special Accessories | S0 | No Special Accessories | |
| X | Options | N | No Option | |