

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Br.: **DOC-5857**
Date / Datum: **2023-05-16**

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity / Deklaracija o sukladnosti

We Pepperl+Fuchs SE declare under our sole responsibility that the products listed below are in conformity with the listed European Directives and standards.

Mi, Pepperl+Fuchs SE, izjavljujemo pod vlastitom i isključivom odgovornošću da su proizvodi u nastavku sukladni navedenim europskim direktivama i standardima.

Products / Proizvodi

Products Proizvodi	Itemnumber Broj stavke	Description Opis
FS-LBAS-IA1	70146555	Ethernet-APL Surge Protector
FN-LBAS-IA1	70146514	Ethernet-APL Surge Protector

Directives and Standards / Direktive i standardi

EU-Directive EU direktiva	Standards Standardi
ATEX 2014/34/EU (L96/309-356)	EN 60079-18:2015-04 EN 60079-18/AC:2018-09 EN IEC 60079-0:2018-07 EN 60079-1:2014-10 EN IEC 60079-7/A1:2018-01 EN 60079-7:2015-12 EN 60079-11:2012-01
RoHS 2011/65/EU (L174/88-110)	EN IEC 63000:2018-12
Supplemental Standards	IEC/TS 60079-47:2021-02

Affixed CE Marking / Dodijeljena CE oznaka



Signatures / Potpisi

Mannheim, 2023-05-16

ppa. Michael Kessler

Executive Vice President
Components & Technology

i.V. Gunther Rogoll

Manager - Product Group Fieldbus
Technology

The English version represents the signed original.

Verzija na engleskom jeziku predstavlja potpisani originalni dokument.

ANNEX ATEX / ANEKS ATEX

Notified Body QM-System / Prijavljeno tijelo QM-System

Physikalisch Technische Bundesanstalt (0102)
Bundesallee 100
38116 Braunschweig
Germany

Marking and Certificates / Označavanje i certifikati

Marking Označavanje	Certificate Certifikat	Issuer ID ID izdavača
⊕ I M2 ⊕ I M2 (M1) ⊕ II 2 (1) D ⊕ II 2 (1) G ⊕ II 2 G	TÜV 22 ATEX 8786 X	0035

Key for Issuer ID / Šifra za ID izdavača

ID	Issuer Izdavač
0035	TÜV Rheinland Industrial Services GmbH Automation and Functional Safety (AFS) Am Grauen Stein 51105 Cologne Germany