

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-6199
Date: 2022-08-15

Signatures
Mannheim, 2022-08-15

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



L.V. U. Ehrenfried

i.V. Ulrich Ehrenfried
Head of Innovation Unit
Electromagnetic Sensors

i.V. T. Schieck

i.V. Thorsten Schieck
Product Manager
Electromagnetic Sensors

Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

Products

Product	Item number	Description
NJ4-N-H31 L1=60MM L2=4M	302328-0024	Inductive sensor
NJ4-N-H31 L1=60MM L2=6M	302328-0025	Inductive sensor
Prod.Fam. NJ4-N-H31...	302328	Inductive sensor
NJ4-N-H31 L1=100MM L2=1M	302328-0039	Inductive sensor
NJ4-N-H31 L1=100MM L2=2M	302328-0040	Inductive sensor
NJ4-N-H31 L1=100MM L2=6M	302328-0043	Inductive sensor
NJ4-N-H31 L1=40MM L2=0,5M	302328-0001	Inductive sensor
NJ4-N-H31 L1=50MM L2=1M	302328-0012	Inductive sensor
NJ4-N-H31 L1=50MM L2=10M	302328-0018	Inductive sensor
NJ4-N-H31 L1=50MM L2=2M	302328-0013	Inductive sensor
NJ4-N-H31 L1=50MM L2=3M	302328-0014	Inductive sensor
NJ4-N-H31 L1=50MM L2=8M	302328-0017	Inductive sensor
NJ4-N-H31 L1=60MM L2=10M	302328-0027	Inductive sensor

Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN 60947-5-6:2000-01 EN IEC 60947-5-2:2020-03

Affixed UKCA Marking

