

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No.: DOC-6461B
Date: 2023-04-21

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the products listed below are in conformity with the listed UK Regulations as indicated below and amended by UK SI 2019 No. 696, and standards.

Products

Products	Itemnumber	Description
NBB15-30GM50-E2-3G-3D	70126049	Inductive sensor
NBB2-12GM60-A2-3G-3D	70126031	Inductive sensor
NBB15-30GM50-E2-V1-3G-3D	70126050	Inductive sensor
NBB2-12GM40-Z0-3G-3D	70126030	Inductive sensor
NBB15-30GM50-E3-V1-3G-3D	70126051	Inductive sensor
NBB10-30GS50-Z4L-V1-3G-3D	70134926-0010	Inductive sensor
NBB4-12GM50-E2-3G-3D	70126032	Inductive sensor
NBB4-12GM50-E2-V1-3G-3D	70126033	Inductive sensor
NBB8-18GM60-A2-V1-3G-3D	70126040	Inductive sensor
NBN15-30GS50-Z4L-V1-3G-3D	70134926-0012	Inductive sensor
NBB8-18GM50-E2-3G-3D	70126037	Inductive sensor
NBB8-18GM50-E2-3G-3D-5M	70126038	Inductive sensor
NBB8-18GM50-E2-V1-3G-3D	70126039	Inductive sensor
NCB2-12GM40-E2-3G-3D	70126070	Inductive sensor
NCB2-12GM40-E2-3G-3D-5M	70126071	Inductive sensor
NCB2-12GM40-Z0-V1-3G-3D	70126034	Inductive sensor
NCB5-18GM40-Z0-3G-3D	70126041	Inductive sensor
NCB5-18GM40-Z0-3G-3D-10M	70126042	Inductive sensor

Products	Itemnumber	Description
NCB5-18GM40-Z0-3G-3D-10M-Y	70126043	Inductive sensor
NCB5-18GM40-Z0-V1-3G-3D	70126044	Inductive sensor
NCB5-18GM40-Z1-3G-3D	70126045	Inductive sensor
NCB10-30GM40-Z0-3G-3D	70126052	Inductive sensor
NCB10-30GM40-Z0-V1-3G-3D	70126053	Inductive sensor
NCN8-18GM40-Z0-3G-3D	70126046	Inductive sensor
NCB10-30GM40-Z1-3G-3D	70126054	Inductive sensor
NCN8-18GM50-E2-3G-3D	70126047	Inductive sensor
NCN8-18GM50-E2-3G-3D-5M	70126048	Inductive sensor
NCN4-12GM40-E2-3G-3D	70126072	Inductive sensor
NCN4-12GM40-E2-V1-3G-3D	70126073	Inductive sensor
NCN4-12GM40-Z0-3G-3D	70126035	Inductive sensor
NCN15-30GM40-Z0-3G-3D	70126055	Inductive sensor
NJ10-30GM50-E2-3G-3D	70126077	Inductive sensor
NJ10-30GM50-E2-3G-3D-5M	70126078	Inductive sensor
NJ10-30GM50-E2-V1-3G-3D	70126079	Inductive sensor
NJ15-30GM50-E2-3G-3D	70126080	Inductive sensor
NJ15-30GM50-E2-V1-3G-3D	70126081	Inductive sensor
NJ5-18GM50-E2-3G-3D	70126074	Inductive sensor
NJ5-18GM50-E2-3G-3D-5M	70126075	Inductive sensor
NJ5-18GM50-E2-V1-3G-3D	70126076	Inductive sensor

Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN IEC 60947-5-2:2020-03
UK SI 2016 No. 1107 (EX)	EN 60079-31:2014-07 EN IEC 60079-0:2018-07 EN IEC 60079-7/A1:2018-01 EN 60079-7:2015-12

Affixed UKCA Marking




■ Signatures

Mannheim, 2023-04-21



i.V. Ulrich Ehrenfried
Head of Innovation Unit
Electromagnetic Sensors



i.V. Mark Guenther
Global Product Manager

■ ANNEX UK SI 2016 No. 1107 (EX)

Marking and Certificates

Marking	Certificate	ID
⊕ II 3 G	TÜV 20 ATEX 8523 X	TUR
⊕ II 3 D	TÜV 20 ATEX 8524 X	TUR

Key for ID

ID	Responsible Body
TUR	TÜV Rheinland Industrial Services GmbH Automation and Functional Safety (AFS) Am Grauen Stein 51105 Cologne Germany