

## ■ Signatures


Mannheim, 2022-09-22

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6462A  
Date: 2022-09-22



i.V. Ulrich Ehrenfried  
Head of Innovation Unit  
Electromagnetic Sensors



i.V. Mark Guenther  
Global Product Manager

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



## ■ ANNEX UK SI 2016 No. 1107 (EX)



## ■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

## ■ Products

| Product                  | Item number   | Description      |
|--------------------------|---------------|------------------|
| NBB10-30GS50-Z4L-3G-3D   | 70134926-0009 | Inductive sensor |
| NBB2-12GS40-Z4L-V1-3G-3D | 70134926-0002 | Inductive sensor |
| NBB2-12GS40-Z4L-3G-3D    | 70134926-0001 | Inductive sensor |
| NBB5-18GS50-Z4L-V1-3G-3D | 70134926-0006 | Inductive sensor |
| NBB5-18GS50-Z4L-3G-3D    | 70134926-0005 | Inductive sensor |
| NBN15-30GS50-Z4L-3G-3D   | 70134926-0011 | Inductive sensor |
| NBN4-12GS40-Z4L-V1-3G-3D | 70134926-0004 | Inductive sensor |
| NBN4-12GS40-Z4L-3G-3D    | 70134926-0003 | Inductive sensor |
| NBN8-18GS50-Z4L-V1-3G-3D | 70134926-0008 | Inductive sensor |
| NBN8-18GS50-Z4L-3G-3D    | 70134926-0007 | Inductive sensor |

## ■ Marking and Certificates

| Marking  | Certificate        | ID  |
|--|--------------------|-----|
|  II 3 G | TÜV 20 ATEX 8523 X | TUR |
|  II 3 D | TÜV 20 ATEX 8524 X | TUR |

## ■ Key for ID

| ID  | Responsible Body   |
|-----|--|
| TUR | TÜV Rheinland Industrial Services GmbH Automation and Functional Safety (AFS)<br>Am Grauen Stein<br>51105 Cologne<br>Germany |

## ■ Regulations and Standards

| UK Regulation              | Standards  |
|----------------------------|--|
| UK SI 2012 No. 3032 (RoHS) | EN IEC 63000:2018-12   |
| UK SI 2016 No. 1091 (EMC)  | EN IEC 60947-5-2:2020-03   |
| UK SI 2016 No. 1107 (EX)   | EN 60079-31:2014-07<br>EN 60079-7:2015-12<br>EN IEC 60079-0:2018-07<br>EN IEC 60079-7/A1:2018-01 |

## ■ Affixed UKCA Marking

