

## Pin-Out Table

Termination Board field side			Modules		Termination Board control side	
Module	Channel	IS terminals M1 ... M4	IS terminals SL2 field side	Non-IS terminals SL1 control side	System connector X1	Signal name
1	1	1	5a	8a	37	CH1+
		4	5b	7a	19	CH1-
	2	2	1a	10a	36	CH2+
		5	1b	9a	18	CH2-
	3	3	3a	9b	35	CH3+
		6	3b	10b	17	CH3-
	4	7	7a	8b	34	CH4+
		8	7b	7b	16	CH4-
2	5	1	5a	8a	33	CH5+
		4	5b	7a	15	CH5-
	6	2	1a	10a	32	CH6+
		5	1b	9a	14	CH6-
	7	3	3a	9b	31	CH7+
		6	3b	10b	13	CH7-
	8	7	7a	8b	30	CH8+
		8	7b	7b	12	CH8-
3	9	1	5a	8a	29	CH9+
		4	5b	7a	11	CH9-
	10	2	1a	10a	28	CH10+
		5	1b	9a	10	CH10-
	11	3	3a	9b	27	CH11+
		6	3b	10b	9	CH11-
	12	7	7a	8b	26	CH12+
		8	7b	7b	8	CH12-
4	13	1	5a	8a	25	CH13+
		4	5b	7a	7	CH13-
	14	2	1a	10a	24	CH14+
		5	1b	9a	6	CH14-
	15	3	3a	9b	23	CH15+
		6	3b	10b	5	CH15-
	16	7	7a	8b	22	CH16+
		8	7b	7b	4	CH16-
					1	V <sub>cc</sub>
					20	GND

## Pin-Out Table


Termination Board field side			Modules		Termination Board control side	
Module	Channel	IS terminals M5 ... M8	IS terminals SL2 field side	Non-IS terminals SL1 control side	System connector X2	Signal name
5	17	1	5a	8a	37	CH17+
		4	5b	7a	19	CH17-
	18	2	1a	10a	36	CH18+
		5	1b	9a	18	CH18-
	19	3	3a	9b	35	CH19+
		6	3b	10b	17	CH19-
	20	7	7a	8b	34	CH20+
		8	7b	7b	16	CH20-
6	21	1	5a	8a	33	CH21+
		4	5b	7a	15	CH21-
	22	2	1a	10a	32	CH22+
		5	1b	9a	14	CH22-
	23	3	3a	9b	31	CH23+
		6	3b	10b	13	CH23-
	24	7	7a	8b	30	CH24+
		8	7b	7b	12	CH24-
7	25	1	5a	8a	29	CH25+
		4	5b	7a	11	CH25-
	26	2	1a	10a	28	CH26+
		5	1b	9a	10	CH26-
	27	3	3a	9b	27	CH27+
		6	3b	10b	9	CH27-
	28	7	7a	8b	26	CH28+
		8	7b	7b	8	CH28-
8	29	1	5a	8a	25	CH29+
		4	5b	7a	7	CH29-
	30	2	1a	10a	24	CH30+
		5	1b	9a	6	CH30-
	31	3	3a	9b	23	CH31+
		6	3b	10b	5	CH31-
	32	7	7a	8b	22	CH32+
		8	7b	7b	4	CH32-
					1	V <sub>cc</sub>
					20	GND

## Pin-Out Table

Terminal pin-out	Connector	Pin	Channel	
HART Signal	HART1	1, 2	CH1+, CH1-	
		3, 4	CH2+, CH2-	
		5, 6	CH3+, CH3-	
		7, 8	CH4+, CH4-	
		9, 10	CH5+, CH5-	
		11, 12	CH6+, CH6-	
		13, 14	CH7+, CH7-	
		15, 16	CH8+, CH8-	
		17, 18	CH9+, CH9-	
		19, 20	CH10+, CH10-	
		21, 22	CH11+, CH11-	
		23, 24	CH12+, CH12-	
		25, 26	CH13+, CH13-	
		27, 28	CH14+, CH14-	
		29, 30	CH15+, CH15-	
		31, 32	CH16+, CH16-	
	HART2		1, 2	CH17+, CH17-
			3, 4	CH18+, CH18-
			5, 6	CH19+, CH19-
			7, 8	CH20+, CH20-
			9, 10	CH21+, CH21-
			11, 12	CH22+, CH22-
			13, 14	CH23+, CH23-
			15, 16	CH24+, CH24-
			17, 18	CH25+, CH25-
			19, 20	CH26+, CH26-
			21, 22	CH27+, CH27-
			23, 24	CH28+, CH28-
			25, 26	CH29+, CH29-
			27, 28	CH30+, CH30-
			29, 30	CH31+, CH31-
			31, 32	CH32+, CH32-

Terminal pin-out	Connector	Pin	Signal name
Power supply	X20	6	Supply I -
		5	Supply I +
	X20	4	Supply II -
		3	Supply II +
Fault	X20	1, 2	Fault

Module pin-out (SL1): module 1 ... 8	
V <sub>cc</sub>	2a (+)
	2b (+)
GND	1a (-)
	1b (-)
Fault	6b

 The loop drawing has to be observed. For information see corresponding data sheet on [www.pepperl-fuchs.com](http://www.pepperl-fuchs.com).

03/2014

TDOCT-3622\_ENG 256888

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
[www.pepperl-fuchs.com](http://www.pepperl-fuchs.com)USA: +1 330 486 0002  
[pa-info@us.pepperl-fuchs.com](mailto:pa-info@us.pepperl-fuchs.com)Germany: +49 621 776 2222  
[pa-info@de.pepperl-fuchs.com](mailto:pa-info@de.pepperl-fuchs.com)Singapore: +65 6779 9091  
[pa-info@sg.pepperl-fuchs.com](mailto:pa-info@sg.pepperl-fuchs.com)