



Mannheim, 2017-03-21

Pepperl+Fuchs GmbH
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-2835A
Date / Datum: 2017-03-21

i.V. Ulrich Ehrenfried
Manager Innovation Unit
Electromagnetic Sensors

i.V. Thorsten Schieck
Product Manager

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs GmbH declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs GmbH erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

■ Products / Produkte

| Product / Produkt | Item number | Description / Beschreibung |
|-------------------|-------------|----------------------------|
| NBB20-U1-E1-M | 217916 | Inductive sensor |
| NBB20-U1-E2-M | 217917 | Inductive sensor |
| NBB20-U1-E3-M | 217918 | Inductive sensor |
| NBN40-U1-E0-M | 217919 | Inductive sensor |
| NBN40-U1-E1-M | 217920 | Inductive sensor |
| NBN40-U1-E2-M | 217921 | Inductive sensor |
| NBN40-U1-E3-M | 217922 | Inductive sensor |
| NBB15-U4-A2-M | 915546 | Inductive sensor |
| NBB15-U1-A2-M | 232312 | Inductive sensor |
| NBN30-U1-A2-M | 232313 | Inductive sensor |
| NBB20-U4-A0-M | 241938 | Inductive sensor |
| NBB15-U1-A0-M | 232310 | Inductive sensor |
| NBN30-U1-A0-M | 232311 | Inductive sensor |
| NBB20-U1-A0-M | 207745 | Inductive sensor |
| NBN40-U1-A0-M | 207746 | Inductive sensor |
| NBB20-U1-A2-M | 207747 | Inductive sensor |
| NBN40-U1-A2-M | 207748 | Inductive sensor |
| NBB20-U1-E0-M | 217915 | Inductive sensor |

■ Directives and Standards / Richtlinien und Normen

| EU-Directive EU-Richtlinie | Standards Normen |
|----------------------------------|-------------------------------------------------|
| EMC 2014/30/EU (L96/79-106) | EN 60947-5-2/A1:2012-11 EN 60947-5-2:2007-12 |
| RoHS 2011/65/EU (L174/88-110) | EN 50581:2012-09 |