EU-Declaration of conformity

en/de

EU-Konformitätserklärung

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / *Nr.*: DOC-3629K
Date / *Datum*: 2026-03-23

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

PEPPERL+FUCHS

Declaration of conformity / *Konformitätserklärung*

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

Productfamily / *Produktfamilie*

Productfamily / *Produktfamilie*	**Item number** / Artikelnr.	**Description** / *Beschreibung*
RM-GXP1100-XXXXX-X-XXXXX-XX-X	307487-*	VisuNet GXP RM Operator Workstation for use in Zone 1/21
PC-GXP1100-XXXXX-X-XXXXX-XX-X	307487-*	VisuNet GXP PC Operator Workstation for use in Zone 1/21

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / *Richtlinien und Normen*

EU-Directive *EU-Richtlinie*	**Standards** *Normen*
2014/30/EU (EMC) (L96/79-106)	EN 61000-6-4:2007-01 EN 61000-6-4/A1:2011-02 EN 61326-1:2013-01 EN IEC 61326-1:2021-06 (industrial location) *Non Bluetooth / non RFID products only*
2014/34/EU (ATEX) (L96/309-356)	EN IEC 60079-0:2018-07 EN 60079-5:2015-06 EN 60079-7:2015-12 EN IEC 60079-7/A1:2018-01 EN 60079-11:2012-05 EN 60079-31:2014-12
2014/53/EU (RED) (L153/62-106)	EN 61326-1:2013 EN 300 328 V2.2.2:2019 EN 301 489-1 V2.2.0:2017 EN 301 489-17 V3.2.0:2017 EN 18031-1:2024-08 *Bluetooth products only* EN 61326-1:2013 EN 301489-1 V2.2.3:2019 EN 301489-3 V2.3.2:2023 EN 300 330 V2.1.1:2017 EN 61010-1:2010
	EN 62479 :2010 EN 62311:2008 EN 18031-1:2024-08 *RFID products only*
2011/65/EU (RoHS) (L174/88–110)	EN IEC 63000:2018-12
(EU) 2023/1542 (L191/1–84)	EN IEC 63000:2018-12

Supplemental Standards *Sonstige Normen*	**Remarks** *Bemerkungen*
EN 61010-1:2010	Standards according to Low Voltage Directive

Affixed CE Marking / *Angebrachte CE-Kennzeichnung*

CE 2829

Signatures / *Unterschriften*

Mannheim, 2026-03-23

i.V. Roolf Wessels
Executive Vice President
ECOM+HMI

i.V. Manuel Toth
Technical Product Manager
Innovation Unit HMI

ANNEX ATEX

Notified Body QM-System / *Notifizierte Stelle des QM-Systems*:
Fiditas d.o.o. (2829)
Ulica Slavka Tomerlina 44
10361 Zagreb-Sesvete
Croatia

Marking and Certificates / *Kennzeichnung und Zertifikate*

Products / *Produkte*	**RM-GXP1100-XXXXX-X-XXXXX-XX-X PC-GXP1100-XXXXX-X-XXXXX-XX-X**	
Marking *Kennzeichnung*	Certificate *Zertifikat*	Issuer ID *Aussteller* ID
Ex II 2 G Ex II 2 D	BVS 17 ATEX E 036 X	0158

Key for Issuer ID / *Schlüssel zur Aussteller ID*

ID	**Issuer / *Aussteller***
0158	DEKRA Testing and Certification GmbH, Handwerkstr. 15, 70565 Stuttgart Germany

ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:
Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

RM-GXP1100-XXXXX-X-XXXXX-XX-X PC-GXP1100-XXXXX-X-XXXXX-XX-X			
Variable	**Feature**	**Option**	**Description**
RM-GXP1100-	Model	RM-GXP1100-	VisuNet GXP Remote Monitor for IECEx & ATEX II 2 GD
PC-GXP1100-		PC-GXP1100-	VisuNet GXP PC for IECEx & ATEX II 2 GD
XXXXX-	Display	*XXXXX-*	*Display unit variants of product family DPU1100-J1-**
X-	Power supply	D-	24 V DC Power supply option PSU1100-J1-DC-N0
		A-	115/230 V AC Power supply option PSU1100-J1-AC-N0
XXXXX-	Computing unit	*XXXXX-*	*Computing unit variants of product family TCU1100-J1* / PCU1100-J1**
XX-	Housing	NN-	No housing/bezel; prepared for flush-mount
		H1-	Built into standard system enclosure AG-XX00
		H2-	Built into standard system enclosure AG1
		H3-	Built into standard system enclosure AG1 (Basic-Line pedestal)
		H4-	Built into standard system enclosure AG-XX00 (hinged version)
		P4-	Built into standard system enclosure AG-XX00 (hinged version, pharma)
		S1-	Bezel; prepared for panel mounting and/or into Housing AG-XX00
		S2-	Bezel; prepared for panel mounting and/or into Housing AG1
XX	Options	N0	Standard
		B0	Custom Shell 6
		XX	*Other options without impact on explosion protection*