

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-3933C
Date / Datum: 2026-03-06

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives, Regulations and standards**.

*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien, Verordnungen und Normen** entsprechen.*

Productfamily / Produktfamilie

Productfamily / Produktfamilie	Description / Beschreibung
MNI40N-*****6*N-*****	Magnetic Incremental Encoder

The „ * “ marked letters of the type code are placeholders and replaced by the code described in ANNEX TYPE CODE.
*Die mit „ * “ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.*

Directives and Standards / Richtlinien und Normen

EU-Directive <i>EU-Richtlinie</i>	Standards <i>Normen</i>
EMC 2014/30/EU (L96/79-106)	EN 61000-6-2:2005-08 EN 61000-6-2/AC:2005-09 EN 61000-6-4:2007-01 EN 61000-6-4/A1:2011-02
RoHS 2011/65/EU (L174/88-110)	EN IEC 63000:2018-12
Supplemental Standards	EN IEC 61000-6-2:2019-02 EN IEC 61000-6-4:2019-09

Affixed CE Marking / Angebrachte CE-Kennzeichnung



Signatures / Unterschriften

Mannheim, 2025-03-06



i.V. Stefan Horvatic
Head of Innovation Unit Motion & Condition
Sensors



i.V. Christian Güntert
Head of Product Management
Innovation Unit Motion & Condition
Sensors

ANNEX TYPE CODE

The „*“ marked letters of the type code are placeholders and replaced by the following code:
Die mit „*“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

Produkt Familie Product Family	Gehäuse-material Housing material		Bohrung des Polrades Bore hole of magnetic wheel	Eigenschaften des Polrades Magnetic wheel specifications	Anschluss-art Connection type	Signal-ausgang Signal Output	Ausgangs-schaltung Output type	Option Option		Impulszahl Pulse count
MNI40	N	-	**	**	**	6	*	N	-	*****
			0S, 0A, 0B, 0T, 2B, 0F, 0G, 0H, 0I, 0K	01, A1, E1, D1,	B1, K2	6	1, 6	N	-	00050, 00064, 00100, 00128, 00200, 00360, 00500, 00512, 00800, 01000, 01024, 01250, 01600, 01800, 02048, 02400, 02500, 03072, 03200, 03600, 05000, 07200 10000