

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-4666A
Date / Datum: 2021-10-25

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

Product family / Produktfamilie

Product / Produkt	Description / Beschreibung
V15-a-b-c-d	M12 female A-coded 5-pin field attachable connector

The "a", "b", "c" and "d" marked letters of the type code are placeholders and can be replaced by the code described in AN-NEX TYPE CODE.

Die mit "a", "b", "c" und "d" markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12

Supplemental Standards Sonstige Normen	Remarks Bemerkungen
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking

Affixed CE Marking / Angebrachte CE-Kennzeichnung



Signatures / Unterschriften

Mannheim, 2021-10-25

i.V. Sebastian Stöber

i.V. Sebastian Stöber
Director Business Unit SYSTEMS

i.V. Simon Wagner

i.V. Simon Wagner
Product Manager

ANNEX TYPE CODE

The "a", "b", "c" and "d" marked letters of the type code are placeholders and can be replaced by the following code:

Die mit "a", "b", "c" und "d" markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

V15-a-b-c-d	
V15	Connector type
a	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut
b	ABG = Shielded; PG7 = 4-6mm sheath diameter; PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter
c	PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter
d	blank = Standard; Y followed by any number = Special version