



Mannheim, 2021-09-06

i.V. R. Wessels

i.V. Roolf Wessels
Executive Vice President
Business Unit MCC+HMI

i.V. Dr. Marc Seißler

i.V. Dr. Marc Seißler
Head of Product Management HMI
Business Unit MCC+HMIPepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000No. / Nr.: DOC-4984A
Date / Datum: 2021-09-06Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

■ Product Family / Produktfamilie

Product Family / Produktfamilie	Item number / Artikelnr.	Description / Beschreibung
RM-320P-NX-XXXX-D-XXXXXXXX-NN0	70124565-*	Panel mount Thin Client
PC-320P-NX-XXXX-D-XXXXXXXX-NN0		Panel mount PC
DM-320P-NX-XXXX-D-XXXXXXXX-NN0		Panel mount Direct Monitor

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

■ Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2014/30/EU (EMC) (L96/79-106)	EN 61000-6-4:2007+A1:2011 EN 55035:2017/A11:2020 EN 55011:2016+A1:2017
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12

■ ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

XX-XXXX-XX-XXXX-X-XXXXXXXX-NN0			
Variable	Feature	Option	Description
XX-XXXX-	Technology	RM-320P-	Remote Monitor Panel
		PC-320P-	Panel PC
		DM-320P-	Direct Monitor Panel
X	Certification	N	Industrial, non-ex general purpose
X-	Operating Temperature	A-	0 ... 45 °C
		B-	-20 ... 55 °C
XXXX-	Display	22GT-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch
		22FC-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
		19SC-	19" (5:4), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
		15FC-	15,6" (16:9), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
X-	Power Supply	D-	24 V DC (+/- 20%)
XX	Computing Platform	1N	Intel Celeron 3965U
		2N	Intel Core i5-7300U
		VN	Direct Monitor unit
X	RAM	N	none (<i>only Model "Direct Monitor"</i>)
		A	4 GB
		B	8 GB
		C	16 GB
		K	4 GB (<i>wide temp</i>)
		L	8 GB (<i>wide temp</i>)
		M	16 GB (<i>wide temp</i>)
X	Storage	N	none (<i>only Model "Direct Monitor"</i>)
		A	32 GB
		D	256 GB
		E	512 GB
		K	32 GB (<i>wide temp</i>)
		P	256 GB (<i>wide temp</i>)
		Q	512 GB (<i>wide temp</i>)
X	Software	N	none (<i>only Model "Direct Monitor"</i>)
		1	Windows 10 IoT Enterprise
		2	P+F RM Shell 5
		X	<i>Other software options</i>
XX-	Mounting	S1-	Panel mounting w/ stainless steel bezel
NN0	Options	NN0	Standard