



Mannheim, 2023-04-03

i.V. Rolf Wessels  
Executive Vice President  
Business Unit MCC+HMI  
Division MCC+HMI

i.V. Dr. Marc Seißler  
Head of Product Management HMI  
Business Unit HMI  
Division MCC+HMI

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-4984B  
Date / Datum: 2023-04-03

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



## ■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

## ■ Product Family / Produktfamilie

Product Family / Produktfamilie	Item number / Artikelnr.	Description / Beschreibung
RM-320P-NX-XXXX-D-XXXXXXXX-NN0	70124565-*	Panel mount Thin Client
PC-320P-NX-XXXX-D-XXXXXXXX-NN0		Panel mount PC
DM-320P-NX-XXXX-D-XXXXXXXX-NN0		Panel mount Direct Monitor

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

*Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.*

## ■ Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
<b>2014/30/EU (EMC)</b> (L96/79-106)	EN 61000-6-4:2007+A1:2011 EN 55035:2017/A11:2020 EN 55011:2016+A1:2017
<b>2011/65/EU (RoHS)</b> (L174/88-110)	EN IEC 63000:2018-12

## ■ ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

XX-XXXX-XX-XXXX-X-XXXXXXXX-NN0			
Variable	Feature	Option	Description
XX-XXXX-	Technology	RM-320P-	Remote Monitor Panel
		PC-320P-	Panel PC
		DM-320P-	Direct Monitor Panel
X	Certification	N	Industrial, non-ex general purpose
X-	Operating Temperature	A-	0 ... 45 °C
		B-	-20 ... 55 °C
XXXX-	Display	22GT-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch
		22FC-	21.5" (16:9), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
		19SC-	19" (5:4), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
		15FC-	15,6" (16:9), FullHD (1920x1080 pixel), capacitive touch w/ optical bonding
X-	Power Supply	D-	24 V DC (+/- 20%)
XX	Computing Platform	1N	Intel Celeron 3965U
		2N	Intel Core i5-7300U
		VN	Direct Monitor unit
X	RAM	N	none ( <i>only Model "Direct Monitor"</i> )
		A	4 GB
		B	8 GB
		C	16 GB
		K	4 GB ( <i>wide temp</i> )
		L	8 GB ( <i>wide temp</i> )
		M	16 GB ( <i>wide temp</i> )
X	Storage	N	none ( <i>only Model "Direct Monitor"</i> )
		A	32 GB
		B	64 GB
		D	256 GB
		E	512 GB
		K	32 GB ( <i>wide temp</i> )
		L	64 GB ( <i>wide temp</i> )
		P	256 GB ( <i>wide temp</i> )
		Q	512 GB ( <i>wide temp</i> )
X	Software	N	none ( <i>only Model "Direct Monitor"</i> )
		1	Windows 10 IoT Enterprise 2019 LTSC
		2	P+F RM Shell 5
		3	Windows 10 IoT Enterprise 2021 LTSC
		4	P+F RM Shell 6
		X	<i>Other software options</i>
XX-	Mounting	S1-	Panel mounting w/ stainless steel bezel (SS304)
		S2-	Panel mounting w/ stainless steel bezel (SS316L)
NN0	Options	NN0	Standard