

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-5267
Date: 2021-07-05

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

■ Productfamily

Productfamily	Description
ML100... ML107...	Photoelectrical standard sensor
M100... MV100... M107... MV107...	Through beam sensor

The „...“ marked parts of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

■ Regulations and Standards

UK Regulation	Standards
UK SI 2016 No. 1091 (EMC)	EN IEC 60947-5-2:2020-03
UK SI 2012 No. 3032 (RoHS)	SN EN IEC 63000:2018-12

■ Affixed UKCA Marking



■ Signatures

Berlin, 2021-07-05

ppa. Hinrik Weber
Factory Automation –
Director Business Unit Opto

i.V. Dr. Lutz Lohmann
Factory Automation –
Manager Development Opto KOS

■ ANNEX TYPE CODE

The „...“ marked parts of the type code are placeholders and can be replaced by the following code:

Nomenclature												
Series		Optical principle, optional		Operating distance, only for triangulation		Version, optional, several combinations		Customer specific assembling instruction, optional		Special options, optional		Y-Variants, optional
I	-	II	-	III	-	IV	-	V	-	VI	-	VII
ML100 M100 MV100 ML107 M107 MV107	-	6 8 8-H 8-HW 8-HGU 8-W 54 54-F 54-G 55 55-F 55-G	-	Any number and letter combination or a number range consisting of two sets of numbers separated by a “ - “	-	IR RT	-	Any number with 4 digits	-	Options in any number and order consisting of a slash, followed by up to 10 alpha-numeric characters	-	Y followed by up to six digits