

Pepperl+Fuchs SE  
 Lilienthalstrasse 200  
 68307 Mannheim  
 Germany  
 Phone +49 621 776-0  
 Fax +49 621 776-1000

No: DOC-5355  
 Date: 2021-09-01

Copyright Pepperl+Fuchs  
 www.pepperl-fuchs.com



### ■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### ■ Productfamily / Produktfamilie

Productfamily / Produktfamilie	Description / Beschreibung
MLV12...	Photoelectrical standard sensor
M12... MV12...	Through beam sensor

The „...“ marked parts of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### ■ Regulations and Standards

UK Regulation	Standards
UK SI 2016 No. 1091 (EMC)	EN IEC 60947-5-2:2020-03
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

### ■ Affixed UKCA Marking



### ■ Signatures

Mannheim, 2021-09-01

ppa. Hinrik Weber  
 Factory Automation –  
 Director Business Unit Opto

i.V. Dr. Lutz Lohmann  
 Factory Automation –  
 Manager Development Opto KOS

## ■ ANNEX TYPE CODE

The „...“ marked parts of the type code are placeholders and can be replaced by the following code:

Die mit „...“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

Nomenclature										
Series		Optical principle, optional		Operating distance, only for triangulation sensors		Version, optional, several combinations		Customer specific assembling instruction, optional		Special options, optional
<b>I</b>	-	<b>II</b>	-	<b>III</b>	-	<b>IV</b>	-	<b>V</b>	-	<b>VI</b>
MLV12 M12 MV12	-	8-H 8-HW 54 54-G	-	Any number and letter combination	-	F1 F2 F3 F4 IR LAS RT	-	Any number with 4 digits	-	Options in any number and order consisting of a slash, followed by up to 10 alpha-numeric characters