

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6580  
Date: 2022-05-31

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### Productfamily

| Productfamily | Description                     |
|---------------|---------------------------------|
| O...-R103-... | Photoelectrical standard sensor |

The „...“ marked parts of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### Regulations and Standards

| UK Regulation              | Standards                |
|----------------------------|--------------------------|
| UK SI 2016 No. 1091 (EMC)  | EN IEC 60947-5-2:2020-03 |
| UK SI 2012 No. 3032 (RoHS) | EN IEC 63000:2018-12     |

### Affixed UKCA Marking



### Signatures

Mannheim, 2022-05-31

ppa. Hinrik Weber  
Factory Automation –  
Director Business Unit Opto

i.v. Dr. Lutz Lohmann  
Factory Automation –  
Manager Development Opto KOS

## ■ ANNEX TYPE CODE

The „...“ marked parts of the type code are placeholders and can be replaced by the following code:

| <b>Nomenclature / Nomenklatur</b> |  |   |   |                       |   |                              |   |  |   |                           |   |                                |
|-----------------------------------|--|---|---|-----------------------|---|------------------------------|---|--|---|---------------------------|---|--------------------------------|
| Sensor principle                  | Sensor category and optical principle  | Sensing range                                       |   | Mechanical properties |   | Electrical process interface |   | Mechanical process interface, optional   |   | Special options, optional |   | Y-Variants, optional           |
| <b>I</b>                          | <b>II</b>                              | <b>III</b>  | - | <b>IV</b>             | - | <b>V</b>                     | - | <b>VI</b>                                | - | <b>VII</b>                | - | <b>VIII</b>                    |
| O                                 | BD<br>BE<br>BR<br>BT<br>MT<br>QT<br>BG | Sensing range (mm) plus optional designation letter | - | R103                  | - | any                          | - | V3<br>V31<br>0,3MV1<br>0,3MV3<br>0,3MV31 | - | 1R<br>1T<br>IR<br>L       | - | Y followed by up to six digits |