

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6623  
Date: 2022-07-14

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### Product Family

Product Family	Description
PHAUuu-F200v-B17-w-V1D-xxxx	Vision 2-D Sensor

The „u,v,w,x“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN 55011:2016-04 EN 61000-6-2/AC:2005-09 EN 61000-6-2:2005-08 EN 61000-6-4/A1:2011-02 EN 61000-6-4:2007-01

### Affixed UKCA Marking



### Signatures

Mannheim, 2022-07-14

i.V. Hilmar Hofmann

RnD Manager Business Unit Industrial  
Vision Components

i.V. Armin Hornberger

Head of Global Product Management  
Business Unit Industrial Vision  
Components

**■ ANNEX TYPE CODE**

The „u,v,w,x“ marked letters of the type code are placeholders and can be replaced by the following code:

<b>PHAuuu-F200v-B17-w-V1D-xxxx</b>					
<b>u = Working Distance</b>	<b>v = Housing Variant</b>	<b>B17</b>	<b>w = Option</b>	<b>V1D</b>	<b>x = Customer Specific</b>
150 – mm Distance	F200 – Mounting 90°	Interface	T - Temperature	Connection	
200 – mm Distance	F200A – Mounting 180°				
250 – mm Distance					
300 – mm Distance					
350 – mm Distance					
400 – mm Distance					
500 – mm Distance					
600 – mm Distance					
650 – mm Distance					
700 – mm Distance					
800 – mm Distance					
950 – mm Distance					