

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-6801
Date: 2022-10-14

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

■ Product Family

■ Product Family	Description
VOSxxxxy-Fxxxxy-xxxx-x	Vision Sensor

The „x,y“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

■ Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN 55011/A11:2020-03 EN 55011:2016-04 EN 55032/A11:2020-03 EN 55032:2015-07 EN 55035:2017-07 EN 61326-1:2013-01

■ Affixed UKCA Marking



■ Signatures

Mannheim, 2022-10-14

i.V. Hilmar Hofmann
RnD Manager Business Unit Industrial
Vision Components

i.V. Markus Karch
Product Manager Business Unit Industrial
Vision Components

■ ANNEX TYPE CODE

The „x,y“ marked letters of the type code are placeholders and can be replaced by the following code:

VOSxxxxy-Fxxx-xxxx-x					
xxxx Resolution	y Image Sensor	Fxxx Housing Variant	y Light Color	xxxx Focal length	x Firmware
1000 640x480 2000 1280x960 5000 2560x2048	/ Monochrome C Color	F226 Standard w. two connectors F227 Large w. three connectors	/ no integrated light W integrated light white LED R integrated light red LED B integrated light blue LED I integrated light infrared LED U integrated light UV LED	6MM integrated lens with 6mm 8MM integrated lens with 8mm 12MM integrated lens with 12mm 16MM integrated lens with 16mm C C-Mount	S Standard I Ident