



Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Br.: DOC-2577C
Date / Datum: 2024-03-21

Signatures / Potpisi

Mannheim, 2024-03-21

i.V. Ulrich Ehrenfried
Head of Innovation Unit
Electromagnetic Sensors

i.V. Thorsten Schieck
Product Manager Electromagnetic
Sensors

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



The English version represents the signed original.
Verzija na engleskom jeziku predstavlja potpisani originalni dokument.

Declaration of Conformity / Izjava o sukladnosti

We, Pepperl+Fuchs SE, declare under our sole responsibility that the products listed below are in conformity with the listed European Directives, Regulations, and standards.

Mi, Pepperl+Fuchs SE, izjavljujemo pod vlastitom i isključivom odgovornošću da su proizvodi u nastavku sukladni navedenim europskim direktivama, uredbama i standardima.

Products / Proizvodi

| Product Proizvod | Itemnumber Broj stavke | Description Opis |
|----------------------|---------------------------|---------------------|
| CBN10-F46-E0 | 051977 | Capacitive sensor |
| CBN10-F46-E2 | 051979 | Capacitive sensor |
| CBN10-F46-E2-0,1M-V1 | 260151 | Capacitive sensor |
| CBN10-F46-E2-0,4M-V3 | 259577 | Capacitive sensor |
| CBN10-F46-E2-10M | 181875 | Capacitive sensor |
| CBN10-F46-E3 | 051980 | Capacitive sensor |
| CBN2-F46-E0 | 051968 | Capacitive sensor |
| CBN2-F46-E1 | 051969 | Capacitive sensor |
| CBN2-F46-E2 | 051970 | Capacitive sensor |
| CBN2-F46-E3 | 051971 | Capacitive sensor |
| CBN5-F46-E0 | 051972 | Capacitive sensor |
| CBN5-F46-E1 | 050537 | Capacitive sensor |
| CBN5-F46-E2 | 051974 | Capacitive sensor |
| CBN5-F46-E2-10M | 122665 | Capacitive sensor |
| CBN5-F46-E3 | 051976 | Capacitive sensor |
| CBN5-F46-E3-5M | 222961 | Capacitive sensor |
| CBN7-F46-E2 | 239734 | Capacitive sensor |

Directives and Standards / Direktive i standardi

| EU Directive EU direktiva | Standards Standardi |
|----------------------------------|--------------------------|
| EMC 2014/30/EU (L96/79-106) | EN IEC 60947-5-2:2020-03 |
| RoHS 2011/65/EU (L174/88-110) | EN IEC 63000:2018-12 |