

Pepperl+Fuchs SE  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. /Nr.: **DOC-5069B**  
Date /Dato: **2023-04-21**

Copyright Pepperl+Fuchs  
[www.pepperl-fuchs.com](http://www.pepperl-fuchs.com)



### Declaration of conformity / Overensstemmelseserklæring

We Pepperl+Fuchs SE declare under our sole responsibility that the products listed below are in conformity with the listed European Directives and standards.

*Vi, Pepperl+Fuchs SE, erklærer hermed under eneansvar, at de nedenfor anførte produkter er i overensstemmelse med de angivne EU-direktiver og -standarder.*

### Products / Produkter

| Products<br>Produkter     | Itemnumber<br>Varenummer | Description<br>Beskrivelse |
|---------------------------|--------------------------|----------------------------|
| NBB15-30GM50-E2-3G-3D     | 70126049                 | Inductive sensor           |
| NBB2-12GM60-A2-3G-3D      | 70126031                 | Inductive sensor           |
| NBB15-30GM50-E2-V1-3G-3D  | 70126050                 | Inductive sensor           |
| NBB2-12GM40-Z0-3G-3D      | 70126030                 | Inductive sensor           |
| NBB15-30GM50-E3-V1-3G-3D  | 70126051                 | Inductive sensor           |
| NBB10-30GS50-Z4L-V1-3G-3D | 70134926-0010            | Inductive sensor           |
| NBB4-12GM50-E2-3G-3D      | 70126032                 | Inductive sensor           |
| NBB4-12GM50-E2-V1-3G-3D   | 70126033                 | Inductive sensor           |
| NBB8-18GM60-A2-V1-3G-3D   | 70126040                 | Inductive sensor           |
| NBN15-30GS50-Z4L-V1-3G-3D | 70134926-0012            | Inductive sensor           |
| NBB8-18GM50-E2-3G-3D      | 70126037                 | Inductive sensor           |
| NBB8-18GM50-E2-3G-3D-5M   | 70126038                 | Inductive sensor           |
| NBB8-18GM50-E2-V1-3G-3D   | 70126039                 | Inductive sensor           |
| NCB2-12GM40-E2-3G-3D      | 70126070                 | Inductive sensor           |
| NCB2-12GM40-E2-3G-3D-5M   | 70126071                 | Inductive sensor           |
| NCB2-12GM40-Z0-V1-3G-3D   | 70126034                 | Inductive sensor           |
| NCB5-18GM40-Z0-3G-3D      | 70126041                 | Inductive sensor           |

| Products<br>Produkter      | Itemnumber<br>Varenummer | Description<br>Beskrivelse |
|----------------------------|--------------------------|----------------------------|
| NCB5-18GM40-Z0-3G-3D-10M   | 70126042                 | Inductive sensor           |
| NCB5-18GM40-Z0-3G-3D-10M-Y | 70126043                 | Inductive sensor           |
| NCB5-18GM40-Z0-V1-3G-3D    | 70126044                 | Inductive sensor           |
| NCB5-18GM40-Z1-3G-3D       | 70126045                 | Inductive sensor           |
| NCB10-30GM40-Z0-3G-3D      | 70126052                 | Inductive sensor           |
| NCB10-30GM40-Z0-V1-3G-3D   | 70126053                 | Inductive sensor           |
| NCN8-18GM40-Z0-3G-3D       | 70126046                 | Inductive sensor           |
| NCB10-30GM40-Z1-3G-3D      | 70126054                 | Inductive sensor           |
| NCN8-18GM50-E2-3G-3D       | 70126047                 | Inductive sensor           |
| NCN8-18GM50-E2-3G-3D-5M    | 70126048                 | Inductive sensor           |
| NCN4-12GM40-E2-3G-3D       | 70126072                 | Inductive sensor           |
| NCN4-12GM40-E2-V1-3G-3D    | 70126073                 | Inductive sensor           |
| NCN4-12GM40-Z0-3G-3D       | 70126035                 | Inductive sensor           |
| NCN15-30GM40-Z0-3G-3D      | 70126055                 | Inductive sensor           |
| NJ10-30GM50-E2-3G-3D       | 70126077                 | Inductive sensor           |
| NJ10-30GM50-E2-3G-3D-5M    | 70126078                 | Inductive sensor           |
| NJ10-30GM50-E2-V1-3G-3D    | 70126079                 | Inductive sensor           |
| NJ15-30GM50-E2-3G-3D       | 70126080                 | Inductive sensor           |
| NJ15-30GM50-E2-V1-3G-3D    | 70126081                 | Inductive sensor           |
| NJ5-18GM50-E2-3G-3D        | 70126074                 | Inductive sensor           |
| NJ5-18GM50-E2-3G-3D-5M     | 70126075                 | Inductive sensor           |
| NJ5-18GM50-E2-V1-3G-3D     | 70126076                 | Inductive sensor           |

### Directives and Standards / Direktiver og standarder

| EU-Directive<br>EU-direktiv   | Standards<br>Standarder  |
|-------------------------------|--|
| ATEX 2014/34/EU (L96/309-356) | EN 60079-31:2014-07<br>EN IEC 60079-0:2018-07<br>EN IEC 60079-7/A1:2018-01<br>EN 60079-7:2015-12 |
| EMC 2014/30/EU (L96/79-106)   | EN IEC 60947-5-2:2020-03   |
| RoHS 2011/65/EU (L174/88-110) | EN IEC 63000:2018-12   |

### Affixed CE Marking / Anbragt CE-mærkning



## Signatures / Underskrifter

Mannheim, 2023-04-21



i.V. Ulrich Ehrenfried  
Head of Innovation Unit  
Electromagnetic Sensors



i.V. Mark Guenther  
Global Product Manager

The English version represents the signed original.  
*Den engelske version repræsenterer den underskrevne original.*

## ANNEX ATEX / ATEX-BILAG

### Marking and Certificates / Mærkning og certifikater

| Marking<br><i>Mærkning</i> | Certificate<br><i>Certifikat</i> | Issuer ID<br><i>Udsteder-ID</i> |
|----------------------------|----------------------------------|---------------------------------|
| ⊕ II 3 G                   | TÜV 20 ATEX 8523 X               | TUR                             |
| ⊕ II 3 D                   | TÜV 20 ATEX 8524 X               | TUR                             |

### Key for Issuer ID / Nøgle for udsteder-ID

| ID  | Issuer<br><i>Udsteder</i>   |
|-----|---|
| TUR | TÜV Rheinland Industrial Services GmbH<br>Automation and Functional Safety (AFS)<br>Am Grauen Stein<br>51105 Cologne<br>Germany |