

Pepperl+Fuchs SE
 Lilienthalstrasse 200
 68307 Mannheim
 Germany
 Phone +49 621 776-0
 Fax +49 621 776-1000

No: DOC-6563A
 Date: 2022-09-22

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Affixed UKCA Marking



Signatures

Mannheim, 2022-09-22

ppa. Wolfgang Helm
 Director
 Business Unit Sensors

i.V. Ulrich Ehrenfried
 Head of Innovation Unit
 Electromagnetic Sensors

Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

Products

Product	Item number	Description
NCN50-FP-N0-P4-V1	70133127	Inductive sensor
NJ15-M1K-N	70133067	Inductive sensor
NJ15-M1K-N-V1	70133129	Inductive sensor
NJ2-V3-N	70133090	Inductive sensor
NJ2-V3-N-V5	70133094	Inductive sensor
NJ2-V3-N-Y220141	70133097	Inductive sensor
NJ2-V3-N-Y70132206	70134413	Inductive sensor
NJ2-V3-N-0,075M	70133092	Inductive sensor
NJ4-F-N	70133120	Inductive sensor
NCB2-V3-N0	70133083	Inductive sensor
NCB2-V3-N0-Y243357	70133085	Inductive sensor
NCB2-V3-N0-Y244943	70133086	Inductive sensor
NCB2-V3-N0-2M	70133084	Inductive sensor
NCB40-FP-N0-P1	70133036	Inductive sensor
NCB40-FP-N0-P1-V1	70133125	Inductive sensor
NCB40-FP-N0-P4	70133126	Inductive sensor
NCN4-V3-N0	70133087	Inductive sensor
NCN4-V3-N0-V5	70133089	Inductive sensor
NJ50-FP-N-P1	70133037	Inductive sensor
NCN4-V3-N0-0,8M	70133088	Inductive sensor
NJ50-FP-N-P4	70133128	Inductive sensor

ANNEX UK SI 2016 No. 1107 (EX)

Approved Body QM-System:

Eurofins E&E CML Limited (2503)
 Newport Business Park - New Port Road
 CH65 4LZ Ellesmere Port
 United Kingdom

Marking and Certificates

Marking	Certificate	ID
	CML 21UKEX2975X	2503

Key for ID

ID	Responsible Body
2503	Eurofins E&E CML Limited Newport Business Park - New Port Road CH65 4LZ Ellesmere Port United Kingdom

Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12
UK SI 2016 No. 1091 (EMC)	EN 60947-5-6:2000-01 EN IEC 60947-5-2:2020-03
UK SI 2016 No. 1107 (EX)	EN 60079-11:2012-01 EN IEC 60079-0:2018-07