

# VisuNet HMIs for Operating and Visualizing Processes and MES



VisuNet monitors and workstations are purpose-built HMIs with industrial-rated components. They can be configured to the exact requirements of a wide variety of applications. The modularity is one of their key advantages. Single components can easily be assembled or replaced. This allows users to keep their devices state-of-the-art in a sustainable and cost-efficient way. Depending on your application, Pepperl+Fuchs offers a broad portfolio of industrial and hazardous-location-rated remote monitors, panel PCs, direct monitors and the possibility to use the KVM-over-IP technology with qualified switches.. Find out more: [www.pepperl-fuchs.com/hmi](http://www.pepperl-fuchs.com/hmi)

## VisuNet GXP



RM, PC

- Modular system
- Compact design
- Lightweight
- Field maintainable (module exchange)
- No Ex-protection housing for hazardous areas required

Zone 1/21,  
Zone 2/22



19 inch, 21.5 inch



-20 ... +50 °C



## VisuNet FLX



RM, PC, DM

- Modular system
- Global certifications
- Field maintainable (module exchange)
- Maximized configuration and installation flexibility
- Design in accordance with GMP

Zone 2/22  
Class I, II, III, Div. 2  
Non-hazardous areas



System: 21.5 inch  
Panel: 21.5 inch,  
19 inch, 15 inch



System A: 0 ... +40 °C  
System B: -20... +50 °C  
Panel A: 0 ... +45 °C  
Panel B: -20 ... +55 °C



## Industrial Box Thin Clients



- Rugged design
- Long-term availability
- High installation flexibility
- Passive cooling design; 24/7
- Pre-installed VisuNet RM Shell 6 thin client firmware
- Alternate versions available as PC/IGEL OS 12 or ThinManager Ready

BTC22: up to 2 × 4K  
BTC24: up to 4 × 4K



0 ... +55 °C  
or  
-20 ... +60 °C



Your automation, our passion.

 **PEPPERL+FUCHS**

# Industrial Box PCs



- 7<sup>th</sup> generation Intel Celeron and i5 embedded processor generation
- Supports high performance M.2 NVMe storage
- Up to 16 GB RAM and 512 GB storage
- High installation flexibility: stand-alone PC, panel PC, system with enclosure

-20 ... +55 °C



# Industrial Tablet Thin Client



- Thin Client solution (with VisuNet RM Shell firmware)
- Capacitive multitouch screen
- Outstanding wireless connectivity
- Intel Wireless AC9260
- Bluetooth® 5.0


Zone 2/22  
Class I, II, III, Div. 2  
Non-hazardous areas




11.6 inch  
widescreen display



-10 ... +55 °C




# Thin Client Software



## VisuNet RM Shell 6

- Eases configuration
- Enhances security and liability (easy and flexible configuration of remote profiles (RDP, VNC, etc.)
- High flexibility



## VisuNet Control Center

- Efficient, centralized remote configuration
- Simplified maintenance
- Monitoring and remote support
- Complements VisuNet RM Shell 6 firmware

# Peripherals/Accessories



## IDM 1-D/2-D Code Handheld Reader

- ATEX and IECEx Zone 1/21 and 2/22
- Bluetooth® and wired
- Compatible with all VisuNet families



## EXTA4 Keyboards

- Class I, II, III, Div. 2 and Zone 1/21; IP66
- Mouseless, touchpad mouse, joystick mouse, or wash-down approved optical trackball mouse available



## KVM-over-IP Switch

- Allows direct connection from a VisuNet remote monitor to a host system
- Supports concurrent remote and local access to an operator workstation



## Power Supplies

- Designed for use with VisuNet operator workstations and BTC box thin clients

# Engineered Solutions



Special mounting, dual monitor, mobile workstation, RFID, control elements, Wi-Fi, Div. 1, tailored to customer needs.