

HAZARDOUS (CLASSIFIED) LOCATION

Class I, Zone 0, IIC
Class I, Division 1, 2, Groups A,B,C,D
Class II, Division 1, 2, Groups E,F,G
Class III

Single Seal	Model	MWP*	Limited to: Process Temperature**
LHC-M51		40 (5800 psi)	-40°C...+100°C
PPC-M51		40 (580 psi)	-40°C...+125°C

* Limitations of the Maximum Working Pressure (MWP) are marked on the nameplate and must be considered!
** Limitations of the process temperature range depending on the used version are specified in the applicable technical information of the manufacturer and must be considered!

NONHAZARDOUS LOCATION

Any FM Approved Apparatus Suitable for Entity-concept or FISCO-concept

Intrinsically safe installations intrinsically safe for Cl. I, II, III Div. 1, Gp. ABCDEFG; AEx ia IIC T6

- FM Approved apparatus must be installed in accordance with manufacturer instructions
- FM Approved apparatus must meet the following requirements:
Uo or Voc or Vi ≤ Ui (Vmax) and Io or Isc or Ii ≤ Ii (Imax) and Po or Pmax ≤ Pi (Pmax)
- The maximum non-hazardous area voltage must not exceed 250 V
- The installation must be in accordance with the National Electrical Code NFPA 70 (NEC) and ANSI/ISA - RP 12.06.01 (except chapter 5).
- Be aware of multiple earthing of screen. The screen must be connected in accordance with National Electrical Code.
- Caution: Use only supply wires suitable for 5 °C above surrounding temperature
- Warning: Substitution of components may impair intrinsic safety.
- The polarity for connecting PA+ (1) and PA- (2) is of no importance due to an internal rectifier.

Division 2 and Zone 2 installation
Nonincendive Class I, Div. 2, group A,B,C,D Hazardous Location Installation (not for separated housing).

- Installation shall be in accordance with NEC using threaded conduits or other wiring methods in accordance with articles 500 to 510.
- Intrinsic safety barrier not required. Max. supply voltage 32 V. For T-code see table.
- Warning: Explosion Hazard- Do not disconnect equipment unless power has been switched off or the area is known to be non hazardous
- Nonincendive field wiring installation
The Nonincendive Field Wiring Circuit Concept allows interconnection of nonincendive field wiring apparatus with associated nonincendive field wiring apparatus or associated apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when Vmax ≤ Voc or Vi, Ca ≤ Ci + Ccable, La ≤ Li + Lcable
Transmitter parameters are as follows: Vmax = 32 VDC; Ci ≤ 5 nF; Li ≤ 10 µH; Imax = see note 12
- For these current controlled circuit, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the nonincendive field wiring or associated apparatus.
- Warning: Substitution of Components may impair suitability for Class I, Div. 2

PPC-M51, LHC-M51 with electronic insert for Profibus PA (Entity-Concept)

Ui (Vmax) = 24 V
Ii (Imax) = 250mA
Pi (Pmax) = 1.2 W
Ci ≤ 5nF
Li ≤ 10 µH
Leakage current ≤ 50 µA

Temperature classification	T6	T4
Max. ambient temperature	40°C 104 °F	70°C 158 °F

Min. ambient temp: -40°C (optional -50°C)

PPC-M51, LHC-M51 with electronic insert for Profibus PA/ (FISCO-Concept)

Ui (Vmax) = 17.5 V
Ii (Imax) = 500mA
Pi (Pmax) = 5.5 W
Ci ≤ 5nF
Li ≤ 10 µH
Leakage current ≤ 50 µA

Temperature classification	T6	T4
Max. ambient temperature	40°C 104 °F	70°C 158 °F

Min. ambient temp: -40°C (optional -50°C)

Any FM Approved Intrinsically Safe Apparatus Suitable for Entity-concept or FISCO concept

PPC-M51, LHC-M51 is suitable for the connection to a Profibus PA system according to the Entity- or FISCO-concept (as described below).

FISCO-Concept
The FISCO Concept allows interconnection of intrinsically safe apparatus to associated apparatus not specifically examined in such combination.
The criteria for interconnection is that the voltage (Ui or Vmax), the current (Ii or Imax) and the power (Pi or Pmax) which intrinsically safe apparatus can receive and remain intrinsically safe, considering faults, must be equal or greater than the voltage (Uo or Voc or Vi), the current (Io or Isc or Ii) and the power (Po or Pmax) levels which can be delivered by the associated apparatus, considering faults and applicable factors. In addition, the maximum unprotected capacitance (Ci) and inductance (Li) of each apparatus (other than the termination) connected to the fieldbus must be less than or equal to 5 nF and 10 µH respectively.
In each segment only one active device, normally the associated apparatus, is allowed to provide the necessary energy for the fieldbus system.
The voltage Uo (or Voc or Vi) of the associated apparatus has to be limited to the range of 14V to 24V d.c. All other equipment connected to the bus cable has to be passive, meaning that they are not allowed to provide energy to the system, except to a leakage current of 50 µA for each connected device.
Separately powered equipment needs a galvanic isolation to assure that the intrinsically safe fieldbus circuit remains passive.

The cable used to interconnect the devices needs to have the parameters in the following range:
loop resistance R': 15 ... 150 Ohm/km inductance per unit length L': 0.4 ... 1 mH/km
capacitance per unit length C': 80 ... 200 nF/km
C' = C' line/line + 0.5 C' line/screen, if both lines are floating or C' = C' line/line + C' line/screen, if the screen is connected to one line
length of spur cable: 30 m length of trunk cable: 1 km length of splice: 1 m
At each end of the trunk cable an approved infallible line termination with the following parameters is suitable:
R = 90 ... 100 Ohm, C = 0 ... 2.2 µF.
One of the allowed terminations might already be integrated in the associated apparatus.

116-0398

LHC-M51, PPC-M51 PROFIBUS PA
FM control drawing

71265370

FM Control Drawing no. 116-0398

Dieses Dokument enthält sicherheitsrelevante Angaben. Es darf nicht ohne Absprache mit dem Normenfachmann (NE Ex) geändert werden!
This document contains safety-relevant information. It must not be altered without the authorization of the norm expert (NE Ex)!

CONFIDENTIAL acc. to ISO 16016 Only valid as long as released in EDM or with a valid production documentation! date: 2014 March 04

PEPPERL+FUCHS

Control Drawing - FM

PPC-M51, LHC-M51 Profibus PA

16-990FM-12A

sheet 4 of 4