

Instruction Manual

1. Marking

FieldBarrier in Aluminum Housing F2D0-FB-Ex4.*
ATEX certificate: PTB 02 ATEX 2086 ATEX marking: Ⓜ II 2 (1) G Ex eb mb [ia Ga] IIC T4 Gb , Ⓜ II 2 (1) D Ex tb [ia Da] IIIC 130 °C Db
IECEX certificate: IECEX PTB 03.0003 IECEX marking: Ex eb mb [ia Ga] IIC T4 Gb , Ex tb [ia Da] IIIC 130 °C Db
Canada Certificates: 1845315 (CSA) Class I, Division 2, Groups A-D, T4 Class I, Zone 2, IIC, T4 Associated apparatus with intrinsically safe circuits for: Class I, Division 1, Groups A-D; Class II, Division 1, Groups E-G; Class III, Division 1 Class I, Zone 0, IIC
USA Certificates: 3015728 (FM) Class I, Division 2, Groups A-D, T4 Class I, Zone 2, AEx nA [ia] IIC T4 Associated apparatus with intrinsically safe circuits for: Class I, Division 1, Groups A-D; Class II, Division 1, Groups E-G; Class III, Division 1 Class I, Zone 0, IIC

FieldBarrier for cabinet installation RD0-FB-Ex4.*
ATEX certificate: PTB 02 ATEX 2086 ATEX marking: Ⓜ II 2 (1) G Ex eb mb [ia Ga] IIC T4 Gb , Ⓜ II (1) D [Ex ia Da] IIIC
IECEX certificate: IECEX PTB 03.0003 IECEX marking: Ex eb mb [ia Ga] IIC T4 Gb , [Ex ia Da] IIIC
Canada Certificates: 1845315 (CSA) Class I, Division 2, Groups A-D, T4 Class I, Zone 2, IIC, T4 Associated apparatus with intrinsically safe circuits for: Class I, Division 1, Groups A-D; Class II, Division 1, Groups E-G; Class III, Division 1 Class I, Zone 0, IIC
USA Certificates: 3015728 (FM) Class I, Division 2, Groups A-D, T4 Class I, Zone 2, AEx nA [ia] IIC T4 Associated apparatus with intrinsically safe circuits for: Class I, Division 1, Groups A-D; Class II, Division 1, Groups E-G; Class III, Division 1 Class I, Zone 0, IIC

The *-marked letters of the type code are placeholders for versions of the device.

Pepperl+Fuchs Group Lilienthalstraße 200, 68307 Mannheim, Germany
Internet: www.pepperl-fuchs.com

2. Validity

Specific processes and instructions in this instruction manual require special provisions to guarantee the safety of the operating personnel.

3. Target Group, Personnel

Responsibility for planning, assembly, commissioning, operation, maintenance, and dismantling lies with the plant operator. The personnel must be appropriately trained and qualified in order to carry out mounting, installation, commissioning, operation, maintenance, and dismantling of the device. The trained and qualified personnel must have read and understood the instruction manual.

4. Reference to Further Documentation

Observe directives, standards, and national laws applicable to the intended use and the operating location. Observe Directive 1999/92/EC in relation to hazardous areas. The corresponding datasheets, manuals, declarations of conformity, EU-type examination certificates, certificates, and control drawings if applicable supplement this document. You can find this information under www.pepperl-fuchs.com. For specific device information such as the year of construction, scan the QR code on the device. As an alternative, enter the serial number in the serial number search at www.pepperl-fuchs.com.

Due to constant revisions, documentation is subject to permanent change. Please refer only to the most up-to-date version, which can be found under www.pepperl-fuchs.com.

5. Intended Use

The device is a device coupler for fieldbus technology that connects field devices through intrinsically safe spurs to the trunk of a segment in accordance with IEC/EN 61158-2.

Each spur individually limits or isolates the current during a spur failure, ensuring that the remaining segment is not affected.

The spurs are intrinsically safe according to FISCO or Entity model.

The device must only be operated in the specified ambient temperature range and at the specified relative humidity without condensation.

5.1. F2D0-FB-Ex4.*

The device is designed for wall mounting.
The device is designed for panel mounting.

5.2. RD0-FB-Ex4.*

The device is designed for mounting on a 35 mm DIN mounting rail according to EN 60715.

6. Improper Use

Protection of the personnel and the plant is not ensured if the device is not used according to its intended use.

7. Mounting and Installation

Prior to mounting, installation, and commissioning of the device you should make yourself familiar with the device and carefully read the instruction manual.

Do not mount a damaged or polluted device.

Observe the tightening torque of the screws.

Requirements for Cables and Connection Lines

Observe the following points when installing cables and connection lines:

Observe the permissible core cross section of the conductor.

The insulation stripping length must be considered.

When using stranded conductors, crimp wire end ferrules on the conductor ends.

The non-intrinsically safe cables have to be fixed with cable ties at the intended fixtures.

The shield of each intrinsically safe circuit is internally connected to the grounding terminal via a capacitor.

Spur cable shield grounding:	Capacitive via < 12 nF
------------------------------	------------------------

The shield of the non-intrinsically safe circuit is internally connected to the grounding terminal via a capacitor.

Trunk cable shield grounding:	Capacitive via 5.7 nF Direct
-------------------------------	---------------------------------

The capacitor can be bypassed by setting the plug-in jumper between specified terminals.

Observe the grounding requirements for type of protection Ex i according to IEC/EN 60079-14.

7.1. Hazardous Area

If the device has already been operated in general electrical installations, the device may subsequently no longer be installed in electrical installations used in combination with hazardous areas.

Observe the installation instructions according to IEC/EN 60079-14.

Observe the installation instructions according to IEC/EN 60079-25.

Ensure that the trunk is equipped with two terminators, one at each end of the trunk.

7.1.1. Type of Protection

7.1.1.1. Type of Protection Ex i

The intrinsically safe output circuits may lead into Zone 0.

The intrinsically safe output circuits may lead into Zone 20.

Keep the separation distances between all non-intrinsically safe circuits and intrinsically safe circuits according to IEC/EN 60079-14.

For intrinsically safe circuits, the dielectric strength of the insulation against other intrinsically safe circuits and against the shield must be at least 500 V according to IEC/EN 60079-14.

Avoid electrostatic charges which could result in electrostatic discharges while installing, operating, or maintaining the device.

The connection cover of the device according to the degree of protection IP30 must be attached.

The device provides a grounding terminal to which an equipotential bonding conductor with a minimum cross section of 4 mm² must be connected.

Connection or disconnection of energized non-intrinsically safe circuits is only permitted in the absence of a potentially explosive atmosphere. Only plug and pull the plug-in jumpers in the absence of a potentially explosive atmosphere.

7.1.1.2. Type of Protection Ex e

If intrinsically safe and non-intrinsically safe circuits are being operated together, the connections of the non-intrinsically safe circuits must be covered. The cover must comply with degree of protection IP30 according to IEC/EN 60529.

7.1.2. Gas

The device may be installed in gas groups IIC, IIB, and IIA.

7.1.2.1. Zone 1

The device may be installed in Zone 1.

7.1.2.2. Zone 2

The device may be installed in Zone 2.

7.1.3. F2D0-FB-Ex4.* Dust

The device may be installed in dust groups IIIC, IIIB, and IIIA.

7.1.3.1. Zone 20

The intrinsically safe output circuits may lead into Zone 20.

7.1.3.2. Zone 22

The device may be installed in Zone 22.

8. Housings and Surrounding Enclosures

To ensure the degree of protection:

- The housing must not be damaged, distorted or corroded.
- All seals must be undamaged and correctly fitted.
- All screws of the housing/housing cover must be tightened with the appropriate torque.
- All cable glands must be suitably sized for the incoming cable diameters.
- All cable glands must be tightened with the appropriate torque.
- All unused cable glands must be sealed and closed with appropriate sealing plugs or stopping plugs.

8.1. RD0-FB-Ex4.*

The device must be installed and operated only in surrounding enclosures that

- comply with the requirements for surrounding enclosures according to IEC/EN 60079-0,
- are rated with the degree of protection IP54 according to IEC/EN 60529.

9. Operation, Maintenance, Repair

Prior to using the product make yourself familiar with it. Read the instruction manual carefully.

Do not repair, modify, or manipulate the device.

If there is a defect, always replace the device with an original device.

10. Delivery, Transport, Disposal

Check the packaging and contents for damage.

Check if you have received every item and if the items received are the ones you ordered.

Keep the original packaging. Always store and transport the device in the original packaging.

Store the device in a clean and dry environment. The permitted ambient conditions must be considered, see datasheet.

The device, built-in components, packaging, and any batteries contained within must be disposed in compliance with the applicable laws and guidelines of the respective country.