



EXTREME RIG MONITORING

VISUNET XT





VisuNet XT—Tougher than a roughneck

VisuNet XT... bringing new meaning to the concept of a rugged PC. This rugged HMI outperforms the abysmal conditions aboard open sea and land drilling rigs. It offers extreme durability and an extended operating range, -40 °C ... 65 °C, making it well suited for oil exploration and extraction.

The XT is a Zone 2/Div.2 operator workstation with an Intel® Core™ i7 processor. The high-bright, LED-backlit LCD panel provides high performance with an optically bonded, glove friendly touchscreen.

Certifications
ATEX and IECEx Zone 2
Class I, Div. 2
IP66, Type 4/4x

High-bright Display
15 in (38.1 cm) or 19 in (48.3 cm)
optically bonded, sunlight readable
LCD offers clear resolution under any
light conditions

Powerful
Intel Core i7
technology supports
modern software
applications

**Lightweight,
Low-profile
Housing**
State-of-the-art
design dissipates
heat without use
of a cooling fan

Versatility
Portable and field
maintainable

Accessibility
Keypad offers user-configurable
function keys, brightness and
touchscreen control, and LEDs
for internal diagnostics

Easy Setup
Simplified connectivity
through rear-mounted
junction box

Flexible Networking
Redundant LAN ports, multi-mode
fiber-optic LAN connection, and
wireless Ethernet

Mounting Options
Yoke mount, VESA mount
(100 mm), or panel mount
with optional sunshield
and keyboard tray

YOUR DEMAND. OUR CHALLENGE.

PROCESS INTERFACES

- Intrinsic Safety Barriers
- Signal Conditioners
- FieldConnex Fieldbus Infrastructure
- Remote I/O Systems
- HART Interface Solutions
- Level Measurement
- Purge+Pressurization Systems
- Industrial Monitors+HMI Solutions
- Explosion Protection Equipment
- Solutions for Process Interfaces
- Wireless Solutions

INDUSTRIAL SENSORS

- Proximity Sensors
- Photoelectric Sensors
- Industrial Vision
- Ultrasonic Sensors
- Rotary Encoders
- Positioning Systems
- Inclination and Acceleration Sensors
- AS-Interface
- Identification Systems
- Logic Control Units



Worldwide/German Headquarters

Pepperl+Fuchs GmbH
Mannheim · Germany
Tel. +49 621 776 2222
E-Mail: pa-info@de.pepperl-fuchs.com

North/Central America Headquarters

Pepperl+Fuchs Inc.
Twinsburg · Ohio · USA
Tel. +1 330 486 0002
E-Mail: pa-info@us.pepperl-fuchs.com

Asia Pacific Headquarters

Pepperl+Fuchs PTE Ltd.
Singapore
Company Registration No. 199003130E
Tel. +65 6779 9091
E-Mail: pa-info@sg.pepperl-fuchs.com

Southern/Eastern Europe Headquarters

Pepperl+Fuchs Elcon srl
Sulbiate · Italy
Tel. +39 039 62921
E-Mail: pa-info@it.pepperl-fuchs.com

www.pepperl-fuchs.com

 **PEPPERL+FUCHS**